








wiha Tool Sets

Tools that work for you

Screwdriver and Pliers Sets								
Part Number	Number of Pieces	Part Image	Set Type	Pliers Type	Screwdriver Type	Tip Sizes	Set Includes	Price
<u>WT26190</u>	8		Screwdriver and pliers set	Long Nose	⊕ Philips	#00 #0 #	(7) precision screwdrivers (Phillips: #00, #0, #1, slotted: 1.5mm, 2.0mm, 2.5mm, 3.0mm), (1) 6.3in industrial long nose pliers	\$61uk:
					⊖ Slotted	1.5mm 2.0mm 3.0mm		
<u>WT26191</u>			Screwdriver and cutters set	Classic Diagonal	⊕ Philips	#00 #0 #1	(7) precision screwdrivers (Phillips #00, #0, #1, slotted 1.5mm, 2.0mm, 2.5mm, 3.0mm), (1) 5in classic grip precision diagonal cutters	\$61uq:
					⊖ Slotted	1.5mm 2.0mm 3.0mm		
<u>WT32872</u>	5		Screwdriver, pliers, and cutters set	Long Nose Diagonal	⊕ Philips	#2	(1) 6.3in diagonal cutters, (1) 8in long nose pliers, (3) insulated SoftFinished screwdrivers (slotted 3.0mm, 4.5, Phillips #2), belt pack pouch	\$061vu:
					⊖ Slotted	3.0mm 4.0mm		
<u>WT32875</u>				Linesman's Long Nose	⊕ Philips	#2	(1) 9.5in lineman's pliers, (1) 8in long nose pliers, (3) insulated SoftFinish screwdrivers (slotted 4.5mm, 6.5mm, Phillips #2), belt pack pouch	\$061vv:
					⊖ Slotted	4.5mm 6.5mm		
<u>WT32984</u>	6			Combination Long Nose	⊕ Philips	#2	(1) combination pliers 8in, (1) long nose pliers 8in, (4) insulated SoftFinish screwdrivers (slotted 3.0mm, 4.5mm, Phillips #2, square #2)	\$061v?:
					⊖ Slotted	3.0mm 4.5mm		
					⊞ Square	#2		
<u>WT32985</u>	7		Screwdriver and pliers set	Combination Long Nose Diagonal	⊕ Philips	#1 #2	(4) insulated SoftFinish screwdrivers (slotted 3.0mm, 4.5mm, Phillips #1, #2), (1) industrial long nose pliers 6.3in, (1) industrial combination pliers 8in, (1) industrial diagonal cutters 6.3in, belt pack pouch	\$061v.:
					⊖ Slotted	3.0mm 4.5mm		
<u>WT32986</u>	11			Long Nose Combination Diagonal Wire Stripping	⊕ Philips	#1 #2	(1) long nose pliers 6.3in, (1) combination pliers 8in, (1) diagonal cutters 6.3in, (1) stripping pliers 6.3in, (7) insulated SoftFinish screwdrivers (slotted 3.0mm, 4.5mm, 5.5mm, Phillips #1, #2, square #1, #2), roll-up tool pouch	\$061x2:
					⊖ Slotted	3.0mm 4.5mm 5.5mm		
					⊞ Square	#1 #2		