


# Talk Fast for Less

Stride Ethernet Switches for Industrial Applications



Our STRIDE family of industrial grade unmanaged Ethernet switches and media converter is specifically built for industrial environments. Install Stride switches and your Ethernet control network will maintain more consistent cycle times even under heavy I/O and data exchange. The aluminum-housed models offer a wider operating temperature range (-40 to +85 deg. C).

## Advanced Industrial Hardware

- All 10/100BaseT RJ45 ports are auto-detecting, auto-crossover and auto-polarity
- Redundant power inputs with surge and spike protection
- Optional 100Mbps multimode fiber optic port for distances up to 4km
- **NEW!** SC (push-pull type) fiber optic connector models, in addition to ST (slotted bayonet) style versions

## Real-time Performance

- Store and forward wire speed switching - no delays
- Full-duplex operation with flow control (no collisions!)
- Auto crossover (MDI/MDIX) and auto polarity

## True Industrial Design

- Ethernet Isolation - 1500 VRMS 1 minute
- Spike protection - 5,000 watts (10x for 10 uS)
- UL (CUL) listed and CE certified
- Hazardous locations rated for Class 1, Div. 2

Also Available



Shielded Cat5e cables starting at: \$5.00

## CHECK OUT PRICES ON ETHERNET SWITCHES

### Product Description

Product Description	AutomationDirect	
	Stainless Plastic Models Price/Part Number	Stainless Metal Models Price/Part Number
5-port Ethernet switch with five 10/100BaseT RJ45 Ethernet ports	\$ 99.00 SE-SWSU	\$ 199.00 SE-SWSU-WT
8-port Ethernet switch with eight 10/100BaseT RJ45 Ethernet ports	\$ 172.00 SE-SWBU	\$ 259.00 SE-SWBU-WT
5-port Ethernet switch with four 10/100BaseT RJ45 Ethernet ports and one 100BaseFX fiber optic port	\$ 172.00 SE-SWSU-ST	\$ 259.00 SE-SWSU-ST-WT
9-port Ethernet switch with eight 10/100BaseT RJ45 Ethernet ports and one 100BaseFX fiber optic port	\$ 242.00 SE-SWBU-ST	\$ 399.00 SE-SWBU-ST-WT
Ethernet-Fiber converter with one 10/100BaseT RJ45 Ethernet port and one 100BaseFX fiber optic port	\$ 162.00 SE-MC2U-ST	

AutomationDirect prices are U.S. published prices as of October 2011. Prices subject to change without notice.

[www.automationdirect.com/ethernet](http://www.automationdirect.com/ethernet)

[www.automationdirect.com](http://www.automationdirect.com)

Go online or call to get complete information, request your free catalog, or place an order.

**1-800-633-0405**



Order Today,  
Ships Today!

\* See our Web site for details and restrictions.  
© Copyright 2012 AutomationDirect, Cumming, GA USA. All rights reserved.



**AUTOMATIONDIRECT**.com  
the #1 value in automation