

# KNOW Pressure

Our low-cost pressure sensors/gauges make it easy

proense®

## Proven Pressure Sensors/Gauges

Get great prices on accurate, dependable pressure sensors and gauges at AutomationDirect! Our vast selection of industrial ProSense® pressure components includes electronic and mechanical switches, transmitters and vacuum transducers, digital switches and transmitters, dial pressure gauges and differential pressure transmitters.

NEW!

## Digital Pressure Switches/Transmitters

### EPS Series starting at \$234.00

- Stainless steel housing with IP67 rating
- Ranges from vacuum to 5800 psig
- Selectable display units include: psig, bar, mbar, kPa, MPa, inH<sub>2</sub>O, and inHg
- Two discrete outputs: NO or NC
- Analog output on select models
- Large 2 color, 4 digit display
- Simple pushbutton setup

### QPS Series starting at \$69.00

- Two digital outputs (NPN or PNP) and a 4-20 mA analog output
- Two vacuum to pressure ranges (-14.5 to 14.5 psi and -14.5 to 145 psi)
- Tri-color digital LCD display

## Air Differential Pressure Transmitters

### DPTA Series starting at \$105.00

- Highly stable capacitive sensing element
- Positive, negative, and bi-directional pressure measurement
- Pressure ranges from 0.1 to 25 inches of water column

## Pressure Transmitters and Vacuum Transducers

### SPTD25 Series starting at \$99.00

- 4-20 mA or 0-10V outputs
- Sensing ranges from vacuum to 5000 psi
- Ceramic or stainless steel sensing elements
- M12, DIN connectorized, and cabled models

## Dial Pressure Gauges

### starting at \$6.50

- 1.5", 2.0" and 2.5" diameter dials
- Steel (IP52) or stainless steel (IP65) cases
- Dry or liquid filled models
- Sensing ranges from vacuum to 6000 psi

## Mechanical Pressure Switches

### MPS25 Series starting at \$82.00

- Sensing ranges from -15 psi to 7500 psi
- Tamper resistant field adjustment
- 1/4 inch NPT male process connection
- Snap-acting SPDT, 3 Amp, mechanical switch output

## Electronic Pressure Switches

### PSD25 Series starting at \$89.00

- Sensing ranges up to 5800 psi (400 bar)
- Long Life - over 50 million switching cycles
- Mechanical adjustment dials rotate quickly to establish the setpoint and reset point
- No calibration required

Research, price, buy at: [www.go2adc.com/pressure](http://www.go2adc.com/pressure)

Order Today, Ships Today!

VOTED  
Best in  
SERVICE  
15 YEARS

AUTOMATIONDIRECT.com

1-800-633-0405

the #1 value in automation

\*See our Web site for details and restrictions. © Copyright 2016 AutomationDirect, Cumming, GA USA. All rights reserved.