




# Screw-type at a glance

## Single-level Feed-through Terminal Blocks

Can handle currents up to 175A. These blocks accept a wide range of wiring sizes from 26 AWG to 2/0 AWG and have a 100kA SCCR rating. (Gray models shown)



## Double-level Feed-through Terminal Blocks

Come in 20A and 30A versions and a variety of colors. Optional features include LED indications, diode and direct cross level connections, and double-level terminal blocks with an added grounding leg.



## Triple-level Feed-through Terminal Blocks

Can handle up to 24A and can accept a wide range of wiring sizes from 24 AWG to 12 AWG. Optional features include NPN and PNP sensor blocks with LED indication, as well as triple-level terminal blocks with an added grounding leg.




## Ground Terminal Blocks

Available with screw-down or snap-on clamping ground connection and offer low contact resistance and corrosion-free connection points.



## Circuit Protection Blocks

Fuse holder terminal blocks can be used with 5mm x 20mm glass fuses up to 6.3A. Fuses are easily installed and removed. Fuse holder terminal blocks are an ideal solution when there is a need to change fuses while the system is powered.




### CHECK OUT OUR PRICES

| Terminal Connectors          | AutomationDirect<br>Distributor | US                   | A-B                  | Weidmuller            | Phoenix Contact |
|------------------------------|---------------------------------|----------------------|----------------------|-----------------------|-----------------|
| Terminal block 10 AWG        | \$0.37<br>KN-T10GRY             | \$2.84<br>1492-W6    | \$1.27<br>102010     | \$0.88<br>30 04 36 2  |                 |
| Terminal block 5 x 20mm fuse | \$1.66<br>KN-F10                | \$11.90<br>1492-WF84 | \$20.31<br>189650000 | \$8.65<br>30 46 09 0  |                 |
| Three-level terminal block   | \$1.60<br>KN-TL14               | \$8.41<br>1492-WTF3  |                      | \$8.01<br>27 15 97 9  |                 |
| DIN rail (2 m)               | \$5.60<br>DN-R35S1              | \$21.80 *<br>199-DR1 | \$16.97<br>51450     | \$23.90<br>08 01 73 9 |                 |

\* sold in 1m lengths  
Prices may vary by dealer. Many other part numbers are available from all vendors. All prices are U.S. published prices. AutomationDirect prices from April 2013 Price List. A-B prices from www.rockwellautomation.com/evolve-tools. 2/28/13. Phoenix Contact prices from www.phoenixcontact.com. 2/28/13. Weidmuller prices from www.digikey.com. 2/28/12.

**KONNECT-IT**  
TERMINAL BLOCKS  
A full lineup of economically-priced terminal blocks and accessories



Many Konnect-It terminal blocks are available in up to 8 colors!



## Accessories

- Separators
- Top Covers
- Label Holders
- End Brackets
- Jumpers
- Marking Tags
- ... and more

- AutomationDirect
- Company Information
- Systems Overview
- Programmable Controllers
- Field I/O
- Software
- C-more & other HMI
- Drives
- Soft Starters
- Motors & Gearbox
- Steppers/Servos
- Motor Controls
- Proximity Sensors
- Photo Sensors
- Limit Switches
- Encoders
- Current Sensors
- Pressure Sensors
- Temperature Sensors
- Pushbuttons/Lights
- Process
- Relays/Timers
- Comm.
- Terminal Blocks & Wiring
- Power
- Circuit Protection
- Enclosures
- Tools
- Pneumatics
- Safety
- Appendix
- Product Index
- Part # Index