

# Accessories for OPT2016-OPT2019 Photoelectric Sensors


## Right-Angle Mounting Brackets

Mounting bracket, right angle, steel and nickel plated. For use with OPT2016-OPT2019 photoelectric sensors.

| Mounting Brackets for OPT Series Photoelectric Sensors |        |   |      |                |
|--|--------|---|------|----------------|
| Part Number  | Price  | Description   | Qty. | Weight         |
| <b>OPT2033</b>   | \$5.50 | Right-angle mounting bracket, vertical adjustment, steel and nickel plated. For use with OPT2016 - OPT2019 photoelectric sensors. | 1    | 16g [0.564 oz] |

### Dimensions

mm [inches]



**OPT2033**

## Right-angle Swivel Mounting Systems


Mounting bracket, right-angle swivel, 360 degree vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT2016-OPT2019 photoelectric sensors. Available in all stainless steel or with an aluminum head with a stainless steel mounting plate.

| Accessories for 26.8mm Sensors |         |  |                     |                     |             |
|--------------------------------|---------|--|---------------------|---------------------|-------------|
| Part Number                    | Price   | Description  | Mounting Head       | Mounting Plate      | Weight [lb] |
| <b>OPT2120</b>                 | \$9.00  | Mounting bracket, right-angle swivel, 360 vertical and horizontal adjustment, aluminum, 12mm rod mount. For use with OPT2016-OPT2019 photoelectric sensors.            | Aluminum            | 304 Stainless Steel | 0.14        |
| <b>OPT2121</b>                 | \$16.00 | Mounting bracket, right-angle swivel, 360 vertical and horizontal adjustment, 304 stainless steel, 12mm rod mount. For use with OPT2016-OPT2019 photoelectric sensors. | 304 Stainless Steel | 304 Stainless Steel | 0.27        |

**Note: 304 Stainless steel mounting rods sold separately: OPT2109 (200mm length), OPT2110 (300mm length), and OPT2111 (500mm length).**

### Dimensions

mm [inches]



**OPT2120, OPT2121**

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings

# Mounting Rods

## Mounting Rods

304 Stainless steel rods for mounting swivel brackets OPT2112 - OPT2127. Available in three lengths: 200mm, 300mm, and 500mm. 12mm diameter.


| Mounting Rods for OPT2112-2127 Swivel Mounting Brackets |         |   |             |
|---|---------|---|-------------|
| Part Number   | Price   | Description   | Weight [lb] |
| <b>OPT2109</b>  | \$10.00 | Mounting rod, 12mm diameter, 200mm length, 304 stainless steel. | 0.41        |
| <b>OPT2110</b>  | \$12.00 | Mounting rod, 12mm diameter, 300mm length, 304 stainless steel. | 0.60        |
| <b>OPT2111</b>  | \$16.00 | Mounting rod, 12mm diameter, 500mm length, 304 stainless steel. | 0.98        |



**OPT2109, OPT2110, OPT2111**

## Dimensions


mm [inches]



## Right-angle Mounting Bracket

Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111.


| Accessories for 12mm Sensors |         |   |             |
|------------------------------|---------|---|-------------|
| Part Number                  | Price   | Description   | Weight [lb] |
| <b>OPT2108</b>               | \$12.00 | Mounting bracket, right-angle, nickel-plated brass. For use with 12mm mounting rods OPT2109, OPT2110 & OPT2111. | 0.07        |



**OPT2108**

## Dimensions

mm [inches]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings