

# 1437A Cut Sheet



Hammond pushbutton enclosure, 1 hole, 30mm, NEMA 12/13, 4 x 4 x 5in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1437A>

## Technical Specifications

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Brand</b>                        | Hammond              |
| <b>Item</b>                         | Pushbutton enclosure |
| <b>Number of Pushbutton Holes</b>   | 1 hole               |
| <b>Pushbutton Hole Nominal Size</b> | 30mm                 |
| <b>Slope Top</b>                    | No                   |
| <b>NEMA Rating</b>                  | 12/13                |
| <b>IP Rating</b>                    | IP54                 |
| <b>Nominal Enclosure Dimensions</b> | 4 x 4 x 5in (HxWxD)  |
| <b>Enclosure Height</b>             | 4.31in               |
| <b>Enclosure Width</b>              | 4.31in               |
| <b>Enclosure Depth</b>              | 4.91in               |

|                                 |              |
|---------------------------------|--------------|
| <b>Mounting</b>                 | Wall         |
| <b>Integral Mounting Feet</b>   | Yes          |
| <b>Integral Mounting Flange</b> | No           |
| <b>Dual Access</b>              | No           |
| <b>Knockouts</b>                | No           |
| <b>Material</b>                 | Carbon steel |
| <b>Color</b>                    | ANSI 61 gray |
| <b>Finish</b>                   | Powder coat  |
| <b>Cover Type</b>               | Screw cover  |
| <b>Padlockable</b>              | No           |
| <b>Keylocking</b>               | No           |
| <b>Additional Information</b>   | Extra deep   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1437A.pdf>  
See store item page for other formats.