

# 46052075 Cut Sheet



WERMA EvoSIGNAL Mini TwinFLASH series LED audible-visual signal beacon, 95 dB at 1m, continuous/pulse tone(s), double flash or EVS (Enhanced Visibility System) flashing (random flashing), blue, 62mm, 24 VAC/VDC, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/46052075>

## Technical Specifications

|                         |  |
|-------------------------|--|
| <b>Brand</b>            | WERMA  |
| <b>Item</b>             | Audible-visual signal beacon   |
| <b>Series</b>           | EvoSIGNAL Mini TwinFLASH   |
| <b>Bulb Type</b>        | LED  |
| <b>Operator Size</b>    | 62mm   |
| <b>Operator Color</b>   | Blue   |
| <b>Light Color(s)</b>   | Blue   |
| <b>Light Function</b>   | Double flash (ON 30ms, Off 160ms, ON 30ms, Off 740ms, 1 Hz flash frequency) or EVS (Enhanced Visibility System) flashing (random flashing) |
| <b>Housing Material</b> | Polycarbonate  |

|                             |                   |
|-----------------------------|-------------------|
| <b>Material</b>             | ABS/polycarbonate |
| <b>Loudness Decibel</b>     | 95 dB at 1m       |
| <b>Tone Frequency</b>       | 4 kHz             |
| <b>Tone Type</b>            | Continuous/pulse  |
| <b>Touch to Acknowledge</b> | No                |
| <b>Number of Alarms</b>     | 2                 |
| <b>Voltage Rating</b>       | 24 VAC/VDC        |
| <b>Mounting</b>             | Modular           |
| <b>IP Rating</b>            | IP66              |
| <b>Requires</b>             | Mounting adapter  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E164155                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/46052075.pdf>  
See store item page for other formats.