

# AH664HW Cut Sheet



AttaBox Heartland series enclosure, NEMA 1/3R/4/4X/6P/12, 6 x 6 x 4in (HxWxD), wall mount, polycarbonate, Pantone 7541 C light gray, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/AH664HW>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | AttaBox                      |
| <b>Item</b>                         | Enclosure                    |
| <b>Series</b>                       | Heartland                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 1/3R/4/4X/6P/12              |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 6 x 6 x 4in (HxWxD)          |
| <b>Enclosure Height</b>             | 7.40in                       |
| <b>Enclosure Width</b>              | 7.41in                       |
| <b>Enclosure Depth</b>              | 5.35in                       |

|                                 |                            |
|---------------------------------|----------------------------|
| <b>Mounting</b>                 | Wall                       |
| <b>Integral Mounting Feet</b>   | No                         |
| <b>Integral Mounting Flange</b> | No                         |
| <b>Dual Access</b>              | No                         |
| <b>Knockouts</b>                | No                         |
| <b>Bottom Gland Plate</b>       | No                         |
| <b>Material</b>                 | Polycarbonate              |
| <b>Color</b>                    | Pantone 7541 C light gray  |
| <b>Cover Type</b>               | Hinged screw cover         |
| <b>Shelf</b>                    | No                         |
| <b>Padlockable</b>              | Yes                        |
| <b>Keylocking</b>               | No                         |
| <b>Additional Information</b>   | Mounting feet and hardware |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E319779                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/AH664HW.pdf>  
See store item page for other formats.