

# CF5PB22 Cut Sheet



Stahlin CF series pushbutton enclosure, 5 holes, 22mm, NEMA 1/3R/4X/6P/12, 11 x 4 x 4in (HxWxD), wall mount, fiberglass reinforced polyester, gray, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CF5PB22>

## Technical Specifications

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Brand</b>                        | Stahlin              |
| <b>Item</b>                         | Pushbutton enclosure |
| <b>Series</b>                       | CF                   |
| <b>Number of Pushbutton Holes</b>   | 5 holes              |
| <b>Pushbutton Hole Nominal Size</b> | 22mm                 |
| <b>Slope Top</b>                    | No                   |
| <b>NEMA Rating</b>                  | 1/3R/4X/6P/12        |
| <b>IP Rating</b>                    | IP68                 |
| <b>Nominal Enclosure Dimensions</b> | 11 x 4 x 4in (HxWxD) |
| <b>Enclosure Height</b>             | 11.13in              |

|                                 |                                 |
|---------------------------------|---------------------------------|
| <b>Enclosure Width</b>          | 3.81in                          |
| <b>Enclosure Depth</b>          | 3.89in                          |
| <b>Mounting</b>                 | Wall                            |
| <b>Integral Mounting Feet</b>   | No                              |
| <b>Integral Mounting Flange</b> | No                              |
| <b>Dual Access</b>              | No                              |
| <b>Knockouts</b>                | No                              |
| <b>Material</b>                 | Fiberglass reinforced polyester |
| <b>Color</b>                    | Gray                            |
| <b>Cover Type</b>               | Screw cover                     |
| <b>Padlockable</b>              | No                              |
| <b>Keylocking</b>               | No                              |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64358                                 |
| <b>UL Recognized File #</b> | E333478                                |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR069014                               |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/CF5PB22.pdf>  
See store item page for other formats.