


CR2701-200-C298 Cut Sheet



Code barcode scanner, 1D and 2D, imager, cordless, Bluetooth communication, USB, general duty, 1280 x 960 optical resolution. Removable battery, charging base station and 3ft USB cable included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/CR2701-200-C298>

Technical Specifications

Brand	Code
Item	Barcode scanner
Form Factor	Palm
Scanner Capability	1D and 2D
Scanner Type	Imager
Connectivity	Cordless
Communication Type	Bluetooth
Connection	USB
Duty Rating	General duty
Optical Resolution	1280 x 960
Decode Capability	<ul style="list-style-type: none">• 1D: BC412, Codabar, Code 11, Code 32, Code 39, Code 93, Code 128, IATA 2 of 5, Interleaved 2 of 5, GS1 DataBar, Hong Kong 2 of 5, Matrix 2 of 5, MSI Plessey, NEC 2 of 5, Plessey, Straight 2 of 5, Telepen, Trioptic, UPC/EAN/JAN• Stacked 1D: Codablock F, Code 49, GS1 Composite (CC-A/CC-B/CC-C), MicroPDF, PDF417• 2D: Aztec Code, Data Matrix, Data Matrix Rectangular Extension, Grid Matrix, Han Xin, Maxicode, Micro QR Code, QR Code, QR Model 1• Postal: Australian Post, Canada Post, Intelligent Mail, Japan Post, KIX Code, Korea Post, Planet, Post-net, UK Royal Mail, UPU ID-tags

Field Of View	High Density: 30 degree horizontal by 20 degree vertical and Wide Field: 50 degree horizontal by 33.5 degree vertical
Shock Rating	Multiple drops of 6ft on concrete
IP Rating	IP65
Operating Temperature	-20 degrees to 55 degrees C/-4 degrees to 131 degrees F
Includes	Removable battery, charging base station and 3ft USB cable
Dangerous Goods	<ul style="list-style-type: none">• Battery Installed: NO• Packaging Instructions: 966• UN Number: UN3481• Hazard Type: Lithium Ion Batteries• Battery Type: Battery• Watt Hours: 4.9• Replacement Battery: N/A• Generic Battery: N/A

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/CR2701-200-C298.pdf>
See store item page for other formats.