

# H161407HCF-6P-P10 Cut Sheet



Integra Premium series enclosure, NEMA 1/2/3/3R/3S/4/4X/5/6/6P/12/13, 16 x 14 x 7in (HxWxD), wall mount, polycarbonate, gray, gloss finish, clear polycarbonate hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/H161407HCF-6P-P10>

## Technical Specifications

|                                     |                               |
|-------------------------------------|-------------------------------|
| <b>Brand</b>                        | Integra                       |
| <b>Item</b>                         | Enclosure                     |
| <b>Series</b>                       | Premium                       |
| <b>Subpanel</b>                     | Purchase subpanel separately  |
| <b>Slope Top</b>                    | No                            |
| <b>NEMA Rating</b>                  | 1/2/3/3R/3S/4/4X/5/6/6P/12/13 |
| <b>IP Rating</b>                    | IP68                          |
| <b>Nominal Enclosure Dimensions</b> | 16 x 14 x 7in (HxWxD)         |
| <b>Enclosure Height</b>             | 16.70in                       |
| <b>Enclosure Width</b>              | 14.70in                       |
| <b>Enclosure Depth</b>              | 8.04in                        |

|                                 |  |
|---------------------------------|--|
| <b>Mounting</b>                 | Wall                                   |
| <b>Integral Mounting Flange</b> | No                                     |
| <b>Dual Access</b>              | No                                     |
| <b>Knockouts</b>                | No                                     |
| <b>Material</b>                 | Polycarbonate                          |
| <b>Color</b>                    | Gray                                   |
| <b>Finish</b>                   | Gloss                                  |
| <b>Cover Type</b>               | Clear polycarbonate hinged screw cover |
| <b>Padlockable</b>              | No                                     |
| <b>Keylocking</b>               | No                                     |
| <b>Includes</b>                 | (2) mounting flanges                   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E207562                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/H161407HCF-6P-P10.pdf>  
See store item page for other formats.