

# HW-141206CHQRW Cut Sheet



Wiegmann Premier series enclosure, NEMA 1/3/3S/4X/12/13, 14 x 12 x 6in (HxWxD), wall mount, fiberglass reinforced polyester, gray, crowned single-door, (2) quick-release latches, padlock hasp and staple, acrylic window.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HW-141206CHQRW>

## Technical Specifications

|                                 |                              |
|---------------------------------|------------------------------|
| <b>Brand</b>                    | Wiegmann                     |
| <b>Item</b>                     | Enclosure                    |
| <b>Series</b>                   | Premier                      |
| <b>Subpanel</b>                 | Purchase subpanel separately |
| <b>Slope Top</b>                | No                           |
| <b>NEMA Rating</b>              | 1/3/3S/4X/12/13              |
| <b>Nominal Enclosure Height</b> | 14in                         |
| <b>Nominal Enclosure Width</b>  | 12in                         |
| <b>Nominal Enclosure Depth</b>  | 6in                          |
| <b>Mounting</b>                 | Wall                         |
| <b>Integral Mounting Feet</b>   | No                           |
| <b>Integral Mounting Flange</b> | No                           |

|                                  |                                 |
|----------------------------------|---------------------------------|
| <b>Dual Access</b>               | No                              |
| <b>Knockouts</b>                 | No                              |
| <b>Material</b>                  | Fiberglass reinforced polyester |
| <b>Color</b>                     | Gray                            |
| <b>Cover Type</b>                | Crowned single-door             |
| <b>Hinge Type</b>                | Continuous hinge                |
| <b>Number of Hinges Per Door</b> | 1                               |
| <b>Latch Type</b>                | (2) quick-release latches       |
| <b>Padlock Attachment Type</b>   | Padlock hasp and staple         |
| <b>Window Material</b>           | Acrylic                         |
| <b>Padlockable</b>               | Yes                             |
| <b>Keylocking</b>                | No                              |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HW-141206CHQRW.pdf>  
See store item page for other formats.