

# HYJ16138SS Cut Sheet



Hammond sanitary enclosure, slope top, NEMA 3R/4/4X/12, 16 x 13 x 8in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/HYJ16138SS>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Hammond                      |
| <b>Item</b>                         | Sanitary enclosure           |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | Yes                          |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 3R/4/4X/12                   |
| <b>IP Rating</b>                    | IP69K                        |
| <b>Nominal Enclosure Dimensions</b> | 16 x 13 x 8in (HxWxD)        |
| <b>Enclosure Height</b>             | 16.36in                      |
| <b>Enclosure Width</b>              | 13.40in                      |
| <b>Enclosure Depth</b>              | 8.53in                       |
| <b>Mounting</b>                     | Wall                         |

|                                 |                     |
|---------------------------------|---------------------|
| <b>Integral Mounting Feet</b>   | No                  |
| <b>Integral Mounting Flange</b> | No                  |
| <b>Dual Access</b>              | No                  |
| <b>Knockouts</b>                | No                  |
| <b>Bottom Gland Plate</b>       | No                  |
| <b>Material</b>                 | 304 stainless steel |
| <b>Finish</b>                   | #4 brush            |
| <b>Cover Type</b>               | Screw cover         |
| <b>Shelf</b>                    | No                  |
| <b>Padlockable</b>              | No                  |
| <b>Keylocking</b>               | No                  |
| <b>Includes</b>                 | Mounting hardware   |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E517628/E65324                         |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/HYJ16138SS.pdf>  
See store item page for other formats.