

# RM1U0804SBK Cut Sheet



Hammond enclosure, 1U, 2 x 8 x 4in (HxWxD), desktop mount, aluminum, black, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/RM1U0804SBK>

## Technical Specifications

|                                     |                     |
|-------------------------------------|---------------------|
| <b>Brand</b>                        | Hammond             |
| <b>Item</b>                         | Enclosure           |
| <b>Slope Top</b>                    | No                  |
| <b>3-Piece Assembly</b>             | No                  |
| <b>Vented</b>                       | No                  |
| <b>Nominal Enclosure Dimensions</b> | 2 x 8 x 4in (HxWxD) |
| <b>Enclosure Height</b>             | 1.75in              |
| <b>Enclosure Width</b>              | 8.30in              |
| <b>Enclosure Depth</b>              | 4.25in              |
| <b>Rack Height</b>                  | 1U                  |
| <b>Mounting</b>                     | Desktop             |
| <b>Integral Mounting Feet</b>       | No                  |
| <b>Integral Mounting Flange</b>     | No                  |

|                               |                               |
|-------------------------------|-------------------------------|
| <b>Dual Access</b>            | No                            |
| <b>Knockouts</b>              | No                            |
| <b>Bottom Gland Plate</b>     | No                            |
| <b>Material</b>               | Aluminum                      |
| <b>Color</b>                  | Black                         |
| <b>Finish</b>                 | Powder coat                   |
| <b>Cover Type</b>             | Screw cover                   |
| <b>Shelf</b>                  | No                            |
| <b>Padlockable</b>            | No                            |
| <b>Keylocking</b>             | No                            |
| <b>Includes</b>               | (4) self-adhesive rubber feet |
| <b>Additional Information</b> | Assembly required             |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | None  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/RM1U0804SBK.pdf>  
See store item page for other formats.