

# SCE-72XM3418SS Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 72 x 34 x 18in (HxWxD), freestanding, 304 stainless steel, #4 brush finish, single-door, 3-point padlocking handle, powder coated subpanel included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-72XM3418SS>

## Technical Specifications

|                                     |                        |                                  |                                 |
|-------------------------------------|------------------------|----------------------------------|---------------------------------|
| <b>Brand</b>                        | Saginaw                | <b>Mounting</b>                  | Freestanding                    |
| <b>Item</b>                         | Disconnect enclosure   | <b>Integral Mounting Feet</b>    | No                              |
| <b>Slope Top</b>                    | No                     | <b>Material</b>                  | 304 stainless steel             |
| <b>Vented</b>                       | No                     | <b>Finish</b>                    | #4 brush                        |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13          | <b>Cover Type</b>                | Single-door                     |
| <b>IP Rating</b>                    | IP66                   | <b>Hinge Type</b>                | Concealed hinges                |
| <b>Disconnect Mounting</b>          | Right flange           | <b>Number of Hinges Per Door</b> | 4                               |
| <b>Nominal Enclosure Dimensions</b> | 72 x 34 x 18in (HxWxD) | <b>Latch Type</b>                | 3-point padlocking handle       |
| <b>Enclosure Height</b>             | 72.00in                | <b>Padlockable</b>               | Yes                             |
| <b>Enclosure Width</b>              | 33.50in                | <b>Keylocking</b>                | No                              |
| <b>Enclosure Depth</b>              | 19.05in                | <b>Subpanel</b>                  | Powder coated subpanel included |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | E69392                                                              |
| <b>UL Recognized File #</b> | None                                                                |
| <b>UL Hazardous File #</b>  | None                                                                |
| <b>CE</b>                   | None                                                                |
| <b>CSA File #</b>           | None                                                                |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-72XM3418SS.pdf>  
See store item page for other formats.