

# SCE-90XM4EW18 Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/12/13, right flange, 90 x 158 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 4-door, 3-point padlocking handle, (2) powder coated subpanels included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-90XM4EW18>

## Technical Specifications

|                                 |                      |
|---------------------------------|----------------------|
| <b>Brand</b>                    | Saginaw              |
| <b>Item</b>                     | Disconnect enclosure |
| <b>Slope Top</b>                | No                   |
| <b>Vented</b>                   | No                   |
| <b>NEMA Rating</b>              | 3R/12/13             |
| <b>IP Rating</b>                | IP55                 |
| <b>Disconnect Mounting</b>      | Right flange         |
| <b>Nominal Enclosure Height</b> | 90in                 |
| <b>Nominal Enclosure Width</b>  | 157.5in              |
| <b>Nominal Enclosure Depth</b>  | 19.07in              |
| <b>Mounting</b>                 | Freestanding         |
| <b>Material</b>                 | Carbon steel         |

|                                  |                                                                                                                   |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------|
| <b>Color</b>                     | ANSI 61 gray                                                                                                      |
| <b>Finish</b>                    | Powder coat                                                                                                       |
| <b>Cover Type</b>                | 4-door                                                                                                            |
| <b>Hinge Type</b>                | Concealed hinges                                                                                                  |
| <b>Number of Hinges Per Door</b> | 4                                                                                                                 |
| <b>Latch Type</b>                | 3-point padlocking handle                                                                                         |
| <b>Padlockable</b>               | Yes                                                                                                               |
| <b>Keylocking</b>                | No                                                                                                                |
| <b>Subpanel</b>                  | (2) powder coated subpanels included                                                                              |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | E69392                                                              |
| <b>UL Recognized File #</b> | None                                                                |
| <b>UL Hazardous File #</b>  | None                                                                |
| <b>CE</b>                   | None                                                                |
| <b>CSA File #</b>           | None                                                                |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-90XM4EW18.pdf>  
See store item page for other formats.