

# SCE-42HS3712LP Cut Sheet



Saginaw disconnect enclosure, NEMA 3R/4/12/13, right flange, 42 x 37 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, plated steel clamps, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-42HS3712LP>

## Technical Specifications

|                                 |                      |
|---------------------------------|----------------------|
| <b>Brand</b>                    | Saginaw              |
| <b>Item</b>                     | Disconnect enclosure |
| <b>Slope Top</b>                | No                   |
| <b>Vented</b>                   | No                   |
| <b>NEMA Rating</b>              | 3R/4/12/13           |
| <b>IP Rating</b>                | IP66                 |
| <b>Disconnect Mounting</b>      | Right flange         |
| <b>Nominal Enclosure Height</b> | 42in                 |
| <b>Nominal Enclosure Width</b>  | 37.38in              |
| <b>Nominal Enclosure Depth</b>  | 13.07in              |
| <b>Mounting</b>                 | Wall                 |
| <b>Integral Mounting Feet</b>   | Yes                  |
| <b>Material</b>                 | Carbon steel         |

|                                  |                                                                                                                   |
|----------------------------------|-------------------------------------------------------------------------------------------------------------------|
| <b>Color</b>                     | ANSI 61 gray                                                                                                      |
| <b>Finish</b>                    | Powder coat                                                                                                       |
| <b>Cover Type</b>                | Single-door                                                                                                       |
| <b>Hinge Type</b>                | Concealed hinges                                                                                                  |
| <b>Number of Hinges Per Door</b> | 3                                                                                                                 |
| <b>Latch Type</b>                | Plated steel clamps                                                                                               |
| <b>Padlockable</b>               | No                                                                                                                |
| <b>Keylocking</b>                | No                                                                                                                |
| <b>Subpanel</b>                  | Purchase subpanel separately                                                                                      |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | E69392                                                              |
| <b>UL Recognized File #</b> | None                                                                |
| <b>UL Hazardous File #</b>  | None                                                                |
| <b>CE</b>                   | None                                                                |
| <b>CSA File #</b>           | None                                                                |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-42HS3712LP.pdf>  
See store item page for other formats.