


# SCE-60XEL3712SSLP Cut Sheet



Saginaw Enviroline series disconnect enclosure, NEMA 3R/4/4X/12/13, right flange, 60 x 37 x 12in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-60XEL3712SSLP>

## Technical Specifications

|                                     |                        |
|-------------------------------------|------------------------|
| <b>Brand</b>                        | Saginaw                |
| <b>Item</b>                         | Disconnect enclosure   |
| <b>Series</b>                       | Enviroline             |
| <b>Slope Top</b>                    | No                     |
| <b>Vented</b>                       | No                     |
| <b>NEMA Rating</b>                  | 3R/4/4X/12/13          |
| <b>IP Rating</b>                    | IP66                   |
| <b>Disconnect Mounting</b>          | Right flange           |
| <b>Nominal Enclosure Dimensions</b> | 60 x 37 x 12in (HxWxD) |
| <b>Enclosure Height</b>             | 60.00in                |
| <b>Enclosure Width</b>              | 37.38in                |
| <b>Enclosure Depth</b>              | 13.10in                |

|                                  |                              |
|----------------------------------|------------------------------|
| <b>Mounting</b>                  | Wall                         |
| <b>Integral Mounting Feet</b>    | No                           |
| <b>Material</b>                  | 304 stainless steel          |
| <b>Finish</b>                    | #4 brush                     |
| <b>Cover Type</b>                | Single-door                  |
| <b>Hinge Type</b>                | Concealed hinges             |
| <b>Number of Hinges Per Door</b> | 3                            |
| <b>Latch Type</b>                | 3-point padlocking handle    |
| <b>Padlockable</b>               | Yes                          |
| <b>Keylocking</b>                | No                           |
| <b>Subpanel</b>                  | Purchase subpanel separately |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-60XEL3712SSLP.pdf>  
See store item page for other formats.