

# SCE-8C8ELJ Cut Sheet



Saginaw operator console, NEMA 3R/4/12/13, 8 x 8 x 7in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 1/4-turn semi-flush latch.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-8C8ELJ>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Operator console             |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 3R/4/12/13                   |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 8 x 8 x 7in (HxWxD)          |
| <b>Enclosure Height</b>             | 7.44in                       |
| <b>Enclosure Width</b>              | 8.00in                       |
| <b>Enclosure Depth</b>              | 7.09in                       |
| <b>Mounting</b>                     | Desktop or pedestal          |
| <b>Integral Mounting Feet</b>       | No                           |
| <b>Integral Mounting Flange</b>     | No                           |

|                               |                                     |
|-------------------------------|-------------------------------------|
| <b>Dual Access</b>            | No                                  |
| <b>Knockouts</b>              | No                                  |
| <b>Bottom Gland Plate</b>     | No                                  |
| <b>Material</b>               | Carbon steel                        |
| <b>Color</b>                  | ANSI 61 gray                        |
| <b>Finish</b>                 | Powder coat                         |
| <b>Cover Type</b>             | Single-door                         |
| <b>Hinge Type</b>             | ELJ removable hinge                 |
| <b>Number of Lid Hinges</b>   | 2                                   |
| <b>Latch Type</b>             | 1/4-turn semi-flush latch           |
| <b>Number Of Latches</b>      | 1                                   |
| <b>Shelf</b>                  | No                                  |
| <b>Padlockable</b>            | No                                  |
| <b>Keylocking</b>             | No                                  |
| <b>Additional Information</b> | Purchase pedestal column separately |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CE</b>                   | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/SCE-8C8ELJ.pdf>  
See store item page for other formats.