

# SCE-N80XM4018 Cut Sheet



Saginaw NextGen series disconnect enclosure, NEMA 3R/4/12/13, 80 x 40 x 18in (HxWxD), freestanding, carbon steel, ANSI 61 gray, polyester powder coat finish, single-door, 3-point padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SCE-N80XM4018>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Saginaw                      |
| <b>Item</b>                         | Disconnect enclosure         |
| <b>Series</b>                       | NextGen                      |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>NEMA Rating</b>                  | 3R/4/12/13                   |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 80 x 40 x 18in (HxWxD)       |
| <b>Enclosure Height</b>             | 80.00in                      |
| <b>Enclosure Width</b>              | 40.25in                      |
| <b>Enclosure Depth</b>              | 18.00in                      |
| <b>Mounting</b>                     | Freestanding                 |
| <b>Integral Mounting Feet</b>       | No                           |
| <b>Integral Mounting Flange</b>     | No                           |

|                                  |                                 |
|----------------------------------|---------------------------------|
| <b>Dual Access</b>               | No                              |
| <b>Knockouts</b>                 | No                              |
| <b>Material</b>                  | Carbon steel                    |
| <b>Color</b>                     | ANSI 61 gray                    |
| <b>Finish</b>                    | Polyester powder coat           |
| <b>Cover Type</b>                | Single-door                     |
| <b>Hinge Type</b>                | Concealed hinges                |
| <b>Number of Hinges Per Door</b> | 4                               |
| <b>Latch Type</b>                | 3-point padlocking combo handle |
| <b>Number Of Latches</b>         | 1                               |
| <b>Shelf</b>                     | No                              |
| <b>Padlockable</b>               | Yes                             |
| <b>Keylocking</b>                | No                              |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E69392  |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | None  |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/SCE-N80XM4018.pdf>  
See store item page for other formats.