

# SDN12423108PL Cut Sheet



Wiegmann disconnect enclosure, NEMA 12/13, right flange, 42 x 31 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 3-point padlocking handle, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/SDN12423108PL>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Wiegmann              |
| <b>Item</b>                         | Disconnect enclosure  |
| <b>Slope Top</b>                    | No                    |
| <b>NEMA Rating</b>                  | 12/13                 |
| <b>Disconnect Mounting</b>          | Right flange          |
| <b>Nominal Enclosure Dimensions</b> | 42 x 31 x 8in (HxWxD) |
| <b>Enclosure Height</b>             | 42.00in               |
| <b>Enclosure Width</b>              | 31.38in               |
| <b>Enclosure Depth</b>              | 8.88in                |
| <b>Mounting</b>                     | Wall                  |
| <b>Integral Mounting Feet</b>       | Yes                   |
| <b>Integral Mounting Flange</b>     | No                    |
| <b>Dual Access</b>                  | No                    |
| <b>Knockouts</b>                    | No                    |
| <b>Material</b>                     | Carbon steel          |

|                                  |   |
|----------------------------------|---|
| <b>Color</b>                     | ANSI 61 gray  |
| <b>Finish</b>                    | Powder coat   |
| <b>Cover Type</b>                | Single-door   |
| <b>Hinge Type</b>                | Continuous hinge  |
| <b>Number of Hinges Per Door</b> | 1   |
| <b>Latch Type</b>                | 3-point padlocking handle   |
| <b>Padlockable</b>               | Yes   |
| <b>Keylocking</b>                | No  |
| <b>Subpanel</b>                  | Purchase subpanel separately  |
| <b>For Use With</b>              | Most major brand disconnect switches and circuit breakers   |
| <b>Additional Information</b>    | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64791                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |