

# TRD-SHR1024A5D Cut Sheet



Koyo TRD-SR series incremental (quadrature) rotary encoder, light duty, 5-26 VDC, radial exit, NPN open collector output, 1024 ppr, 8mm hollow shaft, 38mm diameter body, IP50, 6.5ft/2m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/TRD-SHR1024A5D>

## Technical Specifications

|                            |                          |
|----------------------------|--------------------------|
| <b>Brand</b>               | Koyo                     |
| <b>Item</b>                | Encoder                  |
| <b>Series</b>              | TRD-SR                   |
| <b>Feedback Type</b>       | Incremental (quadrature) |
| <b>Encoder Type</b>        | Rotary                   |
| <b>Duty Rating</b>         | Light duty               |
| <b>Voltage Rating</b>      | 5-26 VDC                 |
| <b>Exit Orientation</b>    | Radial                   |
| <b>Encoder Output Type</b> | NPN open collector       |
| <b>Encoder Resolution</b>  | 1024 ppr                 |
| <b>Shaft Type</b>          | Hollow                   |
| <b>Shaft Diameter</b>      | 8mm                      |

|                              |          |
|------------------------------|----------|
| <b>Radial Shaft Load</b>     | 30N      |
| <b>Axial Shaft Load</b>      | 20N      |
| <b>Frequency Response</b>    | 200 kHz  |
| <b>Speed Rating</b>          | 6000rpm  |
| <b>Flange Mount</b>          | No       |
| <b>Encoder Body Diameter</b> | 38mm     |
| <b>Housing Material</b>      | Aluminum |
| <b>IP Rating</b>             | IP50     |
| <b>Cable Length</b>          | 6.5ft/2m |
| <b>Cable Diameter Size</b>   | 6mm      |
| <b>Wire Size</b>             | 26 AWG   |
| <b>Connector Type</b>        | Pigtail  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E189395                                |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/2d/TRD-SHR1024A5D.pdf>  
See store item page for other formats.