

# WRD907224FSD4 Cut Sheet



Wiegmann KwikHinge series enclosure, NEMA 3R/4/12, 90 x 72 x 24in (HxWxD), freestanding, carbon steel, ANSI 61 gray, powder coat finish, 2-door, 3-point keylocking/padlocking combo handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/WRD907224FSD4>

## Technical Specifications

|                                     |                              |
|-------------------------------------|------------------------------|
| <b>Brand</b>                        | Wiegmann                     |
| <b>Item</b>                         | Enclosure                    |
| <b>Series</b>                       | KwikHinge                    |
| <b>Subpanel</b>                     | Purchase subpanel separately |
| <b>Slope Top</b>                    | No                           |
| <b>3-Piece Assembly</b>             | No                           |
| <b>Vented</b>                       | No                           |
| <b>NEMA Rating</b>                  | 3R/4/12                      |
| <b>IP Rating</b>                    | IP66                         |
| <b>Nominal Enclosure Dimensions</b> | 90 x 72 x 24in (HxWxD)       |
| <b>Enclosure Height</b>             | 90.13in                      |
| <b>Enclosure Width</b>              | 72.13in                      |
| <b>Enclosure Depth</b>              | 25.35in                      |
| <b>Mounting</b>                     | Freestanding                 |

|                                 |  |
|---------------------------------|--|
| <b>Integral Mounting Feet</b>   | No   |
| <b>Integral Mounting Flange</b> | No   |
| <b>Dual Access</b>              | No   |
| <b>Knockouts</b>                | No   |
| <b>Bottom Gland Plate</b>       | No   |
| <b>Material</b>                 | Carbon steel                               |
| <b>Color</b>                    | ANSI 61 gray                               |
| <b>Finish</b>                   | Powder coat                                |
| <b>Cover Type</b>               | 2-door                                     |
| <b>Hinge Type</b>               | KwikHinge sliding hinge pins               |
| <b>Latch Type</b>               | 3-point keylocking/padlocking combo handle |
| <b>Shelf</b>                    | No   |
| <b>Padlockable</b>              | Yes  |
| <b>Keylocking</b>               | Yes  |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E64791, E470978                        |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | None                                   |
| <b>CSA File #</b>           | None                                   |
| <b>RoHS Status</b>          | No                                     |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/WRD907224FSD4.pdf>  
See store item page for other formats.