


Enclosure Accessories



Drip Shields

Drip shields attach easily to the enclosure with stainless steel screws, gasket and sealing washers to protect door hardware from dripping water and settling dust. All mounting hardware is included. Stainless steel door clamps are furnished to replace the standard door clamps on kits for enclosure widths up to 36.0 in [914 mm].



Shipping Schedule				
Same day	1 - 5 days	1 - 7 days	1 - 15 days	1 - 20 days
Color indicates shipping lead time in business days.				

Drip Shield	Price	Material/Finish	For Use With	Wt.[lb]	Description
DK12	\$47.00	14 gauge Steel/ANSI 61 gray polyester powder	12in [305mm] NEMA 12 and NEMA 4 enclosures	0.95	Wiegmann enclosure drip shield kit. Includes 2 replacement stainless steel door clamps, integral gasket, and mounting hardware.
SSDK12	\$125.00	14 gauge Stainless Steel/grained finish		0.95	
DK16	\$56.00	14 gauge Steel/ANSI 61 gray polyester powder	16in [406mm] NEMA 12 and NEMA 4 enclosures	1.20	
SSDK16	\$137.00	14 gauge Stainless Steel/grained finish		0.95	
DK20	\$61.00	14 gauge Steel/ANSI 61 gray polyester powder	20in [508mm] NEMA 12 and NEMA 4 enclosures	1.59	
SSDK20	\$149.00	14 gauge Stainless Steel/grained finish		1.20	
DK24	\$60.00	14 gauge Steel/ANSI 61 gray polyester powder	24in [610mm] NEMA 12 and NEMA 4 enclosures	1.90	Wiegmann enclosure drip shield kit. Includes 3 replacement stainless steel door clamps, integral gasket, and mounting hardware.
SSDK24	\$161.00	14 gauge Stainless Steel/grained finish		1.59	
DK30	\$67.00	14 gauge Steel/ANSI 61 gray polyester powder	30in [762mm] NEMA 12 and NEMA 4 enclosures	2.40	
SSDK30	\$179.00	14 gauge Stainless Steel/grained finish		1.90	
DK36	\$74.00	14 gauge Steel/ANSI 61 gray polyester powder	36in [914mm] NEMA 12 and NEMA 4 enclosures	2.85	
SSDK36	\$197.00	14 gauge Stainless Steel/grained finish		2.40	
DK42	\$87.00	14 gauge Steel/ANSI 61 gray polyester powder	42in [1067mm] NEMA 12 and NEMA 4 enclosures	2.98	Wiegmann enclosure drip shield kit. Includes integral gasket and mounting hardware.
DK48	\$94.00		48in [1219mm] NEMA 12 and NEMA 4 enclosures	3.80	
DK60	\$109.00		60in [1524mm] NEMA 12 and NEMA 4 enclosures	4.75	
DK72	\$123.00		72in [1829mm] NEMA 12 and NEMA 4 enclosures	5.70	

Dimensions

