
















C-more Micro EA3 Series Selection Guide

C-more Micro EA3 Series Panels			
Part Number		Description	Price
EA3-S3ML-RN		C-more Micro EA3 series HMI, 3in monochrome STN LCD, 128 x 64 pixel, LED backlight, supports (1) serial port.	\$98.00
EA3-S3ML-R		C-more Micro EA3 series touch screen HMI, 3in monochrome STN LCD, 128 x 64 pixel, LED backlight, supports (1) serial port.	\$146.00
EA3-S3ML		C-more Micro EA3 series touch screen HMI, 3in monochrome STN LCD, 128 x 64 pixel, supports (2) serial, (1) Ethernet and (1) USB ports.	\$198.00
EA3-T4CL		C-more Micro EA3 series touch screen HMI, 4in color TFT LCD, widescreen, 480 x 272 pixel, WQVGA, supports (2) serial, (1) Ethernet and (1) USB port.	\$269.00
EA3-T6CL		C-more Micro EA3 series touch screen HMI, 6in color TFT LCD, 320 x 240 pixel, QVGA, supports (2) serial and (1) USB port.	\$299.00
EA3-T8CL		C-more Micro EA3 series touch screen HMI, 8in color TFT LCD, 800 x 600 pixel, SVGA, supports (2) serial and (1) USB port.	\$749.00
EA3-T10CL		C-more Micro EA3 series touch screen HMI, 10in color TFT LCD, 800 x 600 pixel, SVGA, supports (2) serial and (1) USB port.	\$899.00



Part Number	Panel Software / Firmware Version Required
EA3-S3ML-RN	4.30 or later
EA3-S3ML-R	4.30 or later
EA3-S3ML	4.20 or later
EA3-T4CL	4.20 or later
EA3-T6CL	3.6 or later
EA3-T8CL	3.5 or later
EA3-T10CL	3.5 or later

C-more Micro EA3 Series Selection Guide



C-more Micro Programming Software			
Part Number		Description	Price
EA-MG-PGMSW		C-more Micro Windows-based programming software, CD. For use with C-more Micro panels. Requires USB port connection from PC to C-more Micro panel.	\$25.00
EA-MG-PGM-CBL		USB/RS-232 programming cable assembly, USB Type A male to RJ12 male, 6ft cable length. For use with C-more Micro panels, CLICK CPUs, Do-more H2 series CPUs, and DirectLogic CPUs.	\$43.00
USB-CBL-AB3		USB cable, 3ft/0.9m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$7.50
USB-CBL-AB6		USB cable, 6ft/1.8m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$9.50
USB-CBL-AB10		USB cable, 10ft/3m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$18.00
USB-CBL-AB15		USB cable, 15ft/4.5m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$22.50
USB-CBL-AMICB6		Programming cable, USB A to micro-B USB, 6ft cable length. For use with Productivity2000 CPUs and most USB devices.	\$5.00


C-more Micro EA3 Series Panel Accessories			
Part Number		Description	Price
EA-ECOM		C-more Micro communication expansion module, (1) RJ45 10/100 Mbps Ethernet port. For use with EA3 series 6in, 8in and 10in HMIs. For programming and PLC communications.	\$50.00
EA-ADPTR-4		DSUB port adapter, 15-pin male to 15-pin female, right angle cable entry. For use with C-more Micro EA1 series 4in and 6in HMIs, C-more Micro EA3 series 3in, 4in, and 6in HMIs, C-more EA9 6in and 7in HMIs.	\$39.00
EA-COMCON-3		DSUB port adapter, 15-pin male to 6-pole RS-422/485 terminal block, right angle cable entry. For use with C-more Micro EA1 series 4in and 6in HMIs, C-more Micro EA3 series 3in, 4in, and 6in HMIs, C-more EA9 6in and 7in HMIs.	\$42.00
EA-COMCON-3A		DSUB port adapter, 15-pin male to 6-pole RS-422/485 terminal block, straight cable entry. For use with C-more Micro EA1 series 3in with EA1-MG-SP1, C-more Micro EA3 series 8in and 10in HMIs, C-more EA9 8in, 10in, 12in and 15in HMIs.	\$19.00
EA-MG-COV-CL		Screen protector, clear, 3in. Package of 5. For use with C-more Micro 3in HMIs.	\$35.50
EA-4-COV3		Screen protector, replacement, non-glare, 4in. Package of 3. For use with C-more Micro EA3-T4CL 4in HMIs.	\$33.50
EA-6-COV2		Screen protector, non-glare, 6in. Package of 3. For use with C-more and C-more Micro 6in panels.	\$37.00
EA-8-COV2		Screen protector, non-glare, 8in. Package of 3. For use with C-more and C-more Micro 8in panels.	\$40.00
EA-10-COV2		Screen protector, non-glare, 10in. Package of 3. For use with C-more and C-more Micro 10in panels.	\$45.50

C-more Micro EA3-S3ML-RN and EA3-S3ML-R Panels Overview



C-more Micro EA3 Series Panels			
Part Number		Description	Price
EA3-S3ML-RN		C-more Micro EA3 series HMI, 3in monochrome STN LCD, 128 x 64 pixel, LED backlight, supports (1) serial port.	\$98.00
EA3-S3ML-R		C-more Micro EA3 series touch screen HMI, 3in monochrome STN LCD, 128 x 64 pixel, LED backlight, supports (1) serial port.	\$146.00

Part Number	Panel Software / Firmware Version Required
EA3-S3ML-RN	4.30 or later
EA3-S3ML-R	



C-more Micro Programming Software			
Part Number		Description	Price
EA-MG-PGMSW		C-more Micro Windows-based programming software, CD. For use with C-more Micro panels. Requires USB port connection from PC to C-more Micro panel.	\$25.00
EA-MG-PGM-CBL		USB/RS-232 programming cable assembly, USB Type A male to RJ12 male, 6ft cable length. For use with C-more Micro panels, CLICK CPUs, Do-more H2 series CPUs, and DirectLogic CPUs.	\$43.00




C-more Micro EA3 Series Panel Accessories			
Part Number		Description	Price
EA-MG-COV-CL		Screen protector, clear, 3in. Package of 5. For use with C-more Micro 3in HMIs.	\$35.50

C-more Micro EA3-S3ML and EA3-T4CL Panels Overview




C-more Micro EA3 Series Panels			
Part Number		Description	Price
EA3-S3ML		C-more Micro EA3 series touch screen HMI, 3in monochrome STN LCD, 128 x 64, supports (2) serial, (1) Ethernet and (1) USB ports.	\$198.00
EA3-T4CL		C-more Micro EA3 series touch screen HMI, 4in color TFT LCD, widescreen, 480 x 272, WQVGA, supports (2) serial, (1) Ethernet and (1) USB ports.	\$269.00

Part Number	Panel Software / Firmware Version Required
EA3-S3ML	4.20 or later
EA3-T4CL	



C-more Micro Programming Software			
Part Number		Description	Price
EA-MG-PGMSW		C-more Micro Windows-based programming software, CD. For use with C-more Micro panels. Requires USB port connection from PC to C-more Micro panel.	\$25.00
USB-CBL-AMICB6		Programming cable, USB A to micro-B USB, 6ft cable length. For use with Productivity2000 CPUs and most USB devices.	\$5.00

C-more Micro EA3 Series Panel Accessories			
Part Number		Description	Price
EA-ADPTR-4		DSUB port adapter, 15-pin male to 15-pin female, right angle cable entry. For use with C-more Micro EA1 series 4in and 6in HMIs, C-more Micro EA3 series 3in, 4in, and 6in HMIs, C-more EA9 6in and 7in HMIs.	\$39.00
EA-COMCON-3		DSUB port adapter, 15-pin male to 6-pole RS-422/485 terminal block, right angle cable entry. For use with C-more Micro EA1 series 4in and 6in HMIs, C-more Micro EA3 series 3in, 4in, and 6in HMIs, C-more EA9 6in and 7in HMIs.	\$42.00
EA-MG-COV-CL		Screen protector, clear, 3in. Package of 5. For use with C-more Micro 3in HMIs.	\$35.50
EA-4-COV3		Screen protector, replacement, non-glare, 4in. Package of 3. For use with C-more Micro EA3-T4CL 4in HMIs.	\$33.50






C-more Micro 6-inch, 8-inch & 10-inch EA3 Panels Overview

C-more Micro EA3 Series Panels			
Part Number	Description	Price	
EA3-T6CL	 C-more Micro EA3 series touch screen HMI, 6in color TFT LCD, 320 x 240, QVGA, supports (2) serial and (1) USB port.	\$299.00	
EA3-T8CL	 C-more Micro EA3 series touch screen HMI, 8in color TFT LCD, 800 x 600, SVGA, supports (2) serial and (1) USB port.	\$749.00	
EA3-T10CL	 C-more Micro EA3 series touch screen HMI, 10in color TFT LCD, 800 x 600, SVGA, supports (2) serial and (1) USB port.	\$899.00	

Part Number	Panel Software / Firmware Version Required
EA3-T6CL	3.6 or later
EA3-T8CL	3.5 or later
EA3-T10CL	3.5 or later

C-more Micro Programming Software			
Part Number	Description	Price	
EA-MG-PGMSW	 C-more Micro Windows-based programming software, CD. For use with C-more Micro panels. Requires USB port connection from PC to C-more Micro panel.	\$25.00	
USB-CBL-AB3		USB cable, 3ft/0.9m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$7.50
USB-CBL-AB6		USB cable, 6ft/1.8m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$9.50
USB-CBL-AB10		USB cable, 10ft/3m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$18.00
USB-CBL-AB15		USB cable, 15ft/4.5m cable length, standard A plug to standard B plug. For use with Productivity, C-more and Do-more programming and most USB devices.	\$22.50

C-more Micro 6-inch, 8-inch & 10-inch EA3 Panels Overview

C-more Micro EA3 Series Panel Accessories			
Part Number		Description	Price
EA-ECOM		C-more Micro communication expansion module, (1) RJ45 10/100 Mbps Ethernet port. For use with EA3 series 6in, 8in and 10in HMIs. For programming and PLC communications.	\$50.00
EA-ADPTR-4		DSUB port adapter, 15-pin male to 15-pin female, right angle cable entry. For use with C-more Micro EA1 series 4in and 6in HMIs, C-more Micro EA3 series 3in, 4in, and 6in HMIs, C-more EA9 6in and 7in HMIs.	\$39.00
EA-COMCON-3		DSUB port adapter, 15-pin male to 6-pole RS-422/485 terminal block, right angle cable entry. For use with C-more Micro EA1 series 4in and 6in HMIs, C-more Micro EA3 series 3in, 4in, and 6in HMIs, C-more EA9 6in and 7in HMIs.	\$42.00
EA-COMCON-3A		DSUB port adapter, 15-pin male to 6-pole RS-422/485 terminal block, straight cable entry. For use with C-more Micro EA1 series 3in with EA1-MG-SP1, C-more Micro EA3 series 8in and 10in HMIs, C-more EA9 8in, 10in, 12in and 15in HMIs.	\$19.00
EA-6-COV2		Screen protector, non-glare, 6in. Package of 3. For use with C-more and C-more Micro 6in panels.	\$37.00
EA-8-COV2		Screen protector, non-glare, 8in. Package of 3. For use with C-more and C-more Micro 8in panels.	\$40.00
EA-10-COV2		Screen protector, non-glare, 10in. Package of 3. For use with C-more and C-more Micro 10in panels.	\$45.50

C-more Micro Programming Software

FREE software!

C-more Micro Programming Software can be downloaded at no charge or a CD version may be purchased by ordering EA-MG-PGMSW. The software requires a USB port or Ethernet connection* on your PC to connect to the **C-more** Micro panel. Software Help Files are included in the download. This software programs all the **C-more** Micro panels (does not program the **C-more** 6-inch through 15-inch touch panels).



Copyright © AutomationDirect.com. All rights reserved.



Note: This software is used to program C-more Micro panels only.



Note: The Ethernet port is built in to EA3-S3ML and EA3-T4CL. EA3-T6CL, EA3-T8CL and EA3-T10CL require the optional EA-ECOM module for Ethernet.

Part Number	Panel Software / Firmware Version Required
EA1-S3ML	1.0 or later
EA1-S3ML-N	
EA1-S3MLW	
EA1-S3MLW-N	1.5 or later
EA1-T4CL	
EA1-T6CL	3.0 or later
EA3-S3ML-RN	4.30 or later
EA3-S3ML-R	
EA3-S3ML	4.20 or later
EA3-T4CL	
EA3-T6CL	3.6 or later
EA3-T8CL	3.5 or later
EA3-T10CL	

C-more Micro Programming Software is a spin-off of its powerful sibling **C-more** Touch Panel. It offers very high end features designed to reduce your configuration time. Simply drag and drop the objects from the object list (right side of screen) onto the screen construction area. Then configure your PLC tags and click on the objects you wish to use. Use the built-in simulator to review your work on your PC before ever downloading your project! The time saving benefits of the **C-more** Micro configuration software could easily pay for the panel. Check out www.CmoreMicro.com to download a free version.

Built-in project simulator


- Runs your project on your PC
- Test all of your screens before downloading
- Time savings pays for the panel
- Simulate function keys and keypad bezel

Built-in user object/ screen libraries

Save time by re-using your custom objects and screens.

Thumbnail project preview pane

Helps keep track of multi-screen projects.



Scrolling object selection window

Lets you find the object you want fast. Just drag and drop it on the screen.

Scrolling help window

Gives you helpful information on each object

PC requirements

Following are the minimum system requirements for running **C-more** Micro Programming Software, EA-MG-PGMSW, on a PC:

- Operating System - Windows® XP Professional Edition Service Pack 2, Windows® 7 (32 or 64 bit), Windows 8 (32 or 64 bit) or Windows 10
- 150 MB free hard-disk space
- CD-ROM or DVD drive for installing software from the CD, or internet access to download free programming software
- USB port to use with the correct Programming Cable Assembly for project transfer from the programming software to the panel