

# Enclosure Subpanels



## Subpanels for Double-door Floor Mount Enclosures

- Subpanels are fabricated from 10 gauge carbon steel
- Painted steel subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized subpanels have a conductive finish (no paint)
- Subpanels are used in NEMA 12 double-door floor mount enclosures and some double-door wall mount enclosures




Enclosure Shipping Schedule	
Same day	1 - 7 days
Color indicates shipping lead time in business days.	

Subpanels for Double-door Floor Mount Enclosures					
Painted Steel	Price	Galvanized	Price	Nominal Enclosure Size HxW*	Subpanel Size AxB
<b>NPDD4242</b>	\$171.00	<b>NPDD4242G</b>	\$171.00	42 x 42	39.00 x 39.00 [991 x 991]
<b>NPDD4260</b>	\$251.00	<b>NPDD4260G</b>	\$251.00	42 x 60	38.00 x 56.00 [965 x 1422]
<b>NPDD4842</b>	\$194.00	<b>NPDD4842G</b>	\$194.00	48 x 42	45.00 x 39.00 [1143 x 991]
<b>NPDD4848</b>	\$232.00	<b>NPDD4848G</b>	\$232.00	48 x 48	44.00 x 44.00 [1118 x 1118]
<b>NPDD5442</b>	\$207.00	<b>NPDD5442G</b>	\$207.00	54 x 42	50.00 x 38.00 [1270 x 965]
<b>NPDD6048</b>	\$282.00	<b>NPDD6048G</b>	\$282.00	60 x 48	44.00 x 56.00 [1118 x 1422]
<b>NPDD6060</b>	\$348.00	<b>NPDD6060G</b>	\$348.00	60 x 60	56.00 x 56.00 [1422 x 1422]
<b>NPDD7260</b>	\$414.00	<b>NPDD7260G</b>	\$414.00	72 x 60	56.00 x 68.00 [1422 x 1727]
<b>NPDD7272</b>	\$495.00	—		72 x 72	68.00 x 68.00 [1727 x 1727]

**Notes: Dimensions in inches [millimeters].**  
 Letters in table correspond to letters on dimensional drawing.  
 \*Some floor mount enclosures may be up to 2 inches [51mm] taller than height listed in this table.  
 Disconnect enclosures will be up to 2 inches [51 mm] wider than width dimensions listed in this table.

## Dimensions

in [mm]



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.