

















Water Valve Accessories - Replacement Coils

Water Valve Accessory Coils									
Coil Photo	Part No.	Voltage Rating	Power Rating	Insulation	Connection	Cable Length	Fits Valve Series	Price	Weight (lbs)
	HS4YN02	120VAC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201 and NS301 valves	\$33.00	0.6
	HS4YN04	240VAC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201 and NS301 valves	\$33.00	0.6
	HS4YN24	24VAC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201 and NS301 valves	\$33.00	0.6
	HS4YN16	24VDC	10W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS201, NS211 DC and NS301 valves	\$33.00	0.6
	HS4GN02A24	120VAC	10W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS201 and NS301 valves	\$33.00	0.6
	HS4GN04A24	240VAC	10W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS201 and NS301 valves	\$33.00	0.6
	HS4GN24A24	24VAC	10W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS201 and NS301 valves	\$33.00	0.6
	HS4GN16A24	24VDC	10W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS201, NS211 DC and NS301 valves	\$33.00	0.6
	HS3YN02	120VAC	8W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS211 AC valves	\$27.00	0.5
	HS3YN04	240VAC	8W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS211 AC valves	\$27.00	0.5
	HS3YN24	24VAC	8W	Class N (200°C - 392°F)	18mm (DIN 43650A) style wiring plug	N/A	NS211 AC valves	\$27.00	0.5
	HS3GN02A24	120VAC	8W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS211 AC valves	\$27.00	0.5
	HS3GN04A24	240VAC	8W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS211 AC valves	\$27.00	0.5
	HS3GN24A24	24VAC	8W	Class N (200°C - 392°F)	1/2 in conduit	24.0 in	NS211 AC valves	\$27.00	0.5