

# Enclosure Accessories

## Floor Stand Kit



### Application



- Kit includes two mounting feet and hardware kit.
- Pre-punched mounting feet may be used as a template to drill holes on bottom of enclosure.
- Finished in ANSI 61 gray powder coat or #4 brushed stainless steel.

304 Stainless Steel Floor Stand Kits				
Part Number	Price	For Use with Enclosure Depth	Dimensions HxWxD	Drawing Link
<a href="#">1481FC8KSS</a>	\$510.00	8.00 [203]	12.00 x 6.00 x 8.00 [305 x 152 x 203]	<a href="#">PDF</a>
<a href="#">1481FC10KSS</a>	\$498.00	10.00 [254]	12.00 x 8.00 x 10.00 [305 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FC12KSS</a>	\$615.00	12.00 [305]	12.00 x 8.00 x 12.00 [305 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1481FC18KSS</a>	\$745.00	18.00 [457]	12.00 x 8.00 x 18.00 [305 x 203 x 457]	<a href="#">PDF</a>
<a href="#">1481FC20KSS</a>	\$835.00	20.00 [508]	12.00 x 10.00 x 20.00 [305 x 254 x 508]	<a href="#">PDF</a>
<a href="#">1481FC24KSS</a>	\$838.00	24.00 [610]	12.00 x 10.00 x 24.00 [305 x 254 x 610]	<a href="#">PDF</a>
<a href="#">1481FC16KSS</a>	\$652.00	16.00 [406]	12.00 x 10.00 x 16.00 [305 x 254 x 406]	<a href="#">PDF</a>
<a href="#">1481FK10KSS</a>	\$869.00	10.00 [254]	24.00 x 8.00 x 10.00 [610 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FK12KSS</a>	\$947.00	12.00 [305]	24.00 x 10.00 x 12.00 [610 x 254 x 305]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

Painted Steel Floor Stand Kits				
Part Number	Price	For Use with Enclosure Depth	Dimensions HxWxD	Drawing Link
<a href="#">1481FA8K</a>	\$175.00	8.00 [203]	6.00 x 6.00 x 8.00 [152 x 152 x 203]	<a href="#">PDF</a>
<a href="#">1481FA10K</a>	\$192.00	10.00 [254]	6.00 x 8.00 x 10.00 [152 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FA12K</a>	\$220.00	12.00 [305]	6.00 x 8.00 x 12.00 [152 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1481FA16K</a>	\$234.00	16.00 [406]	6.00 x 10.00 x 16.00 [152 x 254 x 406]	<a href="#">PDF</a>
<a href="#">1481FA18K</a>	\$259.00	18.00 [457]	6.00 x 8.00 x 18.00 [152 x 203 x 457]	<a href="#">PDF</a>
<a href="#">1481FA20K</a>	\$316.00	20.00 [508]	6.00 x 10.00 x 20.00 [152 x 254 x 508]	<a href="#">PDF</a>
<a href="#">1481FC6K</a>	\$210.00	6.00 [152]	12.00 x 5.00 x 6.00 [305 x 127 x 152]	<a href="#">PDF</a>
<a href="#">1481FC8K</a>	\$226.00	8.00 [203]	12.00 x 6.00 x 8.00 [305 x 152 x 203]	<a href="#">PDF</a>
<a href="#">1481FC10K</a>	\$243.00	10.00 [254]	12.00 x 8.00 x 10.00 [305 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FC12K</a>	\$259.00	12.00 [305]	12.00 x 8.00 x 12.00 [305 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1481FC16K</a>	\$293.00	16.00 [406]	12.00 x 10.00 x 16.00 [305 x 254 x 406]	<a href="#">PDF</a>
<a href="#">1481FC18K</a>	\$311.00	18.00 [457]	12.00 x 8.00 x 18.00 [305 x 203 x 457]	<a href="#">PDF</a>
<a href="#">1481FC20K</a>	\$326.00	20.00 [508]	12.00 x 10.00 x 20.00 [305 x 254 x 508]	<a href="#">PDF</a>
<a href="#">1481FC24K</a>	\$364.00	24.00 [610]	12.00 x 10.00 x 24.00 [305 x 254 x 610]	<a href="#">PDF</a>
<a href="#">1481FE6K</a>	\$222.00	6.00 [152]	15.00 x 5.00 x 6.00 [381 x 127 x 152]	<a href="#">PDF</a>
<a href="#">1481FE8K</a>	\$252.00	8.00 [203]	15.00 x 6.00 x 8.00 [381 x 152 x 203]	<a href="#">PDF</a>
<a href="#">1481FE10K</a>	\$269.00	10.00 [254]	15.00 x 8.00 x 10.00 [381 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FE12K</a>	\$286.00	12.00 [305]	15.00 x 8.00 x 12.00 [381 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1481FE16K</a>	\$320.00	16.00 [406]	15.00 x 10.00 x 16.00 [381 x 254 x 406]	<a href="#">PDF</a>
<a href="#">1481FE18K</a>	\$339.00	18.00 [457]	15.00 x 10.00 x 18.00 [381 x 254 x 457]	<a href="#">PDF</a>
<a href="#">1481FE24K</a>	\$380.00	24.00 [610]	15.00 x 10.00 x 24.00 [381 x 254 x 610]	<a href="#">PDF</a>
<a href="#">1481FG6K</a>	\$235.00	6.00 [152]	18.00 x 5.00 x 6.00 [457 x 127 x 152]	<a href="#">PDF</a>
<a href="#">1481FG8K</a>	\$276.00	8.00 [203]	18.00 x 8.00 x 8.00 [457 x 203 x 203]	<a href="#">PDF</a>
<a href="#">1481FG10K</a>	\$293.00	10.00 [254]	18.00 x 8.00 x 10.00 [457 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FG12K</a>	\$311.00	12.00 [305]	18.00 x 8.00 x 12.00 [457 x 203 x 305]	<a href="#">PDF</a>
<a href="#">1481FK10K</a>	\$344.00	10.00 [254]	24.00 x 8.00 x 10.00 [610 x 203 x 254]	<a href="#">PDF</a>
<a href="#">1481FK6K</a>	\$319.00	6.00 [152]	24.00 x 5.00 x 6.00 [610 x 127 x 152]	<a href="#">PDF</a>
<a href="#">1481FK8K</a>	\$326.00	8.00 [203]	24.00 x 8.00 x 8.00 [610 x 203 x 203]	<a href="#">PDF</a>
<a href="#">1481FG16K</a>	\$344.00	16.00 [406]	18.00 x 10.00 x 16.00 [457 x 254 x 406]	<a href="#">PDF</a>
<a href="#">1481FK12K</a>	\$360.00	12.00 [305]	24.00 x 10.00 x 12.00 [610 x 254 x 305]	<a href="#">PDF</a>
<a href="#">1481FK16K</a>	\$393.00	16.00 [406]	24.00 x 12.00 x 16.00 [610 x 305 x 406]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

