

# Universal Rack Shelf



## Features

- Constructed of 14- or 16-gauge steel.
- Universal design mounts to any standard EIA compliant rack or cabinet.
- Allows easy rack mounting of equipment or items that do not have rack mounting capabilities.
- Mounts to rack rails either as an internal shelf or external shelf/work area.
- Available in either vented or solid versions.
- Rugged textured black powder coat finish.



Solid Universal Rack Shelf					
Part Number	Price	Rack Units	Rack Width	Shelf Depth	Drawing Link
<a href="#">RASU190107DBK1</a>	\$44.00	1U	19.0 [483]	7.00 [178]	<a href="#">PDF</a>
<a href="#">RASU190107UBK1</a>	\$44.00	1U	19.0 [483]	7.00 [178]	<a href="#">PDF</a>
<a href="#">RASU190110BK1</a>	\$49.00	1U	19.0 [483]	10.00 [254]	<a href="#">PDF</a>
<a href="#">RASU190112BK1</a>	\$52.00	1U	19.0 [483]	12.00 [305]	<a href="#">PDF</a>
<a href="#">RASU190115BK1</a>	\$61.00	1U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASU190120BK1</a>	\$64.00	1U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASU190312BK1</a>	\$57.00	2U	19.0 [483]	12.00 [305]	<a href="#">PDF</a>
<a href="#">RASU190315BK1</a>	\$62.00	2U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASU190318BK1</a>	\$67.00	2U	19.0 [483]	18.00 [457]	<a href="#">PDF</a>
<a href="#">RASU190320BK1</a>	\$72.00	2U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASU190515BK1</a>	\$64.00	3U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASU230515BK1</a>	\$74.00	3U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASU190715BK1</a>	\$82.00	4U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASU190520BK1</a>	\$78.00	3U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASU190522BK1</a>	\$84.00	3U	19.0 [483]	22.00 [559]	<a href="#">PDF</a>
<a href="#">RASU190524BK1</a>	\$88.00	3U	19.0 [483]	24.00 [610]	<a href="#">PDF</a>
<a href="#">RASU190720BK1</a>	\$93.00	4U	23.0 [584]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASU230520BK1</a>	\$90.00	3U	23.0 [584]	20.00 [508]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

Vented Universal Rack Shelf					
Part Number	Price	Rack Units	Rack Width	Shelf Depth	Drawing Link
<a href="#">RASV190107DBK1</a>	\$50.00	1U	19.0 [483]	7.00 [178]	<a href="#">PDF</a>
<a href="#">RASV190107UBK1</a>	\$50.00	1U	19.0 [483]	7.00 [178]	<a href="#">PDF</a>
<a href="#">RASV190110BK1</a>	\$57.00	1U	19.0 [483]	10.00 [254]	<a href="#">PDF</a>
<a href="#">RASV190112BK1</a>	\$61.00	1U	19.0 [483]	12.00 [305]	<a href="#">PDF</a>
<a href="#">RASV190115BK1</a>	\$64.00	1U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASV190120BK1</a>	\$67.00	1U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASV190312BK1</a>	\$66.00	2U	19.0 [483]	12.00 [305]	<a href="#">PDF</a>
<a href="#">RASV190315BK1</a>	\$70.00	2U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASV190318BK1</a>	\$72.00	2U	19.0 [483]	18.00 [457]	<a href="#">PDF</a>
<a href="#">RASV190320BK1</a>	\$74.00	2U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASV190515BK1</a>	\$67.00	3U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASV190520BK1</a>	\$74.00	3U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASV190715BK1</a>	\$74.00	4U	19.0 [483]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASV190720BK1</a>	\$77.00	4U	19.0 [483]	20.00 [508]	<a href="#">PDF</a>
<a href="#">RASV230515BK1</a>	\$90.00	3U	23.0 [584]	15.00 [381]	<a href="#">PDF</a>
<a href="#">RASV230520BK1</a>	\$99.00	3U	23.0 [584]	20.00 [508]	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].