


IP69K Sanitary Single Door



Features

Hammond HYW sanitary Type 4X wallmount enclosures house electrical and electronic controls in harsh washdown environments. They are designed for facilities where equipment must be cleaned frequently and thoroughly.

- Top sloped 25° to shed water and washdown fluids
- Door-edge mounted silicone gasket in hygienic blue is easily removed and re-installed for cleaning
- 316 stainless steel hygienic quarter-turn latches require the included tool to open
- Internal removable hinges allow 105° door opening and reverse door swing
- Internal alignment guide limits door sag
- Replacement sanitary gaskets available (see table)



Construction

- Formed, smooth 304 stainless steel with #4 dairy finish
- Continuously welded seams ground smooth
- Door stiffeners provided where required
- Bonding stud provided on door and grounding stud installed in enclosure
- Collar studs and hardware kit provided for mounting optional subpanel (sold separately)
- No pre-drilled wall-mounting holes — use 316 stainless steel stand-off mounting kits [ST1MFSS316](#), [ST2MFSS316](#), [ST4MFSS316](#), or [ST6MFSS316](#) to maintain the marked Type rating, or weld in place

Listings

- cUL Type 3R, 4, 4X, and 12 [File E65324]
- NSF/ANSI 169 (not all accessories maintain NSF)
- Complies with:
 - NEMA Type 3R, 4, 4X, and 12
 - IEC 60529, IP66, IP69, IP69K



IP69K Sanitary Single Door

Part Number	Price	Nominal Enclosure Size H x W x D (in)	Optional Subpanel	Price	Replacement Gasket	Price	Drawing Link
HYW16168SS	\$1,700.00	16 x 16 x 8	18P1313	\$45.50	HYG1616	\$254.00	PDF
HYW20168SS	\$1,880.00	20 x 16 x 8	18P1713	\$54.00	HYG2016	\$281.00	PDF
HYW20208SS	\$2,147.00	20 x 20 x 8	18P1717	\$64.00	HYG2020	\$288.00	PDF
HYW202010SS	\$2,213.00	20 x 20 x 10	18P1717	\$64.00	HYG2020	\$288.00	PDF
HYW24208SS	\$2,279.00	24 x 20 x 8	18P2117	\$83.00	HYG2420	\$292.00	PDF
HYW242010SS	\$2,530.00	24 x 20 x 10	18P2117	\$83.00	HYG2420	\$292.00	PDF
HYW242012SS	\$2,723.00	24 x 20 x 12	18P2117	\$83.00	HYG2420	\$292.00	PDF
HYW24248SS	\$2,503.00	24 x 24 x 8	18P2121	\$97.00	HYG2424	\$298.00	PDF
HYW242410SS	\$2,636.00	24 x 24 x 10	18P2121	\$97.00	HYG2424	\$298.00	PDF
HYW242412SS	\$2,843.00	24 x 24 x 12	18P2121	\$97.00	HYG2424	\$298.00	PDF
HYW30248SS	\$2,583.00	30 x 24 x 8	18P2721	\$118.00	HYG3024	\$309.00	PDF
HYW302412SS	\$3,226.00	30 x 24 x 12	18P2721	\$118.00	HYG3024	\$309.00	PDF
HYW363012SS	\$4,107.00	36 x 30 x 12	18P3327	\$188.00	HYG3630	\$325.00	PDF
HYW363016SS	\$4,572.00	36 x 30 x 16	18P3327	\$188.00	HYG3630	\$325.00	PDF
HYW423612SS	\$4,718.00	42 x 36 x 12	18P3933	\$251.00	HYG4236	\$396.00	PDF
HYW423616SS	\$5,563.00	42 x 36 x 16	18P3933	\$251.00	HYG4236	\$396.00	PDF
HYW483612SS	\$5,892.00	48 x 36 x 12	18P4533	\$284.00	HYG4836	\$355.00	PDF
HYW483616SS	\$6,218.00	48 x 36 x 16	18P4533	\$284.00	HYG4836	\$355.00	PDF