

# NEMA 4 and 4X Operator Console Plinths



## Application

- Features removable front and rear panels for easy access to bottom for cabling or transport by forklift.
- For cable access, features 3 double knockouts on each end.
- Available in 4in and 8in heights.
- Available in 24in, 36in, 48in, and 60in widths.
- Maintains NEMA rating of system.
- Formed 14 gauge steel.
- Also offered with formed 14 gauge stainless steel.
- Available in light gray and stainless steel.



NEMA 4 and 4X Operator Console Plinths							
Carbon Steel	Price	Stainless Steel	Price	Size	Fits Consoles		Drawink Link
<a href="#"><u>2CLP42418</u></a>	\$447.00	<a href="#"><u>2CSP42418</u></a>	\$662.00	4.00 x 24.00 x 18.00 [102 x 610 x 457]	2CLC2024	2CSC2024	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP43618</u></a>	\$485.00	<a href="#"><u>2CSP43618</u></a>	\$717.00	4.00 x 36.00 x 18.00 [102 x 914 x 457]	2CLC2036	2CSC2036	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP44818</u></a>	\$597.00	<a href="#"><u>2CSP44818</u></a>	\$882.00	4.00 x 48.00 x 18.00 [102 x 1219 x 457]	2CLC2048	2CSC2048	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP46018</u></a>	\$709.00	<a href="#"><u>2CSP46018</u></a>	\$1,048.00	4.00 x 60.00 x 18.00 [102 x 1524 x 457]	2CLC2060	2CSC2060	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP82418</u></a>	\$746.00	<a href="#"><u>2CSP82418</u></a>	\$1,103.00	8.00 x 24.00 x 18.00 [203 x 610 x 457]	2CLC2024	2CSC2024	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP83618</u></a>	\$858.00	<a href="#"><u>2CSP83618</u></a>	\$1,268.00	8.00 x 36.00 x 18.00 [203 x 914 x 457]	2CLC2036	2CSC2036	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP84818</u></a>	\$1,007.00	<a href="#"><u>2CSP84818</u></a>	\$1,489.00	8.00 x 48.00 x 18.00 [203 x 1219 x 457]	2CLC2048	2CSC2048	<a href="#"><u>PDF</u></a>
<a href="#"><u>2CLP86018</u></a>	\$1,156.00	<a href="#"><u>2CSP86018</u></a>	\$1,709.00	8.00 x 60.00 x 18.00 [203 x 1524 x 457]	2CLC2060	2CSC2060	<a href="#"><u>PDF</u></a>