

# NEMA 4 and 4X Stainless Steel Pushbutton Wall Mount



## Applications

- Designed to accept standard heavy duty oil-tight pushbuttons, switches and pilot lights.
- Provides protection from dirt, dust, oil and large amounts of water from any angle, or where highly corrosive conditions exist.

## Construction

- Smooth continuously welded seams.
- Welded brackets provide for enclosure mounting.
- Captive stainless steel cover screws thread into sealed wells.
- Larger enclosures provide internally hinged removable covers, designed to hold the cover open during wiring.
- Oil-resistant gasket and adhesive.
- A bonding stud is provided on the door, and a grounding stud is provided on the enclosure.

## Listings

- UL 508A Type 4 and 4X [UL File E65324]
- CSA Type 4 and 4X [CSA File R21001]
- Complies with
  - NEMA Type 3R, 4 and 4X
  - IEC 60529, IP66
- All appropriate components are required to maintain these standards.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	



## Finish

- Natural stainless steel with a #4 smooth brushed finish.





NEMA 4 and 4X Stainless Steel Pushbutton Wall Mount											
304 Stainless Steel				316 Stainless Steel				Size HxWxD	# Holes	Steel Gauge	Hinged
22mm	Price	30mm	Price	22mm	Price	30mm	Price				
<b>1435MSSA</b>	\$124.00	<b>1435SSA</b>	\$122.00	<b>1435MS16A</b>	\$156.00	<b>1435S16A</b>	\$154.00	3.81 x 3.56 x 2.91 [97 x 90 x 74]	1	16	No
<b>1435MSSB</b>	\$146.00	<b>1435SSB</b>	\$143.00	<b>1435MS16B</b>	\$184.00	<b>1435S16B</b>	\$182.00	6.06 x 3.56 x 2.91 [154 x 90 x 74]	2		
<b>1435MSSC</b>	\$169.00	<b>1435SSC</b>	\$166.00	<b>1435MS16C</b>	\$213.00	<b>1435S16C</b>	\$210.00	8.31 x 3.56 x 2.92 [211 x 90 x 74]	3		
<b>1435MSSD</b>	\$191.00	<b>1435SSD</b>	\$193.00	<b>1435MS16D</b>	\$241.00	<b>1435S16D</b>	\$238.00	10.56 x 3.56 x 2.92 [268 x 90 x 74]	4		
<b>1435MSSH</b>	\$256.00	<b>1435SSH</b>	\$254.00	<b>1435MS16H</b>	\$318.00	<b>1435S16H</b>	\$314.00	9.81 x 6.56 x 3.22 [249 x 167 x 82]	6	14	Yes
<b>1435MSSK</b>	\$304.00	<b>1435SSK</b>	\$300.00	<b>1435MS16K</b>	\$378.00	<b>1435S16K</b>	\$372.00	9.81 x 8.81 x 3.22 [249 x 224 x 82]	9		
<b>1435MSSO</b>	\$347.00	<b>1435SSO</b>	\$345.00	<b>1435MS16O</b>	\$432.00	<b>1435S16O</b>	\$426.00	12.06 x 8.81 x 3.22 [306 x 224 x 82]	12		

Note: Dimensions in inches [millimeters]

# NEMA 4 and 4X Stainless Steel Pushbutton Wall Mount



## Dimensions



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.