

# Enclosure Subpanels


1418, 1422, 1447, C3RxxxxHCR, HWxxxHK,  
and HN4WM Wall-Mount Enclosures



## Construction

- Steel panels are 12-gauge steel and are finished in RAL9003 white powder coat.
- Galvanized panels are 12-gauge unpainted galvanized steel.
- Stainless steel panels are 12-gauge and are brushed #4 316 SS.
- Aluminum panels are 5052-H32 aluminum alloy.
- Larger panels have two or four formed flanges.
- Some larger panels are 10-gauge.
- Panel mounting hardware not included (provided with enclosure).

## Dimensions



# Enclosure Subpanels

1418, 1422, 1447, C3RxxxxHCR, HWxxxHK, and HN4WM Wall-Mount Enclosures




Subpanels - 1418, 1422, 1447, C3RxxxxHCR, HWxxxHK, and HN4WM Wall-Mount Enclosures										
Painted	Price	Galv.	Price	Aluminum	Price	Stainless	Price	Dimensions HxW	For Use With	Drawing Link
<a href="#">18P1309</a>	\$32.50	<a href="#">18G1309</a>	\$32.50	<a href="#">18A1309</a>	\$47.50	<a href="#">18P1309S16</a>	\$94.00	13.00 x 9.00 [330 x 229]	16x12 (HxW) 1418xxxx and C3R16126HCR	<a href="#">PDF</a>
<a href="#">18P1313</a>	\$40.00	<a href="#">18G1313</a>	\$40.00	<a href="#">18A1313</a>	\$59.00	<a href="#">18P1313S16</a>	\$116.00	13.00 x 13.00 [330 x 330]	16x16 (HxW) 1418xxxx and C3R16166HCR	<a href="#">PDF</a>
<a href="#">18P1515</a>	\$44.00	<a href="#">18G1515</a>	\$44.00	—	—	—	—	15.00 x 15.00 [381 x 381]	18x18 (HxW) C3R1818xxHCR	<a href="#">PDF</a>
<a href="#">18P1709</a>	\$38.00	<a href="#">18G1709</a>	\$38.00	—	—	—	—	17.00 x 9.00 [432 x 229]	20x12 (HxW) 1418CA6 & 1418CA8	<a href="#">PDF</a>
<a href="#">18P1713</a>	\$48.00	<a href="#">18G1713</a>	\$48.00	—	—	<a href="#">18P1713S16</a>	\$138.00	17.00 x 13.00 [432 x 330]	20x16 (HxW) 1418xxxx and C3R20166HCR	<a href="#">PDF</a>
<a href="#">18P1717</a>	\$58.00	<a href="#">18G1717</a>	\$58.00	<a href="#">18A1717</a>	\$86.00	<a href="#">18P1717S16</a>	\$177.00	17.00 x 17.00 [432 x 432]	20x20 (HxW) 1418xxxx, 1447SAxxHK and C3R20208HCR	<a href="#">PDF</a>
<a href="#">18P2109</a>	\$48.00	<a href="#">18G2109</a>	\$48.00	—	—	—	—	21.00 x 9.00 [533 x 229]	24x12 (HxW) 1418xxxx	<a href="#">PDF</a>
<a href="#">18P2113</a>	\$55.00	<a href="#">18G2113</a>	\$55.00	—	—	<a href="#">18P2113S16</a>	\$171.00	21.00 x 13.00 [533 x 330]	24x16 (HxW) 1418xxxx and HW24168xxHK	<a href="#">PDF</a>
<a href="#">18P2117</a>	\$75.00	<a href="#">18G2117</a>	\$75.00	<a href="#">18A2117</a>	\$144.00	<a href="#">18P2117S16</a>	\$215.00	21.00 x 17.00 [533 x 432]	24x20 (HxW) 1418xxxx, 1447SBxxHK, C3R24208HCR and HW2420xxxxHK	<a href="#">PDF</a>
<a href="#">18P2121</a>	\$86.00	<a href="#">18G2121</a>	\$86.00	<a href="#">18A2121</a>	\$167.00	<a href="#">18P2121S16</a>	\$250.00	21.00 x 21.00 [533 x 533]	24x24 (HxW) 1418xxxx, 1447SCxxHK, C3R2424xxHCR and HW2424xxxxHK	<a href="#">PDF</a>
<a href="#">18P2709</a>	\$69.00	<a href="#">18G2709</a>	\$69.00	—	—	—	—	27.00 x 9.00 [686 x 229]	30x12 (HxW) 1418KA8	<a href="#">PDF</a>
<a href="#">18P2713</a>	\$74.00	<a href="#">18G2713</a>	\$74.00	—	—	—	—	27.00 x 13.00 [686 x 330]	30x16 (HxW) 1418FG6 & 1418KG8	<a href="#">PDF</a>
<a href="#">18P2717</a>	\$91.00	<a href="#">18G2717</a>	\$91.00	—	—	<a href="#">18P2717S16</a>	\$265.00	27.00 x 17.00 [686 x 432]	30x20 (HxW) 1418xxxx, 1447SDxxHK and HW30208xxHK	<a href="#">PDF</a>
<a href="#">18P2721</a>	\$105.00	<a href="#">18G2721</a>	\$105.00	<a href="#">18A2721</a>	\$199.00	<a href="#">18P2721S16</a>	\$302.00	27.00 x 21.00 [686 x 533]	24x30/30x24 (HxW) 1418xxxx, 1447Sxxxx, C3R3024xxHCR and HWxxxxxxHK	<a href="#">PDF</a>
<a href="#">18P2727</a>	\$148.00	<a href="#">18G2727</a>	\$148.00	—	—	<a href="#">18P2727S16</a>	\$396.00	27.00 x 27.00 [686 x 686]	30x30 (HxW) 1418xxxx, C3R3030xxHCR and HW30308xxHK	<a href="#">PDF</a>
<a href="#">18P3321</a>	\$126.00	<a href="#">18G3321</a>	\$126.00	<a href="#">18A3321</a>	\$234.00	<a href="#">18P3321S16</a>	\$381.00	33.00 x 21.00 [838 x 533]	36x24 (HxW) 1418xxxx, 1447Sxxxx, C3R362412HCR and HW3624xxxxHK	<a href="#">PDF</a>
<a href="#">18P3327</a>	\$168.00	<a href="#">18G3327</a>	\$168.00	<a href="#">18A3327</a>	\$287.00	<a href="#">18P3327S16</a>	\$470.00	33.00 x 27.00 [838 x 686]	36x30 (HxW) 1418xxxx, 1447Sxxxx, C3R363012HCR and HW3630xxxxHK	<a href="#">PDF</a>
<a href="#">18P3333</a>	\$197.00	<a href="#">18G3333</a>	\$197.00	—	—	<a href="#">18P3333S16</a>	\$568.00	33.00 x 33.00 [838 x 838]	36x36 (HxW) 1418xxxx, C3R3636xxHCR and HW363612xxHK	<a href="#">PDF</a>
<a href="#">18P3921</a>	\$152.00	<a href="#">18G3921</a>	\$152.00	—	—	—	—	39.00 x 21.00 [991 x 533]	24x42/42x24 (HxW) 1418N8, 1422Pxx and HN4WM24428xx	<a href="#">PDF</a>
<a href="#">18P3927</a>	\$192.00	<a href="#">18G3927</a>	\$192.00	—	—	<a href="#">18P3927S16</a>	\$554.00	39.00 x 27.00 [991 x 686]	30x42/42x30 (HxW) 1418xxxx, 1422R10, 1447Sxxxx, C3R423012HCR, HW423010xxHK and HN4WM304210xx	<a href="#">PDF</a>
<a href="#">18P3933</a>	\$225.00	<a href="#">18G3933</a>	\$225.00	—	—	<a href="#">18P3933S16</a>	\$663.00	39.00 x 33.00 [991 x 838]	36x42/42x36 (HxW) 1418xxxx, 1422UV12, 1447Sxxxx, C3R423612HCR, HW423610xxHK and HN4WM364210xx	<a href="#">PDF</a>
<a href="#">18P4521</a>	\$174.00	<a href="#">18G4521</a>	\$174.00	—	—	—	—	45.00 x 21.00 [1143 x 533]	24x48/48x24 (HxW) 1418Q8, 1422PW8, 1447SQ10HK and HN4WM24488xx	<a href="#">PDF</a>
<a href="#">18P4527</a>	\$215.00	<a href="#">18G4527</a>	\$215.00	—	—	—	—	45.00 x 27.00 [1143 x 686]	30x48/48x30 (HxW) 1418xxxx, 1422RW10 and HN4WM304810xx	<a href="#">PDF</a>
<a href="#">18P4533</a>	\$253.00	<a href="#">18G4533</a>	\$253.00	<a href="#">18A4533</a>	\$447.00	<a href="#">18P4533S16</a>	\$717.00	45.00 x 33.00 [1143 x 838]	36x48/48x36 (HxW) 1418xxxx, 1422UW12, 1447Sxxxx, C3R4836xxHCR, HW4836xxxxHK and HN4WM364812xx	<a href="#">PDF</a>
<a href="#">18P5733</a>	\$312.00	<a href="#">18G5733</a>	\$262.00	<a href="#">18A5733</a>	\$554.00	<a href="#">18P5733S16</a>	\$947.00	57.00 x 33.00 [1448 x 838]	36x60/60x36 (HxW) 1418xxxx, 1422UX12, 1447Sxxxx, C3R603612HCR, HW6036xxxxHK and HN4WM366012xx	<a href="#">PDF</a>
<a href="#">18P6927</a>	\$329.00	<a href="#">18G6927</a>	\$329.00	—	—	—	—	69.00 x 27.00 [1753 x 686]	72x30 (HxW) 1418Uxx	<a href="#">PDF</a>
<a href="#">18P6933</a>	\$367.00	<a href="#">18G6933</a>	\$367.00	—	—	—	—	69.00 x 33.00 [1753 x 838]	72x36 (HxW) 1418V12	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# Perforated Subpanels

## 1418, 1447, C3RxxxHCR and HWxxxHK Wall-Mount Enclosures



### Construction

- For use with 1418, 1447, C3RxxxHCR and HWxxxHK wall-mount enclosures.
- Made from 16-gauge steel.
- Accepts self-tapping screws eliminating timely measurement, marking and drilling of component mounting holes.
- 0.25in [6.35mm] diameter holes on 0.25in [6.4mm] staggered centers.
- ANSI 61 gray powder finish.

Subpanels for 1418, 1447, C3RxxxHCR and HWxxxHK Wall-Mount Enclosures				
Part Number	Price	Dimensions HxW	For Use With	Drawing Link
<a href="#">18P1309PP</a>	\$31.00	13.00 x 9.00 [330 x 229]	16x12 (HxW) 1418xxxx and C3R16126HCR	<a href="#">PDF</a>
<a href="#">18P1313PP</a>	\$38.00	13.00 x 13.00 [330 x 330]	16x16 (HxW) 1418xxxx and C3R16166HCR	<a href="#">PDF</a>
<a href="#">18P1515PP</a>	\$41.50	15.00 x 15.00 [381 x 381]	18x18 (HxW) C3R1818xxHCR	<a href="#">PDF</a>
<a href="#">18P1713PP</a>	\$45.00	17.00 x 13.00 [432 x 330]	20x16 (HxW) 1418xxxx and C3R20166HCR	<a href="#">PDF</a>
<a href="#">18P1717PP</a>	\$54.00	17.00 x 17.00 [432 x 432]	20x20 (HxW) 1418xxxx, 1447SAxxHK and C3R20208HCR	<a href="#">PDF</a>
<a href="#">18P2117PP</a>	\$71.00	21.00 x 17.00 [533 x 432]	24x20 (HxW) 1418xxxx, 1447SBxxHK, C3R24208HCR and HW2420xxxxHK	<a href="#">PDF</a>
<a href="#">18P2121PP</a>	\$81.00	21.00 x 21.00 [533 x 533]	24x24 (HxW) 1418xxxx, 1447SCxxHK, C3R2424xxHCR and HW2424xxxxHK	<a href="#">PDF</a>
<a href="#">18P2721PP</a>	\$98.00	27.00 x 21.00 [686 x 533]	24x30/30x24 (HxW) 1418xxxx, 1447Sxxxx, C3R3024xxHCR and HWxxxxxxHK	<a href="#">PDF</a>
<a href="#">18P2727PP</a>	\$139.00	27.00 x 27.00 [686 x 686]	30x30 (HxW) 1418xxxx, C3R3030xxHCR and HW30308xxHK	<a href="#">PDF</a>
<a href="#">18P3321PP</a>	\$119.00	33.00 x 21.00 [838 x 533]	36x24 (HxW) 1418xxxx, 1447Sxxxx, C3R362412HCR and HW3624xxxxHK	<a href="#">PDF</a>
<a href="#">18P3327PP</a>	\$157.00	33.00 x 27.00 [838 x 686]	36x30 (HxW) 1418xxxx, 1447Sxxxx, C3R363012HCR and HW3630xxxxHK	<a href="#">PDF</a>
<a href="#">18P3333PP</a>	\$185.00	33.00 x 33.00 [838 x 838]	36x36 (HxW) 1418xxxx, C3R3636xxHCR and HW363612xxHK	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

### Dimensions

