

# Enclosure Subpanels

## 1418FS and HN4FS Freestanding Enclosures



### Construction

- Formed from 10-gauge or 12-gauge steel.
- All-double door width panels are 10-gauge steel.
- Width panels are available in full or half height.
- Side-mount panels are available in full height only.
- Includes all mounting hardware and center support where required.
- Half panel can be mounted in the top or bottom half of the enclosure.
- Steel subpanels finished in RAL9003 white powder coat.

### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### Side Mount Panels

Part Number	Price	Dimensions HxW	For Use With	Drawing Link
60FD14	\$214.00	48.00 x 14.00 [1219 x 356]	60in (H) 1418xxxx and HN4FS60xxxx	<a href="#">PDF</a>
72FD9	\$224.00	60.00 x 9.00 [1524 x 229]	72in (H) 1418xxxx and HN4FS72xxxx	<a href="#">PDF</a>
72FD14	\$243.00	60.00 x 14.00 [1524 x 356]	72in (H) x min. 18in (D) 1418xxxx and HN4FS72xxxx	<a href="#">PDF</a>
72FD20	\$297.00	60.00 x 20.00 [1524 x 508]	72in (H) x min. 24in (D) 1418xxxx and HN4FS72xxxx	<a href="#">PDF</a>
90FD9	\$330.00	78.00 x 9.00 [1981 x 229]	90in (H) 1418xxxx and HN4FS90xxxx	<a href="#">PDF</a>
90FD14	\$349.00	78.00 x 14.00 [1981 x 356]	90in (H) x min. 18in (D) 1418xxxx and HN4FS90xxxx	<a href="#">PDF</a>
90FD20	\$362.00	78.00 x 20.00 [1981 x 508]	90in (H) x min. 24in (D) 1418xxxx and HN4FS90xxxx	<a href="#">PDF</a>
72FD26	\$458.00	60.00 x 26.00 [1524 x 660]	72in (H) x 36in (D) 1418xxx36 and HN4FS72xx36xx	<a href="#">PDF</a>
90FD26	\$532.00	78.00 x 26.00 [1981 x 660]	90in (H) x 36in (D) 1418xxx36 and HN4FS90xx36xx	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

### Single-Door Subpanels

Painted	Price	Galvanized	Price	Type	Dimensions HxW	For Use With	Drawing Link
60TWFW	\$352.00	60TWFWG	\$369.00	Full Panel	48.00 x 20.00 [1219 x 508]	60x24 1418TW18 and HN4FS602418xx	<a href="#">PDF</a>
72WFW	\$393.00	72WFWG	\$414.00		60.00 x 20.00 [1524 x 508]	72x24/72x25 1418xxxx and HN4FS72xxxxxx	<a href="#">PDF</a>
90YFW	\$458.00	90YFWG	\$478.00		78.00 x 20.00 [1981 x 508]	90x24 1418YW20 and HN4FS902420xx	<a href="#">PDF</a>
72XFW	\$458.00	72XFWG	\$478.00		60.00 x 26.00 [1524 x 660]	72x30/72x31 1418xxxx and HN4FS72xxxxxx	<a href="#">PDF</a>
60TYFW	\$451.00	60TYFWG	\$475.00		48.00 x 32.00 [1219 x 813]	60x36 1418TY24 and HN4FS603624SS	<a href="#">PDF</a>
72YFW	\$521.00	72YFWG	\$546.00		60.00 x 32.00 [1524 x 813]	72x36/72x37 1418xxxx and HN4FS72xxxxxx	<a href="#">PDF</a>
90YFW	\$621.00	90YFWG	\$651.00		78.00 x 32.00 [1981 x 813]	90x36 1418YYxx and HN4FS9036xxxx	<a href="#">PDF</a>
60TWHW	\$236.00	60TWHWG	\$246.00		Half Panel	24.87 x 20.00 [632 x 508]	60x24 1418TW18 and HN4FS602418xx
72WHW	\$255.00	72WHWG	\$267.00	30.87 x 20.00 [784 x 508]		72x24/72x25 1418xxxx and HN4FS72xxxxxx	<a href="#">PDF</a>
90YWHW	\$286.00	90YWHWG	\$300.00	39.87 x 20.00 [1013 x 508]		90x24 1418YW20 and HN4FS902420xx	<a href="#">PDF</a>
72XHW	\$286.00	72XHWG	\$300.00	30.87 x 26.00 [784 x 660]		72x30/72x31 1418xxxx and HN4FS72xxxxxx	<a href="#">PDF</a>
60TYHW	\$286.00	60TYHWG	\$300.00	24.87 x 32.00 [632 x 813]		60x36 1418TY24 and HN4FS603624SS	<a href="#">PDF</a>
72YHW	\$319.00	72YHWG	\$335.00	30.87 x 32.00 [784 x 813]		72x36/72x37 1418xxxx and HN4FS72xxxxxx	<a href="#">PDF</a>
90YHW	\$370.00	90YHWG	\$388.00	39.87 x 32.00 [1013 x 813]		90x36 1418YYxx and HN4FS9036xxxx	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# Enclosure Subpanels

## 1418FS and HN4FS Freestanding Enclosures



### Shipping Schedule

Same day	1 - 15 days
Color indicates shipping lead time in business days.	

### Two-Door Subpanels

Painted	Price	Galvanized	Price	Type	Dimensions HxW	For Use With	Drawing Link
<b>60AWFW</b>	\$723.00	<b>60AWFWG</b>	\$760.00	Full Height	48.00 x 44.00 [1219 x 1118]	60x48 1418AW18	<a href="#">PDF</a>
<b>72ZFWF</b>	\$819.00	<b>72ZFWFG</b>	\$858.00		60.00 x 44.00 [1524 x 1118]	72x48 1418ZWxx	<a href="#">PDF</a>
<b>72ZXFV</b>	\$951.00	<b>72ZXFVG</b>	\$998.00		60.00 x 56.00 [1524 x 1422]	72x60 1418ZXxx	<a href="#">PDF</a>
<b>72ZYFV</b>	\$1,079.00	<b>72ZYFVG</b>	\$1,188.00		60.00 x 68.00 [1524 x 1727]	72x72 1418ZYxx	<a href="#">PDF</a>
<b>90BFWF</b>	\$963.00	<b>90BFWFG</b>	\$1,011.00		78.00 x 44.00 [1981 x 1118]	90x48 1418BW20	<a href="#">PDF</a>
<b>90BYFV</b>	\$1,301.00	<b>90BYFVG</b>	\$1,433.00		78.00 x 68.00 [1981 x 1727]	90x72 1418BYxx	<a href="#">PDF</a>
<b>60AHHW</b>	\$451.00	<b>60AHHWG</b>	\$509.00	Half Height	24.87 x 44.00 [632 x 1118]	60x48 1418AW18	<a href="#">PDF</a>
<b>72ZHHW</b>	\$526.00	<b>72ZHHWG</b>	\$549.00		30.87 x 44.00 [784 x 1118]	72x48 1418ZWxx	<a href="#">PDF</a>
<b>72ZXHV</b>	\$590.00	<b>72ZXHVG</b>	\$619.00		30.87 x 56.00 [784 x 1422]	72x60 1418ZXxx	<a href="#">PDF</a>
<b>72ZYHV</b>	\$658.00	<b>72ZYHVG</b>	\$691.00		30.87 x 68.00 [784 x 1727]	72x72 1418ZYxx	<a href="#">PDF</a>
<b>90BHHW</b>	\$596.00	<b>90BHHWG</b>	\$626.00		39.87 x 44.00 [1013 x 1118]	90x48 1418BW20	<a href="#">PDF</a>
<b>90BYHV</b>	\$766.00	<b>90BYHVG</b>	\$806.00		39.87 x 68.00 [1013 x 1727]	90x72 1418BYxx	<a href="#">PDF</a>

Note: Dimensions in inches [millimeters].

# Freestanding Enclosure 19 in Swing-Out Frame



## 1418FS and HN4FS Enclosures



### Construction

- Formed from 10-gauge steel, frames are drilled and tapped to EIA requirements for mounting standard 19 in [483 mm] rack accessories.
- Designed for installation in 72 in [1829 mm] and 90 in [2286 mm] high enclosures. The swing frame pivots on 0.5 in [12.7 mm] pins within the enclosure for easy access to the rear of rack mounted equipment.
- The frame positions at any depth within the enclosure and is fastened in the closed position with 1/4-turn fasteners.
- Swing frames may be mounted in 30 in [762 mm] and 36 in [914 mm] wide enclosures, or in 60 in [1524 mm] and 72 in [1829 mm] wide enclosures with an optional center panel support.
- One or two frames may be mounted in 30 in [762 mm] and 36 in [914 mm] wide enclosures with dual access, and 1, 2, 3 or 4 frames may be mounted in 60 in [1524 mm] and 72 in [1829 mm] wide dual access enclosures.
- Finished in black powder coat.

### Shipping Schedule

Same day	1 - 15 days
----------	-------------

Color indicates shipping lead time in business days.

### Freestanding Enclosure 19 in [483 mm] Swing-Out Frame

Part Number	Price	For Use With	Rack Units	Drawing Link
1418SFYY	\$957.00	90x36in	44	<a href="#">PDF</a>
1418SFY	\$907.00	72x36in	33	<a href="#">PDF</a>
1418SFX	\$841.00	72x30in	33	<a href="#">PDF</a>

### Dimensions

