

# Enclosure Subpanels

## 1418FS and HN4FS Freestanding Enclosures



### Construction

- Formed from 10 gauge or 12 gauge steel.
- All-double door width panels are 10 gauge steel.
- Width panels are available in full or half height.
- Side-mount panels are available in full height only.
- Includes all mounting hardware and center support where required.
- Half panel can be mounted in the top or bottom half of the enclosure.
- Steel subpanels finished in RAL 9003 white powder coat.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Side Mount Panels			
Part Number	Price	Dimensions HxW	For Use With
<b>60FD14</b>	\$166.00	48.00 x 14.00 [1219 x 356]	60in (H) 1418xxxx and HN4FS60xxxx
<b>72FD9</b>	\$174.00	60.00 x 9.00 [1524 x 229]	72in (H) 1418xxxx and HN4FS72xxxx
<b>72FD14</b>	\$188.00	60.00 x 14.00 [1524 x 356]	72in (H) x min. 18in (D) 1418xxxx and HN4FS72xxxx
<b>72FD20</b>	\$231.00	60.00 x 20.00 [1524 x 508]	72in (H) x min. 24in (D) 1418xxxx and HN4FS72xxxx
<b>72FD26</b>	\$357.00	60.00 x 26.00 [1524 x 660]	72in (H) x 36in (D) 1418xxx36 and HN4FS72xx36xx
<b>90FD9</b>	\$257.00	78.00 x 9.00 [1981 x 229]	90in (H) 1418xxxx and HN4FS90xxxx
<b>90FD14</b>	\$270.00	78.00 x 14.00 [1981 x 356]	90in (H) 1418xxxx and HN4FS90xxxx
<b>90FD20</b>	\$281.00	78.00 x 20.00 [1981 x 508]	90in (H) x min. 24in (D) 1418xxxx and HN4FS90xxxx
<b>90FD26</b>	\$414.00	78.00 x 26.00 [1981 x 660]	90in (H) x 36in (D) 1418xxx36 and HN4FS90xx36xx

*Note: Dimensions in inches [millimeters].*

Single-Door Subpanels						
Painted	Price	Galvanized	Price	Type	Dimensions HxW	For Use With
<b>60TWF</b>	\$272.00	<b>60TWF</b>	\$285.00	Full Panel	48.00 x 20.00 [1219 x 508]	60x24 1418TW18 and HN4FS602418xx
<b>60TWH</b>	\$182.00	<b>60TWH</b>	\$191.00	Half Panel	24.87 x 20.00 [632 x 508]	60x24 1418TW18 and HN4FS602418xx
<b>72WFW</b>	\$305.00	<b>72WFW</b>	\$321.00	Full Panel	60.00 x 20.00 [1524 x 508]	72x24/72x25 1418xxxx and HN4FS72xxxxxx
<b>72WHW</b>	\$197.00	<b>72WHW</b>	\$207.00	Half Panel	30.87 x 20.00 [784 x 508]	72x24/72x25 1418xxxx and HN4FS72xxxxxx
<b>90YWF</b>	\$355.00	<b>90YWF</b>	\$372.00	Full Panel	78.00 x 20.00 [1981 x 508]	90x24 1418YW20 and HN4FS902420xx
<b>90YWH</b>	\$222.00	<b>90YWH</b>	\$233.00	Half Panel	39.87 x 20.00 [1013 x 508]	90x24 1418YW20 and HN4FS902420xx
<b>72XFW</b>	\$355.00	<b>72XFW</b>	\$372.00	Full Panel	60.00 x 26.00 [1524 x 660]	72x30/72x31 1418xxxx and HN4FS72xxxxxx
<b>72XHW</b>	\$222.00	<b>72XHW</b>	\$233.00	Half Panel	30.87 x 26.00 [784 x 660]	72x30/72x31 1418xxxx and HN4FS72xxxxxx
<b>60TYFW</b>	\$351.00	<b>60TYFW</b>	\$369.00	Full Panel	48.00 x 32.00 [1219 x 813]	60x36 1418TY24 and HN4FS603624SS
<b>60TYHW</b>	\$222.00	<b>60TYHW</b>	\$233.00	Half Panel	24.87 x 32.00 [632 x 813]	60x36 1418TY24 and HN4FS603624SS
<b>72YFW</b>	\$404.00	<b>72YFW</b>	\$424.00	Full Panel	60.00 x 32.00 [1524 x 813]	72x36/72x37 1418xxxx and HN4FS72xxxxxx
<b>72YHW</b>	\$248.00	<b>72YHW</b>	\$260.00	Half Panel	30.87 x 32.00 [784 x 813]	72x36/72x37 1418xxxx and HN4FS72xxxxxx
<b>90YFW</b>	\$482.00	<b>90YFW</b>	\$506.00	Full Panel	78.00 x 32.00 [1981 x 813]	90x36 1418YYxx and HN4FS9036xxxx
<b>90YHW</b>	\$286.00	<b>90YHW</b>	\$301.00	Half Panel	39.87 x 32.00 [1013 x 813]	90x36 1418YYxx and HN4FS9036xxxx

*Note: Dimensions in inches [millimeters].*

# Enclosure Subpanels

## 1418FS and HN4FS Freestanding Enclosures



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Double-Door Subpanels						
Painted	Price	Galvanized	Price	Type	Dimensions HxW	For Use With
<b>60AWFW</b>	\$563.00	<b>60AWFWG</b>	\$591.00	Full	48.00 x 44.00 [1219 x 1118]	60x48 1418AW18
<b>60AWHW</b>	\$351.00	<b>60AWHWG</b>	\$396.00	Half	24.87 x 44.00 [632 x 1118]	60x48 1418AW18
<b>72ZFW</b>	\$637.00	<b>72ZFWG</b>	\$669.00	Full	60.00 x 44.00 [1524 x 1118]	72x48 1418ZWxx
<b>72ZHW</b>	\$408.00	<b>72ZHWG</b>	\$427.00	Half	30.87 x 44.00 [784 x 1118]	72x48 1418ZWxx
<b>72ZFW</b>	\$739.00	<b>72ZFWG</b>	\$776.00	Full	60.00 x 56.00 [1524 x 1422]	72x60 1418ZXxx
<b>72ZHW</b>	\$459.00	<b>72ZHWG</b>	\$482.00	Half	30.87 x 56.00 [784 x 1422]	72x60 1418ZXxx
<b>72ZYFW</b>	\$839.00	<b>72ZYFWG</b>	\$924.00	Full	60.00 x 68.00 [1524 x 1727]	72x72 1418ZYxx
<b>72ZYHW</b>	\$511.00	<b>72ZYHWG</b>	\$536.00	Half	30.87 x 68.00 [784 x 1727]	72x72 1418ZYxx
<b>90BFW</b>	\$749.00	<b>90BFWG</b>	\$787.00	Full	78.00 x 44.00 [1981 x 1118]	90x48 1418BW20
<b>90BHW</b>	\$463.00	<b>90BHWG</b>	\$486.00	Half	39.87 x 44.00 [1013 x 1118]	90x48 1418BW20
<b>90BYFW</b>	\$1,013.00	<b>90BYFWG</b>	\$1,116.00	Full	78.00 x 68.00 [1981 x 1727]	90x72 1418BYxx
<b>90BYHW</b>	\$596.00	<b>90BYHWG</b>	\$627.00	Half	39.87 x 68.00 [1013 x 1727]	90x72 1418BYxx


*Note: Dimensions in inches [millimeters].*

See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# Freestanding Enclosure 19in Swing-Out Frame



## 1418FS and HN4FS Enclosures



### Construction



- Formed from 10 gauge steel, frames are drilled and tapped to EIA requirements for mounting standard 19in rack accessories.
- Designed for installation in 72in and 90in high enclosures. The swing frame pivots on 0.5in pins within the enclosure for easy access to the rear of rack mounted equipment.
- The frame positions at any depth within the enclosure and is fastened in the closed position with 1/4-turn fasteners.
- Swing frames may be mounted in 30in and 36in wide enclosures, or in 60in and 72in wide enclosures with an optional center panel support.
- One or two frames may be mounted in 30in and 36in wide enclosures with dual access, and 1, 2, 3 or 4 frames may be mounted in 60in and 72in wide dual access enclosures.
- Finished in black powder coat.

Freestanding Enclosure 19in Swing-Out Frame			
Part Number	Price	For Use With	Rack Units
1418SFYY	\$745.00	90x36in	44
1418SFY	\$705.00	72x36in	33
1418SFX	\$654.00	72x30in	33

*Note: Dimensions in inches [millimeters].*

Shipping Schedule	
Same day	1 - 15 days

Color indicates shipping lead time in business days.



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.