

Enclosure Subpanels

Eclipse Series Enclosures




Construction

- Larger than standard NEMA panel used in same sized enclosure.
- 12 gauge steel construction.
- Larger sizes have 2 or 4 formed flanges for added strength.
- Slotted corner design for easier mounting.
- Finished in RAL 9003 white powder coat or unpainted galvanized.



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	



See our website: www.AutomationDirect.com for complete engineering drawings.

Subpanels for Eclipse Series Hammond Enclosures				
Painted	Price	Galvanized	Price	Dimensions HxW
EP1210	\$12.00	EPG1210	\$11.75	10.17 x 8.17in [258 x 208]
EP1212	\$12.00	EPG1212	\$9.00	10.17 x 10.17in [258 x 258]
EP1224	\$37.00	EPG1224	\$37.00	10.17 x 22.17in [258 x 563]
EP1612	\$15.25	EPG1612	\$11.50	14.17 x 10.17in [360 x 258]
EP1616	\$29.50	EPG1616	\$29.50	14.17 x 14.17in [360 x 360]
EP1620	\$34.00	EPG1620	\$34.00	14.17 x 18.17in [360 x 462]
EP2012	\$27.50	EPG2012	\$34.00	18.17 x 10.17in [462 x 258]
EP2016	\$34.00	EPG2016	\$34.00	18.17 x 14.17in [462 x 360]
EP2020	\$41.00	EPG2020	\$41.00	18.17 x 18.17in [462 x 462]
EP2024	\$52.00	EPG2024	\$52.00	18.17 x 22.17in [462 x 563]
EP2412	\$37.00	EPG2412	\$37.00	22.17 x 10.17in [563 x 258]
EP2416	\$40.50	EPG2416	\$40.50	22.17 x 14.17in [563 x 360]
EP2420	\$52.00	EPG2420	\$52.00	22.17 x 18.17in [563 x 462]
EP2424	\$61.00	EPG2424	\$61.00	22.17 x 22.17in [563 x 563]
EP2430	\$74.00	EPG2430	\$74.00	22.17 x 28.17in [563 x 716]
EP2442	\$102.00	EPG2442	\$102.00	22.17 x 40.17in [563 x 1020]
EP2448	\$115.00	EPG2448	\$115.00	22.17 x 46.17in [563 x 1173]
EP3012	\$45.50	EPG3012	\$45.50	28.17 x 10.17in [716 x 258]
EP3016	\$56.00	EPG3016	\$56.00	28.17 x 14.17in [716 x 360]
EP3020	\$64.00	EPG3020	\$64.00	28.17 x 18.17in [716 x 462]
EP3024	\$74.00	EPG3024	\$74.00	28.17 x 22.17in [716 x 563]
EP3030	\$97.00	EPG3030	\$97.00	28.17 x 28.17in [716 x 716]
EP3036	\$113.00	EPG3036	\$113.00	28.17 x 34.17in [716 x 868]
EP3042	\$133.00	EPG3042	\$133.00	28.17 x 40.17in [716 x 1020]
EP3048	\$149.00	EPG3048	\$149.00	28.17 x 46.17in [716 x 1173]
EP3060	\$181.00	EPG3060	\$181.00	28.17 x 58.17in [716 x 1478]
EP3624	\$86.00	EPG3624	\$86.00	34.17 x 22.17in [868 x 563]
EP3630	\$113.00	EPG3630	\$113.00	34.17 x 28.17in [868 x 716]
EP3636	\$133.00	EPG3636	\$133.00	34.17 x 34.17in [868 x 868]
EP3642	\$156.00	EPG3642	\$156.00	34.17 x 40.17in [868 x 1020]
EP3648	\$171.00	EPG3648	\$171.00	34.17 x 46.17in [868 x 1173]
EP3660	\$209.00	EPG3660	\$209.00	34.17 x 58.17in [868 x 1478]
EP4224	\$100.00	EPG4224	\$100.00	40.17 x 22.17in [1020 x 563]
EP4230	\$133.00	EPG4230	\$133.00	40.17 x 28.17in [1020 x 716]
EP4236	\$156.00	EPG4236	\$156.00	40.17 x 34.17in [1020 x 868]
EP4824	\$115.00	EPG4824	\$115.00	46.17 x 22.17in [1173 x 563]
EP4830	\$145.00	EPG4830	\$149.00	46.17 x 28.17in [1173 x 716]
EP4836	\$171.00	EPG4836	\$171.00	46.17 x 34.17in [1173 x 868]
EP4848	\$207.00	EPG4848	\$184.00	46.17 x 46.17in [1173 x 1173]
EP6036	\$209.00	EPG6036	\$209.00	58.17 x 34.17in [1478 x 868]
EP7230	\$226.00	EPG7230	\$225.00	70.17 x 28.17in [1782 x 716]
EP7236	\$251.00	EPG7236	\$249.00	70.17 x 34.17in [1782 x 868]

Note: Dimensions in inches [millimeters].

Eclipse Series Swing Panel Kits



Construction


- Hinged panel allows access to internally mounted equipment.
- 12 gauge steel panel included.
- Slotted 1/4-turn latches provide closure.
- Adding optional locking 1/4-turn latches (Part Number EQTRL) convert this to a dead front panel.
- Complete with 4-6in depth adjustment channels.
- Hardware kit maintains UL, CSA and NEMA ratings when field installed.
- Finished in RAL 9003 white powder coat.



Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Swing Panel Kits - Eclipse Series			
Part Number	Price	Dimensions HxW	For Use With
ESP1212	\$97.00	9.75 x 9.79in [248 x 249]	12x12 (HxW) EN4SD12126xx & ST12126LG Eclipse series enclosures
ESP1612	\$101.00	13.75 x 9.79in [349 x 249]	16x12 (HxW) EN4SD1612xxx & ST1612xxx Eclipse series enclosures
ESP1616	\$106.00	13.75 x 13.79in [349 x 350]	16x16 (HxW) EN4SD1616xxx & ST1616xxx Eclipse series enclosures
ESP1620	\$112.00	13.75 x 17.79in [349 x 452]	16x20 (HxW) EN4SD1620xxx Eclipse series enclosures
ESP2016	\$112.00	17.75 x 13.79in [451 x 350]	20x16 (HxW) EN4SD2016xxx & ST2016xxx Eclipse series enclosures
ESP2020	\$118.00	17.75 x 17.79in [451 x 452]	20x20 (HxW) EN4SD2020xxx & ST2020xxx Eclipse series enclosures
ESP2024	\$125.00	17.75 x 21.79in [451 x 553]	20x24 (HxW) EN4SD2024xxx Eclipse series enclosures
ESP2416	\$118.00	21.75 x 13.79in [552 x 350]	24x16 (HxW) EN4SD2416xxx Eclipse series enclosures
ESP2420	\$125.00	21.75 x 17.79in [552 x 452]	24x20 (HxW) EN4SD2420xxx & ST2420xxx Eclipse series enclosures
ESP2424	\$134.00	21.75 x 21.79in [552 x 553]	24x24 (HxW) EN4SD2424xxx & ST2424xxx Eclipse series enclosures
ESP3020	\$136.00	27.75 x 17.79in [705 x 452]	30x20 (HxW) EN4SD3020xxx Eclipse series enclosures
ESP3024	\$145.00	27.75 x 21.79in [705 x 553]	30x24 (HxW) EN4SD3024xxx & ST3024xxx Eclipse series enclosures
ESP3030	\$161.00	27.75 x 27.79in [705 x 706]	30x30 (HxW) EN4SD3030xxx & ST3030xxx Eclipse series enclosures
ESP3624	\$158.00	33.75 x 21.79in [857 x 553]	36x24 (HxW) EN4SD3624xxx Eclipse series enclosures
ESP3630	\$176.00	33.75 x 27.79in [857 x 706]	36x30 (HxW) EN4SD3630xxx & ST3630xxx Eclipse series enclosures
ESP3636	\$194.00	33.75 x 33.79in [857 x 858]	36x36 (HxW) EN4SD3636xxx & ST363612xx Eclipse series enclosures
ESP4236	\$215.00	39.75 x 33.79in [1010 x 858]	42x36 (HxW) EN4SD4236xxx Eclipse series enclosures
ESP4824	\$171.00	45.75 x 21.79in [1162 x 553]	48x24 (HxW) EN4SD4824xxx Eclipse series enclosures
ESP4836	\$245.00	45.75 x 33.79in [1162 x 858]	48x36 (HxW) EN4SD4836xxx & ST4836xxxx Eclipse series enclosures
ESP6036	\$290.00	57.75 x 33.79in [1467 x 858]	60x36 (HxW) EN4SD6036xxx & ST6036xxxx Eclipse series enclosures

Note: Dimensions in inches [millimeters].



See our website: www.AutomationDirect.com for complete engineering drawings.

Eclipse Series Swing Frame




Construction

- Provides 19in rack mounting with full EIA spacing (punched holes).
- Hinges allow easy equipment access.
- Slotted 1/4-turn latches provide closure.
- Optional locking 1/4-turn latch available by ordering Part No. EQTRL
- Adding optional locking 1/4-turn latches provides added security.
- Complete with 4-6in depth adjustment channels.
- Mounting hardware sold separately.
- Hardware kit maintains UL, CSA and NEMA ratings when field installed.
- Finished in black powder coat.

Shipping Schedule	
Same day	1 - 15 days
Color indicates shipping lead time in business days.	

Eclipse Swing Frame				
Part Number	Price	For Use With	Rack Spacing Width	Rack Units
ESF2424	\$196.00	24x24in (HxW) wall-mount enclosures	19.00in	11U
ESF3024	\$254.00	30x24in (HxW) wall-mount enclosures	19.00in	14U
ESF3624	\$292.00	36x24in (HxW) wall-mount enclosures	19.00in	17U
<i>Note: Dimensions in inches [millimeters].</i>				



See our website: www.AutomationDirect.com for complete engineering drawings.