


# Subpanels for Premier, JIC and Classic Series Fiberglass Enclosures



Subpanel Specifications		
Subpanel	Material	Color/Finish
Carbon Steel	Carbon Steel	White polyester powder Finish
Aluminum	3003H14 Aluminum	Mill Finish
Stainless Steel	304 Stainless	Mill Finish
Fiberglass	FRP (Fiberglass reinforced panel)	Gray



## Carbon steel subpanels

## Fiberglass subpanels

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt (lb)
HW-MP604CS	\$5.75	4.88 x 2.88 x 0.075 [124 x 73 x .19]	6 x 4	0.3
HW-MP606CS	\$5.75	4.88 x 4.88 x 0.075 [124 x 124 x .19]	6 x 6	0.5
HW-MP706CS	\$7.50	6.00 x 4.88 x 0.075 [152 x 124 x .19]	7 x 6	0.6
HW-MP806CS	\$7.75	6.75 x 4.88 x 0.075 [152 x 124 x .19]	8 x 6	0.8
HW-MP808CS	\$10.00	6.88 x 6.88 x 0.075 [175 x 175 x .19]	8 x 8	0.8
HW-MP906CS	\$9.50	8.25 x 4.88 x 0.075 [175 x 124 x .19]	9 x 6	0.9
HW-MP1008CS	\$11.50	8.75 x 6.88 x 0.075 [225 x 175 x .19]	10 x 8	1.3
HW-MP1210CS	\$14.00	10.88 x 8.75 x 0.075 [276 x 225 x .19]	12 x 10	2.1
HW-MP1412CS	\$15.50	12.88 x 10.88 x 0.075 [327 x 276 x .19]	14 x 12	3.0
HW-MP1614CS	\$20.50	14.88 x 12.88 x 0.075 [378 x 327 x .19]	16 x 14	4.1
HW-MP1816CS	\$26.50	16.88 x 14.88 x 0.075 [429 x 378 x .19]	18 x 16	5.4
HW-MP2016CS	\$33.50	18.88 x 14.88 x 0.075 [479 x 378 x .19]	20 x 16	6.1
HW-MP2020CS	\$98.00	18.00 x 18.00 x 0.105 [457 x 457 x 2.7]	20 x 20	9.4
HW-MP2420CS	\$119.00	22.00 x 18.00 x 0.105 [558 x 457 x 2.7]	24 x 20	11
HW-MP2424CS	\$146.00	22.00 x 22.00 x 0.105 [558 x 558 x 2.7]	24 x 24	22

Note: Dimensions in inches [millimeters].

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt. (lb)
HW-MP604FG	\$5.75	4.88 x 2.88 x 0.13 [124 x 73 x 3.2]	6 x 4	0.1
HW-MP606FG	\$5.75	4.88 x 4.88 x 0.13 [124 x 124 x 3.2]	6 x 6	0.2
HW-MP806FG	\$7.75	6.88 x 4.88 x 0.13 [175 x 124 x 3.2]	8 x 6	0.3
HW-MP808FG	\$10.00	6.88 x 6.88 x 0.13 [175 x 175 x 3.2]	8 x 8	0.3
HW-MP1008FG	\$9.50	8.88 x 6.88 x 0.13 [225 x 175 x 3.2]	10 x 8	0.5
HW-MP1210FG	\$13.50	10.88 x 8.88 x 0.13 [276 x 225 x 3.2]	12 x 10	0.9
HW-MP1412FG	\$17.00	12.88 x 10.88 x 0.13 [327 x 276 x 3.2]	14 x 12	1.0
HW-MP1614FG	\$21.00	14.88 x 12.88 x 0.13 [378 x 327 x 3.2]	16 x 14	0.8
HW-MP1816FG	\$27.00	16.88 x 14.88 x 0.13 [429 x 378 x 3.2]	18 x 16	2.0
HW-MP2016FG	\$33.00	18.88 x 14.88 x 0.13 [479 x 378 x 3.2]	20 x 16	2.2
HW-MP2020FG	\$106.00	18.00 x 18.00 x 0.13 [457 x 457 x 3.2]	20 x 20	2.3
HW-MP2420FG	\$128.00	22.00 x 18.00 x 0.13 [558 x 457 x 3.2]	24 x 20	2.8
HW-MP2424FG	\$157.00	22.00 x 22.00 x 0.13 [558 x 558 x 3.2]	24 x 24	3.5

Note: Dimensions in inches [millimeters].

### Enclosure Shipping Schedule

Same day	1-7 days	1 - 10 days	1-15 days
----------	----------	-------------	-----------

Color indicates shipping lead time in business days.

# Subpanels for Premier, JIC and Classic Series Fiberglass Enclosures

## Stainless steel subpanels

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt. (lb)
<b>HW-MP604SS</b>	\$7.75	4.88 x 2.88 x 0.064 [124 x 73 x 1.5]	6 x 4	0.3
<b>HW-MP606SS</b>	\$9.75	4.88 x 4.88 x 0.064 [124 x 124 x 1.5]	6 x 6	0.5
<b>HW-MP806SS</b>	\$12.50	6.88 x 4.88 x 0.064 [175 x 124 x 1.5]	8 x 6	0.8
<b>HW-MP808SS</b>	\$15.50	6.88 x 6.88 x 0.064 [175 x 175 x 1.5]	8 x 8	0.8
<b>HW-MP1008SS</b>	\$21.00	8.88 x 6.88 x 0.064 [225 x 175 x 1.5]	10 x 8	1.2
<b>HW-MP1210SS</b>	\$31.50	10.88 x 8.88 x 0.064 [276 x 225 x 1.5]	12 x 10	1.9
<b>HW-MP1412SS</b>	\$46.50	12.88 x 10.88 x 0.064 [327 x 276 x 1.5]	14 x 12	2.9
<b>HW-MP1614SS</b>	\$56.00	14.88 x 12.88 x 0.064 [378 x 327 x 1.5]	16 x 14	3.1
<b>HW-MP1816SS</b>	\$65.00	16.88 x 14.88 x 0.064 [429 x 378 x 1.5]	18 x 16	6.0
<b>HW-MP2016SS</b>	\$77.00	18.88 x 14.88 x 0.064 [479 x 378 x 1.5]	20 x 16	6.1

**Note: Dimensions in inches [millimeters].**




## Aluminum subpanels

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Wt. (lb)
<b>HW-MP604A</b>	\$5.75	4.88 x 2.88 x 0.081 [124 x 73 x 2.0]	6 x 4	0.1
<b>HW-MP606A</b>	\$5.75	4.88 x 4.88 x 0.081 [124 x 124 x 2.0]	6 x 6	0.2
<b>HW-MP806A</b>	\$7.75	6.88 x 4.88 x 0.081 [175 x 124 x 2.0]	8 x 6	0.3
<b>HW-MP1008A</b>	\$11.50	8.88 x 6.88 x 0.081 [225 x 175 x 2.0]	10 x 8	0.5
<b>HW-MP1210A</b>	\$14.00	10.88 x 8.88 x 0.081 [276 x 225 x 2.0]	12 x 10	0.8
<b>HW-MP1412A</b>	\$15.50	12.88 x 10.88 x 0.081 [327 x 276 x 2.0]	14 x 12	1.1
<b>HW-MP1614A</b>	\$20.50	14.88 x 12.88 x 0.081 [378 x 327 x 2.0]	16 x 14	1.5
<b>HW-MP1816A</b>	\$26.50	16.88 x 14.88 x 0.081 [429 x 378 x 2.0]	18 x 16	2.5
<b>HW-MP2016A</b>	\$33.50	18.88 x 14.88 x 0.081 [479 x 378 x 2.0]	20 x 16	2.4
<b>HW-MP2020AL</b>	\$94.00	18.0 x 18.0 x 0.129 [457 x 457 x 3.3]	20 x 20	3.7
<b>HW-MP2420AL</b>	\$113.00	22.0 x 18.0 x 0.129 [558 x 457 x 3.3]	24 x 20	4.5
<b>HW-MP2424AL</b>	\$139.00	22.0 x 22.0 x 0.129 [558 x 558 x 3.3]	24 x 24	5.4

**Note: Dimensions in inches [millimeters].**

Enclosure Shipping Schedule		
Same day	1-7 days	1 - 10 days
Color indicates shipping lead time in business days.		

### Dimensions



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# Subpanels for Control Series Fiberglass Enclosures



## Carbon steel subpanels

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Panel Type	Wt. (lb)
<b>HW-WM1610CS</b>	\$25.00	13.00 x 8.50 x 0.105 [330 x 216 x 2.7]	16 x 10	Flat	3.3
<b>HW-WM2016CS</b>	\$43.00	17.00 x 13.00 x 0.105 [432 x 330 x 2.7]	20 x 16	Flat	6.7
<b>HW-WM2412CS</b>	\$41.50	21.00 x 9.00 x 0.105 [533 x 229 x 2.7]	24 x 12	Flat	8.7
<b>HW-WM2420CS</b>	\$85.00	21.00 x 17.00 x 0.105 [533 x 432 x 2.7]	24 x 20	Flat	11
<b>HW-WM2424CS</b>	\$104.00	21.00 x 21.00 x 0.105 [533 x 533 x 2.7]	24 x 24	Flat	13
<b>HW-WM3020CS</b>	\$108.00	27.00 x 17.00 x 0.105 [686 x 432 x 2.7]	30 x 20	Flat	14
<b>HW-WM3024CS</b>	\$133.00	27.00 x 21.00 x 0.105 [686 x 533 x 2.7]	30 x 24	Flat	17
<b>HW-WM3630CS</b>	\$208.00	33.00 x 27.00 x 0.105 [838 x 686 x 2.7]	36 x 30	Flat	27
<b>HW-WM4836CS</b>	\$302.00	33.00 x 45.00 x 0.105 [838 x 1143 x 2.7]	48 x 36	Formed	41
<b>HW-WM6036CS</b>	\$374.00	57.00 x 33.00 x 0.105 [1448 x 838 x 2.7]	60 x 36	Formed	60

Note: Dimensions in inches [millimeters].

Subpanel Specifications		
Subpanel	Material	Finish
Carbon Steel	Carbon Steel	White polyester powder Finish
Aluminum	3003H14 Aluminum	Mill Finish


Enclosure Shipping Schedule	
Same day	1-15 days
Color indicates shipping lead time in business days	

## Aluminum subpanels

Subpanel Part Number	Price	Subpanel Size HxWxD	Enclosure Nominal Size HxW	Panel Type	Wt. (lb)
<b>HW-WM1610A</b>	\$38.50	13.00 x 8.50 x 0.081 [330 x 216 x 2.0]	16 x 10	Flat	1.0
<b>HW-WM2016A</b>	\$43.00	17.00 x 13.00 x 0.081 [432 x 330 x 2.0]	20 x 16	Flat	2.0
<b>HW-WM2412A</b>	\$41.50	21.00 x 9.00 x 0.081 [533 x 229 x 2.0]	24 x 12	Flat	4.5
<b>HW-WM2420A</b>	\$85.00	21.00 x 17.00 x 0.129 [533 x 432 x 3.3]	24 x 20	Flat	4.5
<b>HW-WM2424A</b>	\$104.00	21.00 x 21.00 x 0.129 [533 x 533 x 3.3]	24 x 24	Flat	5.5
<b>HW-WM3020A</b>	\$108.00	27.00 x 17.00 x 0.129 [686 x 432 x 3.3]	30 x 20	Flat	5.8
<b>HW-WM3024A</b>	\$133.00	27.00 x 21.00 x 0.129 [686 x 533 x 3.3]	30 x 24	Flat	7.0
<b>HW-WM3630A</b>	\$208.00	33.00 x 27.00 x 0.129 [838 x 686 x 3.3]	36 x 30	Flat	11
<b>HW-WM4836A</b>	\$302.00	33.00 x 45.00 x 0.129 [838 x 1143 x 3.3]	48 x 36	Formed	22
<b>HW-WM6036A</b>	\$374.00	57.00 x 33.00 x 0.129 [1448 x 838 x 3.3]	60 x 36	Formed	23

Note: Dimensions in inches [millimeters].

### Dimensions



See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.