

KILLARK Accessories and Replacement Parts

Sealing Fitting

The purpose of seals in a Class I hazardous location is to minimize the passage of gases and vapors and prevent the passage of flames from one electrical installation to another through the conduit system. Consult the electrical code or your local inspector for more detailed information.




**ENY-2
Sealing Fitting**

ENY Sealing Fitting Dimensions					
Part Number	Price	Hub Size (inches)	Dimensions (in-mm)		Turning Radius*
			A	B	
ENY-2	\$20.00	3/4	4-1/16 (103)	2-1/16 (52)	1-9/32 (33)

*Use Turning Radius to help determine if sealing fitting will fit properly in your installation.

ENY-2 Sealing Fitting

- Suitable for vertical or horizontal installation
- Copper-free aluminum (less than 0.4 %)
- Electrostatically applied powder coating



Sealing Compound and Packing Fiber



**Sealing
Compound**



Packing Fiber

Ounces Required per Fitting			
Sealing Fitting	Hub Size (inches)	Sealing Compound	Packing Fiber
ENY-2	3/4	2 oz.	1/8 oz.

Sealing Compound

SC series sealing compound is a cement used extensively for sealing conduit to prevent the spread of explosive gases.

- Non-shrinking and forms a secure seal
- Resists acids, water, oil, etc.
- UL listed when used with ENY series sealing fittings
- CE certified when used with any CSA certified sealing fitting

Packing Fiber

- Made from environmentally safe, non-asbestos material
- Easy to use and forms a positive dam to hold sealing compound

Sealing Compound		
Part Number	Price	Size
SC-4-OZ	\$8.00	4 ounces
SC-8-OZ	\$8.00	8 ounces
SC-1-LB	\$14.00	1 pound

Packing Fiber		
Part Number	Price	Size
PF-2	\$20.00	2 ounces
PF-4	\$36.00	4 ounces
PF-16	\$106.00	1 pound

KILLARK Accessories and Replacement Parts - Continued

Accessories and Replacement Parts Overview

We offer an accessory blank cover, a large selection of legend plates, and replacement keys and LEDs.

Replacement contacts are not available for any of our Killark hazardous duty controls. We also do not offer replacement switches, covers, or bolts.

Blank Cover and Replacement Key



X-10
Blank Cover



KEY-C002B
Replacement Key

Blank Cover and Replacement Key		
Part Number	Price	Description
X-10	\$33.00	Blank cover for use with splice/device boxes.
KEY-C002B	\$10.00	Replacement key for FXCS and XCS series key-operated selector switches.

Replacement LED Lamps



Replacement 110 VAC/VDC LED lamps for FXCS and XCS series pilot lights.

Replacement LED Lamps			
Part Number	Price	Color	Volts AC/DC
GOLED-A110	\$43.00	Amber	110 VAC/VDC
GOLED-G110	\$43.00	Green	
GOLED-R110	\$43.00	Red	
GOLED-W110	\$43.00	White	