

# KILLARK XCS Series Control Station Cover Assemblies - Pilot Lights

## Listings



Pilot Light



Double Pilot Light



Pilot Light / Pushbutton



Pilot Light / Two Mini Pushbutton

- UL Listed; File E53360
- Class I, Div. 1 & 2, Groups C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- NEMA 3, 7 (C, D) 9 (E, F, G)
- CSA Certified; File LR11714
- Class I, Zones 1 & 2, Groups IIB, IIA



| XCS Pilot Light                          |          |                    |         |             |            |                      |
|--|----------|--------------------|---------|-------------|------------|----------------------|
| Part Number (Includes cover with device) | Price    | Description        | Diagram | LED Voltage | Lens Color | Legend Plate Marking |
| <b>XCS-0B24ALD</b>                       | \$165.00 | Single pilot light |         | 110 VAC/VDC | Amber      | Blank plate          |
| <b>XCS-0B24CLD</b>                       | \$165.00 | Single pilot light |         | 110 VAC/VDC | Clear      | Blank plate          |
| <b>XCS-0B24GLD</b>                       | \$165.00 | Single pilot light |         | 110 VAC/VDC | Green      | Blank plate          |
| <b>XCS-0B24RLD</b>                       | \$165.00 | Single pilot light |         | 110 VAC/VDC | Red        | Blank plate          |

| XCS Double Pilot Light                   |          |                  |         |             |             |                      |
|--|----------|------------------|---------|-------------|-------------|----------------------|
| Part Number (Includes cover with device) | Price    | Description      | Diagram | LED Voltage | Lens Colors | Legend Plate Marking |
| <b>XCS-0B30ALD</b>                       | \$249.00 | Two pilot lights |         | 110 VAC/VDC | Amber Amber | Two blank plates     |
| <b>XCS-0B30CLD</b>                       | \$243.00 | Two pilot lights |         | 110 VAC/VDC | Clear Clear | Two blank plates     |
| <b>XCS-0B30GLD</b>                       | \$243.00 | Two pilot lights |         | 110 VAC/VDC | Green Green | Two blank plates     |
| <b>XCS-0B30RLD</b>                       | \$243.00 | Two pilot lights |         | 110 VAC/VDC | Red Red     | Two blank plates     |
| <b>XCS-0B30RLD-GLD</b>                   | \$243.00 | Two pilot lights |         | 110 VAC/VDC | Red Green   | Two blank plates     |

| XCS Momentary Contact Pushbutton and Pilot Light |          |   |         |             |                  |            |   |
|--|----------|---|---------|-------------|------------------|------------|---|
| Part Number (Includes cover with device)         | Price    | Description                               | Diagram | LED Voltage | Pushbutton Color | Lens Color | Legend Plate Marking                            |
| <b>XCS-0B13-CD</b>                               | \$172.00 | 1 N.C. momentary operator and pilot light |         | 110 VAC/VDC | Red              | Clear      | Pushbutton: "STOP"<br>Pilot light: Blank plate  |
| <b>XCS-0B13-OD</b>                               | \$172.00 | 1 N.O. momentary operator and pilot light |         | 110 VAC/VDC | Green            | Red        | Pushbutton: "START"<br>Pilot light: Blank plate |
| <b>XCS-0B13-UD</b>                               | \$215.00 | 1 N.O. / 1 N.C. momentary and pilot light |         | 110 VAC/VDC | Black            | Red        | Two blank plates                                |

| XCS Two Mini Momentary Contact Pushbuttons and Pilot Light |          |  |         |             |                   |            |   |
|--|----------|--|---------|-------------|-------------------|------------|---|
| Part Number (Includes cover with device)                   | Price    | Description  | Diagram | LED Voltage | Pushbutton Colors | Lens Color | Legend Plate Marking  |
| <b>XCS-0A15D</b>   | \$272.00 | Mini red operator with 1 N.C. momentary contact and mini green operator with 1 N.O. momentary contact, and pilot light |         | 110 VAC/VDC | Green Red         | Red        | N.O. Pushbutton: "START"<br>N.C. Pushbutton: "STOP"<br>Pilot light: Blank plate |


\* We also offer a large selection of optional legend plates. See accessories later in this section.

# KILLARK Hazardous Location Controls - Dimensions


## XCS Series Cover Assemblies

Dimensions in inches [mm]


### XCS-0B24ALD, -0B24CLD, -0B24RLD




### XCS-0B30ALD, -0B30CLD, -0B30GLD, -0B30RLD, -0B30RLD-GLD



### XCS-0B13-CD, -0B13-OD, -0B13-UD



### XCS-0A15D



# KILLARK SWB Series Splice/Device Boxes For Use With XCS Cover Assemblies



**SWB-2**



**SWB-5**



**SWB-8**



**SWB-11**



**SWB-42**

## Listings

- UL Listed; File E53360
- Class I, Div. 1 & 2, Groups C, D
- Class II, Div. 1 & 2, Groups E, F, G
- Class III
- NEMA 3, 7 (C, D) 9 (E, F, G)
- CSA Certified; File LR11712
- Class I, Zones 1 & 2, Groups IIB, IIA




| SWB Device Bodies |          |   |                   |
|-------------------|----------|---|-------------------|
| Part Number       | Price    | Description                             | Hub Size (inches) |
| <b>SWB-2</b>      | \$40.00  | Single gang / Dead-end                  | 3/4               |
| <b>SWB-5</b>      | \$41.00  | Single gang / Feed-through              | 3/4               |
| <b>SWB-8</b>      | \$78.00  | Double gang / Dead-end                  | 3/4               |
| <b>SWB-11</b>     | \$79.00  | Double gang / Feed-through              | 3/4               |
| <b>SWB-42</b>     | \$103.00 | Single gang / Dead-end / Deep style     | 3/4               |
| <b>SWB-45</b>     | \$127.00 | Single gang / Feed-through / Deep style | 3/4               |

# KILLARK Hazardous Location Controls - Dimensions


## SWB Series Splice/Device Boxes

Dimensions in inches [mm]


### SWB-2




### SWB-5



### SWB-42



### SWB-45




# KILLARK Hazardous Location Controls - Dimensions

## SWB Series Splice/Device Boxes

Dimensions in inches [mm]

### SWB-8



### SWB-11

