





# ISO 15552 Pneumatic Cylinders – Accessories

ISO 15552 Pneumatic Cylinder Accessories					
Item	Part No.	Description	Drawing Link	Weight (lbs)	Price
	<a href="#"><u>W0950322003</u></a>	Metal Work rear clevis mount, aluminum. For use with 32mm bore ISO 15552 cylinders. Mounting hardware included.	<a href="#"><u>PDF</u></a>	0.25	\$21.00
	<a href="#"><u>W0950402003</u></a>	Metal Work rear clevis mount, aluminum. For use with 40mm bore ISO 15552 cylinders. Mounting hardware included.	<a href="#"><u>PDF</u></a>	0.35	\$22.50
	<a href="#"><u>W0950502003</u></a>	Metal Work rear clevis mount, aluminum. For use with 50mm bore ISO 15552 cylinders. Mounting hardware included.	<a href="#"><u>PDF</u></a>	0.54	\$25.00
	<a href="#"><u>W0950632003</u></a>	Metal Work rear clevis mount, aluminum. For use with 63mm bore ISO 15552 cylinders. Mounting hardware included.	<a href="#"><u>PDF</u></a>	0.85	\$29.50
	<a href="#"><u>W0950802003</u></a>	Metal Work rear clevis mount, aluminum. For use with 80mm bore ISO 15552 cylinders. Mounting hardware included.	<a href="#"><u>PDF</u></a>	1.47	\$36.50
	<a href="#"><u>W0951002003</u></a>	Metal Work rear clevis mount, aluminum. For use with 100mm bore ISO 15552 cylinders. Mounting hardware included.	<a href="#"><u>PDF</u></a>	2.31	\$51.00
	<a href="#"><u>W0950322017</u></a>	Metal Work base pivot mount, aluminum. For use with 32mm bore ISO 15552 cylinders.	<a href="#"><u>PDF</u></a>	0.12	\$9.50
	<a href="#"><u>W0950402017</u></a>	Metal Work base pivot mount, aluminum. For use with 40mm bore ISO 15552 cylinders.	<a href="#"><u>PDF</u></a>	0.19	\$10.00
	<a href="#"><u>W0950502017</u></a>	Metal Work base pivot mount, aluminum. For use with 50mm bore ISO 15552 cylinders.	<a href="#"><u>PDF</u></a>	0.34	\$10.50
	<a href="#"><u>W0950632017</u></a>	Metal Work base pivot mount, aluminum. For use with 63mm bore ISO 15552 cylinders.	<a href="#"><u>PDF</u></a>	0.48	\$14.00
	<a href="#"><u>W0950802017</u></a>	Metal Work base pivot mount, aluminum. For use with 80mm bore ISO 15552 cylinders.	<a href="#"><u>PDF</u></a>	0.74	\$23.00
	<a href="#"><u>W0951002017</u></a>	Metal Work base pivot mount, aluminum. For use with 100mm bore ISO 15552 cylinders.	<a href="#"><u>PDF</u></a>	1.19	\$34.50








Illustration shows Rear Clevis and Base Pivot Mount assembled and attached to an ISO 15552 cylinder.

# G-Series ISO 15552 Pneumatic Cylinders – Accessories

G-Series Heavy Duty Pneumatic Cylinder Accessories						
Item	Part Number	Description	Pcs/Pkg	Wt (lb)	Drawing Link	Price
	<a href="#"><u>GRC-M10-125</u></a>	NITRA rod clevis, M10 X 1.25 thread, zinc plated steel. For use with G-series cylinders.	1	0.2	<a href="#">PDF</a>	\$4.50
	<a href="#"><u>GRC-M12-125</u></a>	NITRA rod clevis, M12 X 1.25 thread, zinc plated steel. For use with G-series cylinders.	1	0.3	<a href="#">PDF</a>	\$7.50
	<a href="#"><u>GRC-M16-15</u></a>	NITRA rod clevis, M16 X 1.5 thread, zinc plated steel. For use with G-series cylinders.	1	0.8	<a href="#">PDF</a>	\$16.00
	<a href="#"><u>GRC-M20-15</u></a>	NITRA rod clevis, M20 X 1.5 thread, zinc plated steel. For use with G-series cylinders.	1	1.5	<a href="#">PDF</a>	\$26.00
	<a href="#"><u>GRE-M10-125</u></a>	NITRA rod eye, M10 X 1.25 thread, spherical bearing, zinc plated steel. For use with G-series cylinders.	1	0.2	<a href="#">PDF</a>	\$25.00
	<a href="#"><u>GRE-M12-125</u></a>	NITRA rod eye, M12 X 1.25 thread, spherical bearing, zinc plated steel. For use with G-series cylinders.	1	0.3	<a href="#">PDF</a>	\$28.50
	<a href="#"><u>GRE-M16-15</u></a>	NITRA rod eye, M16 X 1.5 thread, spherical bearing, zinc plated steel. For use with G-series cylinders.	1	0.5	<a href="#">PDF</a>	\$53.00
	<a href="#"><u>GRE-M20-15</u></a>	NITRA rod eye, M20 X 1.5 thread, spherical bearing, zinc plated steel. For use with G-series cylinders.	1	0.9	<a href="#">PDF</a>	\$71.00
	<a href="#"><u>GRCP-M10-125</u></a>	NITRA self-aligning rod coupler, M10 X 1.25 thread, zinc plated steel. For use with G-series cylinders.	1	0.5	<a href="#">PDF</a>	\$57.00
	<a href="#"><u>GRCP-M12-125</u></a>	NITRA self-aligning rod coupler, M12 X 1.25 thread, zinc plated steel. For use with G-series cylinders.	1	0.7	<a href="#">PDF</a>	\$60.00
	<a href="#"><u>GRCP-M16-15</u></a>	NITRA self-aligning rod coupler, M16 X 1.5 thread, zinc plated steel. For use with G-series cylinders.	1	1.4	<a href="#">PDF</a>	\$78.00
	<a href="#"><u>GRCP-M20-15</u></a>	NITRA self-aligning rod coupler, M20 X 1.5 thread, zinc plated steel. For use with G-series cylinders.	1	1.5	<a href="#">PDF</a>	\$96.00
	<a href="#"><u>GMB-32MM</u></a>	NITRA mounting bracket, zinc plated steel. For use with 32mm bore G-series cylinders.	1	0.2	<a href="#">PDF</a>	\$7.00
	<a href="#"><u>GMB-40MM</u></a>	NITRA mounting bracket, zinc plated steel. For use with 40mm bore G-series cylinders.	1	0.3	<a href="#">PDF</a>	\$8.25
	<a href="#"><u>GMB-50MM</u></a>	NITRA mounting bracket, zinc plated steel. For use with 50mm bore G-series cylinders.	1	0.4	<a href="#">PDF</a>	\$9.50
	<a href="#"><u>GMB-63MM</u></a>	NITRA mounting bracket, zinc plated steel. For use with 63mm bore G-series cylinders.	1	0.6	<a href="#">PDF</a>	\$10.50
	<a href="#"><u>GMB-80MM</u></a>	NITRA mounting bracket, zinc plated steel. For use with 80mm bore G-series cylinders.	1	1.0	<a href="#">PDF</a>	\$15.00
	<a href="#"><u>GMB-100MM</u></a>	NITRA mounting bracket, zinc plated steel. For use with 100mm bore G-series cylinders.	1	1.3	<a href="#">PDF</a>	\$24.00

# G-Series ISO 15552 Pneumatic Cylinders – Accessories

G-Series Heavy Duty Pneumatic Cylinder Accessories						
Item	Part Number	Description	Pcs/Pkg	Wt (lb)	Drawing Link	Price
	<a href="#"><u>GMC-32MM</u></a>	NITRA rear pivot eye, zinc plated steel. For use with 32mm bore G-series cylinders.	1	0.2	<a href="#"><u>PDF</u></a>	\$18.00
	<a href="#"><u>GMC-40MM</u></a>	NITRA rear pivot eye, zinc plated steel. For use with 40mm bore G-series cylinders.	1	0.3	<a href="#"><u>PDF</u></a>	\$19.00
	<a href="#"><u>GMC-50MM</u></a>	NITRA rear pivot eye, zinc plated steel. For use with 50mm bore G-series cylinders.	1	0.6	<a href="#"><u>PDF</u></a>	\$22.00
	<a href="#"><u>GMC-63MM</u></a>	NITRA rear pivot eye, zinc plated steel. For use with 63mm bore G-series cylinders.	1	0.9	<a href="#"><u>PDF</u></a>	\$26.00
	<a href="#"><u>GMC-80MM</u></a>	NITRA rear pivot eye, zinc plated steel. For use with 80mm bore G-series cylinders.	1	1.5	<a href="#"><u>PDF</u></a>	\$32.00
	<a href="#"><u>GMC-100MM</u></a>	NITRA rear pivot eye, zinc plated steel. For use with 100mm bore G-series cylinders.	1	2.4	<a href="#"><u>PDF</u></a>	\$44.50
	<a href="#"><u>GSMC-32MM</u></a>	NITRA rear spherical pivot, spherical bearing, zinc plated steel. For use with 32mm bore G-series cylinders.	1	0.3	<a href="#"><u>PDF</u></a>	\$25.00
	<a href="#"><u>GSMC-40MM</u></a>	NITRA rear spherical pivot, spherical bearing, zinc plated steel. For use with 40mm bore G-series cylinders.	1	0.4	<a href="#"><u>PDF</u></a>	\$27.00
	<a href="#"><u>GSMC-50MM</u></a>	NITRA rear spherical pivot, spherical bearing, zinc plated steel. For use with 50mm bore G-series cylinders.	1	0.5	<a href="#"><u>PDF</u></a>	\$39.00
	<a href="#"><u>GSMC-63MM</u></a>	NITRA rear spherical pivot, spherical bearing, zinc plated steel. For use with 63mm bore G-series cylinders.	1	0.7	<a href="#"><u>PDF</u></a>	\$50.00
	<a href="#"><u>GSMC-80MM</u></a>	NITRA rear spherical pivot, spherical bearing, zinc plated steel. For use with 80mm bore G-series cylinders.	1	1.3	<a href="#"><u>PDF</u></a>	\$62.00
	<a href="#"><u>GSMC-100MM</u></a>	NITRA rear spherical pivot, spherical bearing, zinc plated steel. For use with 100mm bore G-series cylinders.	1	1.9	<a href="#"><u>PDF</u></a>	\$84.00
	<a href="#"><u>GFL-32MM</u></a>	NITRA flange mount plate, zinc plated steel. For use with 32mm bore G-series cylinders.	1	0.5	<a href="#"><u>PDF</u></a>	\$12.00
	<a href="#"><u>GFL-40MM</u></a>	NITRA flange mount plate, zinc plated steel. For use with 40mm bore G-series cylinders.	1	0.6	<a href="#"><u>PDF</u></a>	\$13.00
	<a href="#"><u>GFL-50MM</u></a>	NITRA flange mount plate, zinc plated steel. For use with 50mm bore G-series cylinders.	1	1.2	<a href="#"><u>PDF</u></a>	\$16.00
	<a href="#"><u>GFL-63MM</u></a>	NITRA flange mount plate, zinc plated steel. For use with 63mm bore G-series cylinders.	1	1.5	<a href="#"><u>PDF</u></a>	\$23.00
	<a href="#"><u>GFL-80MM</u></a>	NITRA flange mount plate, zinc plated steel. For use with 80mm bore G-series cylinders.	1	3.1	<a href="#"><u>PDF</u></a>	\$26.00
	<a href="#"><u>GFL-100MM</u></a>	NITRA flange mount plate, zinc plated steel. For use with 100mm bore G-series cylinders.	1	4.5	<a href="#"><u>PDF</u></a>	\$31.00
	<a href="#"><u>GN-M10-125</u></a>	NITRA rod nut, M10 X 1.25 thread, zinc plated steel. For use with G-series cylinders.	1	0.2	<a href="#"><u>PDF</u></a>	\$1.50
	<a href="#"><u>GN-M12-125</u></a>	NITRA rod nut, M12 X 1.25 thread, zinc plated steel. For use with G-series cylinders.	1	0.2	<a href="#"><u>PDF</u></a>	\$1.75
	<a href="#"><u>GN-M16-15</u></a>	NITRA rod nut, M16 X 1.5 thread, zinc plated steel. For use with G-series cylinders.	1	0.2	<a href="#"><u>PDF</u></a>	\$2.00
	<a href="#"><u>GN-M20-15</u></a>	NITRA rod nut, M20 X 1.5 thread, zinc plated steel. For use with G-series cylinders.	1	0.2	<a href="#"><u>PDF</u></a>	\$2.25