

# WC10 NEMA 12 and 13 Operator Consoles



## Applications

Designed to hold electrical and electronic controls and instruments. Heavy duty construction provides protection from dirt, dust, oil and water. Pushbuttons, pilot lights, meters, switches, etc. can be mounted on sloping control surfaces. Interior components can be mounted on subpanel and terminal straps.

## Construction

### Base

- Fabricated from 14 gauge steel
- Seams are continuously welded and ground smooth
- 3-point keylocking handle is provided on front, main door
- Flush main door
- Control panels are hinged along bottom edge
- Control panels have captivated screws threaded into sealed wells
- Door stops provided to hold control panel open
- Standard closed cell neoprene gasket
- Removable subpanel is included with enclosure
- Grounding provisions provided

### Top

- Fabricated from 14 gauge steel
- Seams are continuously welded and ground smooth
- Instrument and access panels have captivated screws that thread into sealed wells
- Closed cell neoprene gasket

### Writing desk

- Fabricated from 14 gauge steel
- Seams are continuously welded and ground smooth
- Desks are removable and attach easily to console front

## Finish

- ANSI 61 gray polyester powder inside and out over phosphatized surfaces
- Included painted steel subpanel is white polyester powder over phosphatized surfaces

## Listings

- UL 508, Types 12 and 13 [UL File E64791]
- CSA Certified, Type 12 & 13 [CSA File LL66078]
- NEMA/EEMAC Types 12 & 13



### Enclosure Shipping Schedule

Same day	1-7 days	1 -10 days
----------	----------	------------

Color indicates shipping lead time in business days.


WC10 NEMA 12 and 13 Operator Consoles			
Part Number	Price	Enclosure Size HxWxD	Description
<b>WC10B*</b>	\$1,249.00	40.13 x 24.13 x 20.12 [1019 x 613 x 511]	Console base
<b>WC10T</b>	\$310.00	16.15 x 24.15 x 5.13 [410 x 614 x 130]	Console top for WC10B
<b>WC10W</b>	\$117.00	3.00 x 24.13 x 10.13 [76 x 613 x 26]	Writing desk for WC10B
<b>WC10C</b>	\$173.00	N/A	Caster kit: Set of 4 casters, 2 mounting plates, and hardware

*Notes: Dimensions in inches [millimeters] Letters in table correspond to letters on dimensional drawings.  
\*Subpanel is included with console.  
Tops, writing desks and caster kits must be ordered separately.*

# WC12 NEMA 12 and 13 Operator Consoles

## Dimensions

In [mm]



### NOTES:

1. ACCESS DOORS OPEN 180 DEGREES.
2. 3-POINT KEY LOCKING HANDLES ARE PROVIDED ON MAIN DOORS
3. WRITING DESK IS PROVIDED WITH MOUNTING HARDWARE.
4. 48" WIDE CONSOLE HAS TWO DOORS.


See our website: [www.AutomationDirect.com](http://www.AutomationDirect.com) for complete engineering drawings.

# Enclosure Accessories - Mounting Feet and Casters




## Mounting Feet for Premier, Slim Line, Classic, and In-Line Series Enclosures

Mounting Foot Kit	Price	Description	Wt. [oz]
<b>HW-MGFTKIT</b>	\$13.50	Hubbell-Wiegmann mounting feet kit, fiberglass-reinforced polyester, for use on Premier series non-metallic enclosures. Includes (4) mounting feet and mounting hardware.	1
<b>HW-N4XMTGFTKIT</b>	\$25.50	Hubbell-Wiegmann mounting feet kit, fiberglass-reinforced polyester, for use on Slim Line and In-line series non-metallic enclosures. Includes (2) mounting feet, mounting hardware and silicone adhesive/sealant. (Fits 4-inch wide HW-N4Xxxx, HW-N4XxPB and HW-N4XxPB-22 series enclosures only.)	1
<b>HW-LMTGFTKIT</b>	\$25.508.00	Hubbell-Wiegmann mounting feet kit, fiberglass-reinforced polyester, for use on Classic series non-metallic enclosures. Includes (4) mounting feet and mounting hardware.	1



## Mounting Feet for Ultimate Series Enclosures

Mounting Feet	Price	Description	Wt. [lb]
<b>N412MFK</b>	\$17.25	Hubbell-Wiegmann mounting feet kit, plated finish. For use on NEMA 412 Ultimate series enclosures. Includes (4) mounting feet, mounting hardware and sealing washers.	4
<b>N412MFKSS</b>	\$48.00	Hubbell-Wiegmann mounting feet kit, 304 stainless steel. For use on NEMA 412 Ultimate series enclosures. Includes (4) mounting feet, mounting hardware and sealing washers.	4



## Casters

Casters can be used on any enclosure to provide mobility. Caster kits include mounting plates designed to fit Hubbell-Wiegmann WC10 and WC12 consoles, but can be adapted to fit other enclosures.

Caster Kit	Price	Description	Wt. [lb]	Capacity [lb]
<b>WC10C</b>	\$173.00	Hubbell-Wiegmann caster kit, for WC10 consoles. Includes 4 zinc-plated steel casters (2 swivel, 2 stationary), 2 ANSI 61 gray mounting plates and hardware.	4	200
<b>WC12C</b>	\$173.00	Hubbell-Wiegmann caster kit, for WC12 consoles. Includes 4 zinc-plated steel casters (2 swivel, 2 stationary), 2 ANSI 61 gray mounting plates and hardware.	4	200



Enclosure Shipping Schedule		
Same day	1 - 7 days	1-10 days
Color indicates shipping lead time in business days.		