



Hose Clamps



HC-58

NITRA Adjustable Hose Clamps				
Part No.	Description	Pcs/Pkg	Weight (lbs)	Price
HC-316	NITRA hose clamp, 2-ear, 0.318-0.433in diameter, plated steel. For use with HBV series 3/16in hose.	10	0.1	\$3.75
HC-14	NITRA hose clamp, 2-ear, 0.425-0.512in diameter, plated steel. For use with HBV series 1/4in hose.	10	0.1	\$4.00
HC-516	NITRA hose clamp, 2-ear, 0.492-0.591in diameter, plated steel. For use with HBV series 5/16in hose.	10	0.1	\$4.25
HC-38	NITRA hose clamp, 2-ear, 0.551-0.669in diameter, plated steel. For use with HBV series 3/8in hose.	10	0.1	\$4.25
HC-12	NITRA hose clamp, 2-ear, 0.638-0.787in diameter, plated steel. For use with HBV series 1/2in hose.	10	0.1	\$4.50
HC-58	NITRA hose clamp, 2-ear, 0.748-0.906in diameter, plated steel. For use with HBV series 5/8in hose.	10	0.2	\$5.25
HC-34	NITRA hose clamp, 2-ear, 0.945-1.102in diameter, plated steel. For use with HBV series 3/4in hose.	10	0.3	\$6.50
HC-1	NITRA hose clamp, 2-ear, 1.154-1.339in diameter, plated steel. For use with HBV series 1in hose.	10	0.3	\$11.00



HCSS-58

NITRA Interlocking Hose Clamps				
Part No.	Description	Pcs/Pkg	Weight (lbs)	Price
HCSS-316	NITRA hose clamp, interlocking ear, 0.346-0.413in diameter, 304 stainless steel. For use with HBV series 3/16in hose.	10	0.1	\$4.50
HCSS-14	NITRA hose clamp, interlocking ear, 0.398-0.465in diameter, 304 stainless steel. For use with HBV series 1/4in hose.	10	0.1	\$4.50
HCSS-516	NITRA hose clamp, interlocking ear, 0.472-0.571in diameter, 304 stainless steel. For use with HBV series 5/16in hose.	10	0.1	\$4.50
HCSS-38	NITRA hose clamp, interlocking ear, 0.520-0.618in diameter, 304 stainless steel. For use with HBV series 3/8in hose.	10	0.1	\$4.50
HCSS-12	NITRA hose clamp, interlocking ear, 0.654-0.780in diameter, 304 stainless steel. For use with HBV series 1/2in hose.	10	0.1	\$5.25
HCSS-58	NITRA hose clamp, interlocking ear, 0.823-0.949in diameter, 304 stainless steel. For use with HBV series 5/8in hose.	10	0.1	\$5.50
HCSS-34	NITRA hose clamp, interlocking ear, 0.941-1.067in diameter, 304 stainless steel. For use with HBV series 3/4in hose.	10	0.1	\$5.75
HCSS-1	NITRA hose clamp, interlocking ear, 1.236-1.362in diameter, 304 stainless steel. For use with HBV series 1in hose.	10	0.1	\$6.00



Hose Crimping Tools

NITRA hose crimping tools are designed to work with 2-ear and interlocking ear hose clamps. They come in three styles.

- Straight jaw single action, straight jaw compound action and side jaw compound action styles available
- Made in USA



HCT-ES



HCT-SC



HCT-AC

Nitra Hose Crimping Tools				
Part Number	Description	Pcs/Pkg	Package Weight (lbs)	Price
HCT-ES	NITRA hose clamp crimping tool, single action, straight jaw	1	0.8	\$29.00
HCT-SC	NITRA hose clamp crimping tool, compound action, straight jaw	1	0.9	\$51.00
HCT-AC	NITRA hose clamp crimping tool, compound action, side jaw	1	0.9	\$52.00

