



# Hose Clamps



**HC-58**

<b>NITRA Adjustable Hose Clamps</b>				
<b>Part No.</b>	<b>Description</b>	<b>Pcs/Pkg</b>	<b>Weight (lbs)</b>	<b>Price</b>
<b>HC-316</b>	NITRA hose clamp, 2-ear, 0.318-0.433in diameter, plated steel. For use with HBV series 3/16in hose.	10	0.1	\$4.00
<b>HC-14</b>	NITRA hose clamp, 2-ear, 0.425-0.512in diameter, plated steel. For use with HBV series 1/4in hose.	10	0.1	\$4.00
<b>HC-516</b>	NITRA hose clamp, 2-ear, 0.492-0.591in diameter, plated steel. For use with HBV series 5/16in hose.	10	0.1	\$4.25
<b>HC-38</b>	NITRA hose clamp, 2-ear, 0.551-0.669in diameter, plated steel. For use with HBV series 3/8in hose.	10	0.1	\$4.50
<b>HC-12</b>	NITRA hose clamp, 2-ear, 0.638-0.787in diameter, plated steel. For use with HBV series 1/2in hose.	10	0.1	\$4.75
<b>HC-58</b>	NITRA hose clamp, 2-ear, 0.748-0.906in diameter, plated steel. For use with HBV series 5/8in hose.	10	0.2	\$5.50
<b>HC-34</b>	NITRA hose clamp, 2-ear, 0.945-1.102in diameter, plated steel. For use with HBV series 3/4in hose.	10	0.3	\$7.00
<b>HC-1</b>	NITRA hose clamp, 2-ear, 1.154-1.339in diameter, plated steel. For use with HBV series 1in hose.	10	0.3	\$11.50



**HCSS-58**

<b>NITRA Interlocking Hose Clamps</b>				
<b>Part No.</b>	<b>Description</b>	<b>Pcs/Pkg</b>	<b>Weight (lbs)</b>	<b>Price</b>
<b>HCSS-316</b>	NITRA hose clamp, interlocking ear, 0.346-0.413in diameter, 304 stainless steel. For use with HBV series 3/16in hose.	10	0.1	\$4.50
<b>HCSS-14</b>	NITRA hose clamp, interlocking ear, 0.398-0.465in diameter, 304 stainless steel. For use with HBV series 1/4in hose.	10	0.1	\$4.50
<b>HCSS-516</b>	NITRA hose clamp, interlocking ear, 0.472-0.571in diameter, 304 stainless steel. For use with HBV series 5/16in hose.	10	0.1	\$4.75
<b>HCSS-38</b>	NITRA hose clamp, interlocking ear, 0.520-0.618in diameter, 304 stainless steel. For use with HBV series 3/8in hose.	10	0.1	\$4.75
<b>HCSS-12</b>	NITRA hose clamp, interlocking ear, 0.654-0.780in diameter, 304 stainless steel. For use with HBV series 1/2in hose.	10	0.1	\$5.50
<b>HCSS-58</b>	NITRA hose clamp, interlocking ear, 0.823-0.949in diameter, 304 stainless steel. For use with HBV series 5/8in hose.	10	0.1	\$5.75
<b>HCSS-34</b>	NITRA hose clamp, interlocking ear, 0.941-1.067in diameter, 304 stainless steel. For use with HBV series 3/4in hose.	10	0.1	\$6.00
<b>HCSS-1</b>	NITRA hose clamp, interlocking ear, 1.236-1.362in diameter, 304 stainless steel. For use with HBV series 1in hose.	10	0.1	\$6.25



# Hose Crimping Tools

**NITRA** hose crimping tools are designed to work with 2-ear and interlocking ear hose clamps. They come in three styles.

- Straight jaw single action, straight jaw compound action and side jaw compound action styles available
- Made in USA



**HCT-ES**



**HCT-SC**



**HCT-AC**

Nitra Hose Crimping Tools				
Part Number	Description	Pcs/Pkg	Package Weight (lbs)	Price
<b>HCT-ES</b>	NITRA hose clamp crimping tool, single action, straight jaw	1	0.8	\$30.00
<b>HCT-SC</b>	NITRA hose clamp crimping tool, compound action, straight jaw	1	0.9	\$55.00
<b>HCT-AC</b>	NITRA hose clamp crimping tool, compound action, side jaw	1	0.9	\$56.00

