



1/4" NPT Stainless Steel Manifolds



MRS-2CB

NITRA stainless steel manifolds


- 303 Stainless Steel
- Maximum input pressure of 3500 psi
- Made in the USA



NITRA® 1/4" NPT Stainless Steel Manifolds					
Part No.	Description	A	Parts Per Pkg	Weight (lbs)	Price
MRS-2CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 2 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	1.75 [44.5]	1	0.4	\$49.50
MRS-3CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 3 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	2.50 [63.0]	1	0.5	\$54.00
MRS-4CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 4 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	3.25 [82.6]	1	0.7	\$58.00
MRS-5CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 5 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	4.00 [101.6]	1	0.9	\$62.00
MRS-6CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 6 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	4.75 [120.7]	1	1.1	\$65.00
MRS-7CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 7 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	5.50 [139.7]	1	1.2	\$69.00
MRS-8CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 8 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	6.25 [158.8]	1	1.4	\$74.00
MRS-9CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 9 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	7.00 [177.8]	1	1.6	\$79.00
MRS-10CB	NITRA pneumatic manifold, stainless steel, rectangular, (2) 1/4 inch female NPT inlet port(s), 10 stations, (1) 1/8 inch female NPT outlet port(s) per station, standard hole spacing.	7.75 [196.9]	1	1.7	\$85.00

Dimensions

inches [mm]



See our website www.AutomationDirect.com for complete Engineering drawings.



3/8" NPT Stainless Steel Manifolds



MRS-2DC


- NITRA** stainless steel manifolds
- 303 Stainless Steel
 - Maximum input pressure of 3500 psi
 - Made in the USA



NITRA® 3/8" NPT Stainless Steel Manifolds					
Part No.	Description	A	Parts Per Pkg	Weight (lbs)	Price
MRS-2DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 2 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	2.13 [54.1]	1	0.7	\$58.00
MRS-3DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 3 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	3.00 [76.2]	1	1.0	\$65.00
MRS-4DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 4 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	3.88 [98.6]	1	1.3	\$70.00
MRS-5DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 5 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	4.75 [120.7]	1	1.6	\$78.00
MRS-6DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 6 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	5.63 [143.0]	1	1.9	\$85.00
MRS-7DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 7 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	6.50 [165.1]	1	2.2	\$92.00
MRS-8DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 8 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	7.38 [187.5]	1	2.5	\$100.00
MRS-9DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 9 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	8.25 [209.6]	1	2.8	\$107.00
MRS-10DC	NITRA pneumatic manifold, stainless steel, rectangular, (2) 3/8 inch female NPT inlet port(s), 10 stations, (1) 1/4 inch female NPT outlet port(s) per station, standard hole spacing.	9.13 [231.9]	1	3.1	\$116.00

Dimensions

inches [mm]



See our website www.AutomationDirect.com for complete Engineering drawings.