

C-more Replacement Parts

For new applications choose EA9 series C-more panels, part numbers EA9-TxCL(-R).

The optional replacement parts can be used to replace damaged, worn or lost C-more components.

Part Number	Description	Price
EA-15-BULB* EA-15-BULB2*	15" Panel Backlight Bulb Replacement	<--->
EA-12-BULB* EA-12-BULB2*	12" Panel Backlight Bulb Replacement	<--->
EA-10-BULB* EA-10-BULB2*	10" Panel Backlight Bulb Replacement	<--->
EA-8-BULB* EA-8-BULB2*	8" Panel Backlight Bulb Replacement	<--->
EA-DC-CON	DC Panel Power Connector Replacement	<--->
EA-AC-CON	AC Power Adapter Connector Replacement	<--->
D2-BAT-1	Replacement Battery	<--->
EA-BRK-1	6" Panel Mounting Clip Replacements (2 per pk.)	<--->
EA-BRK-2	8"-15" Panel Mounting Clip Replacements (8 per pk.)	<--->
EA-15-BEZEL	15" Panel Bezel Replacement	<--->
EA-12-BEZEL	12" Panel Bezel Replacement	<--->
EA-10-BEZEL	10" Panel Bezel Replacement	<--->
EA-8-BEZEL	8" Panel Bezel Replacement	<--->
EA-15-GSK	15" Panel Gasket Replacement	<--->
EA-12-GSK	12" Panel Gasket Replacement	<--->
EA-10-GSK	10" Panel Gasket Replacement	<--->
EA-8-GSK	8" Panel Gasket Replacement	<--->
EA-6-GSK	6" Panel Gasket Replacement	<--->
EA-6-ADPTR-GSK	6" Adapter Plate Gasket Replacement	<--->

Replacement parts at a glance:

Battery:
D2-BAT-1

6-inch mounting clips:
EA-BRK-1 (pk of 2)

8 - 15 inch mounting clips:
EA-BRK-2 (pk of 8)

DC power connector:
EA-DC-CON

AC power connector:
EA-AC-CON

15-inch backlight:
EA-15-BULB
EA-15-BULB2

12-inch backlight:
EA-12-BULB
EA-12-BULB2

10-inch backlight:
EA-10-BULB
EA-10-BULB2

8-inch backlight:
EA-8-BULB
EA-8-BULB2

15-inch gasket:
EA-15-GSK

12-inch gasket:
EA-12-GSK

10-inch gasket:
EA-10-GSK

8-inch gasket:
EA-8-GSK

6-inch gasket:
EA-6-GSK

15-inch Bezel:
EA-15-BEZEL (gasket not included)

12-inch Bezel:
EA-12-BEZEL (gasket not included)

10-inch Bezel:
EA-10-BEZEL (gasket not included)

8-inch Bezel:
EA-8-BEZEL (gasket not included)

Note: 6-inch bezel is not user replaceable.

6-inch Adapter Plate replacement gasket
EA-6-ADPTR-GSK

PLEASE REFER TO THE INDIVIDUAL DATA SHEET INSERTS THAT ARE INCLUDED WITH EACH REPLACEMENT PART FOR ADDITIONAL DETAILS.

*C-more Replacement Bulbs		
C-more Model	Bulb Model	C-more Serial Number
EA7-T8C	EA-8-BULB	EA7-T8C+10Z15B020 and older
	EA-8-BULB2	EA7-T8C+10Z15B021 thru EA7-T8C+12Y25B070
	Non-Replaceable LED	EA7-T8C+12Y25B071 and newer
EA7-T10C	EA-10-BULB	EA7-T10C+10Z11B080 and older
	EA-10-BULB2	EA7-T10C+10Z11B081 thru EA7-T10C+12Y29B120
	Non-Replaceable LED	EA7-T10C+12Y29B121 and newer
EA7-T12C	EA-12-BULB	EA7-T12C+10Z29B019 and older
	EA-12-BULB2	EA7-T12C+10Z29B020 thru EA7-T12C+XXXXXXXX
	Non-Replaceable LED	EA7-T12C+XXXXXXXX and newer
EA7-T15C	EA-15-BULB	EA7-T15C+10Z22B120 and older
	EA-15-BULB2	EA7-T15C+10Z22B121 thru EA7-T15C+XXXXXXXX
	Non-Replaceable LED	EA7-T15C+XXXXXXXX and newer

Part No.
EA-8-BULB, EA-8-BULB2,
EA-10-BULB, EA-10-BULB2,
EA-12-BULB, EA-12-BULB2,
EA-15-BULB, & EA-15-BULB2
see table



Panels with serial numbers newer than November 2013 do not have user replaceable backlights. For earlier panels, the correct replacement bulb part number is provided in the adjacent table. No 6" panels have user replaceable backlights. Older 8", 10" and 15" touch panels use two bulbs per panel and the 12" touch panels use one bulb per panel. The bulbs are packaged two per box for the 8", 10" and 15" touch panels and one per box for the 12" touch panels.

Serial Number = [Part Number]+[YYMDDFNNN]

Date Code = YYMF

- YY: Year (05-99 --- e.g. 05 = 2005)
- M: Month (1-9, X, Y, Z --- e.g. X = Oct.)
- DD: Day (1-31)
- F: Manufacturing Site (0-9, A-Z)
- NNN: Sequence number for the date listed (000-999)

C-more Replacement Parts

For new applications choose EA9 series C-more panels, part numbers EA9-TxCL(-R).



MAINTENANCE AND ACCESSORY INSTRUCTION SHEETS CAN BE VIEWED AND DOWNLOADED ONLINE AT:
[HTTP://WWW.AUTOMATIONDIRECT.COM/STATIC/MANUALS/EAUSERM/EAUSERM.HTML](http://www.automationdirect.com/Static/Manuals/EAUSERM/EAUSERM.HTML)

DC Power Connector Part No. EA-DC-CON



Replacement 5-terminal DC power connector for C-more touch panels.

AC Power Connector Part No. EA-AC-CON



Replacement 3-terminal AC power connector for C-more touch panel AC Power Adapters.

Replacement Battery Part No. D2-BAT-1



Backup Battery (supplied with new panels)
 C-more panels use battery backed RAM to store retentive values for internal tags. This battery will last for up to two years, and is easy to replace. You can even set up an alarm condition, and let C-more remind you when the battery needs replacing. The C-more panels come with the D2-BAT-1 already installed.

NOTE: The D2-BAT-1 is the same battery used in our DL06, D2-250(-1), D2-260 and D3-350 PLC products.

6" Panel Mounting Clips Part No. EA-BRK-1



Spare panel mounting clips for 6-inch C-more touch panels. Package of 2 clips with 4 screws.

8"-15" Panel Mounting Clips Part No. EA-BRK-2




Spare panel mounting clips for the 8-inch through 15-inch C-more touch panels. Package of 8 clips with 8 screws.

Part No. EA-8-BEZEL, EA-10-BEZEL, EA-12-BEZEL and EA-15-BEZEL




NEMA 4/4X bezel, customer replaceable, for C-more 8", 10", 12" and 15" touch panels. Gasket not included.

Part No. EA-6-GSK, EA-8-GSK, EA-10-GSK, EA-12-GSK and EA-15-GSK



Replacement NEMA 4/4X touch panel gaskets for C-more 6", 8", 10", 12" and 15" touch panels.

Part No. EA-6-ADPTR-GSK



6-inch replacement NEMA 4/4X gasket for the C-more touch panel adapter plate.



CAUTION - The battery used in this device may present a risk of fire or chemical burn if mistreated. Do not recharge, disassemble, heat above 100 °C (212 °F) or incinerate. Replace battery with AutomationDirect part number D2-BAT-1 or CR2354 only. Use of another battery may present a risk of fire or explosion. Dispose of used battery properly. Keep away from children.

Perchlorate Material, special disposal handling may apply.