

# Enclosure Subpanels



## Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

- 14-gauge
- Painted steel and perforated subpanels are painted white polyester powder over phosphatized surfaces
- Galvanized panels have a conductive finish (no paint)
- Panels listed fit the following enclosures:
  - NEMA 1 small (N1C)
  - NEMA 3R small (RHC)
  - NEMA 12 WA\_GIE



### Shipping Schedule

Same day 1 - 5 days 1 - 7 days 1 - 15 days 1 - 20 days

Color indicates shipping lead time in business days.


### Subpanels for Small NEMA 1, NEMA 3R and NEMA 12 Enclosures

Painted Steel	Price	Galvanized	Price	Perforated	Price	Nominal Enclosure Size HxW	Subpanel Size AxB
<a href="#"><u>N1P0606</u></a>	–	<a href="#"><u>N1P0606G</u></a>	Retired	<a href="#"><u>N1P0606PP</u></a>	Retired	6 x 6	4.25 x 4.25 [108 x 108]
<a href="#"><u>N1P0608</u></a>	–	<a href="#"><u>N1P0608G</u></a>	–	<a href="#"><u>N1P0608PP</u></a>	Retired	6 x 8	6.25 x 4.25 [159 x 108]
<a href="#"><u>N1P0808</u></a>	–	<a href="#"><u>N1P0808G</u></a>	–	<a href="#"><u>N1P0808PP</u></a>	Retired	8 x 8	6.25 x 6.25 [159 x 159]
<a href="#"><u>N1P0810</u></a>	–	<a href="#"><u>N1P0810G</u></a>	–	<a href="#"><u>N1P0810PP</u></a>	Retired	8 x 10	8.25 x 6.25 [210 x 159]
<a href="#"><u>N1P1010</u></a>	–	<a href="#"><u>N1P1010G</u></a>	Retired	<a href="#"><u>N1P1010PP</u></a>	Retired	10 x 10	8.25 x 8.25 [210 x 210]
<a href="#"><u>N1P1012</u></a>	–	<a href="#"><u>N1P1012G</u></a>	Retired	<a href="#"><u>N1P1012PP</u></a>	Retired	10 x 12	10.25 x 8.25 [260 x 210]
<a href="#"><u>N1P1212</u></a>	–	<a href="#"><u>N1P1212G</u></a>	Retired	<a href="#"><u>N1P1212PP</u></a>	Retired	12 x 12	10.25 x 10.25 [260 x 260]
<a href="#"><u>N1P1214</u></a>	–	<a href="#"><u>N1P1214G</u></a>	Retired	<a href="#"><u>N1P1214PP</u></a>	Retired	12 x 14	12.25 x 10.25 [311 x 260]
<a href="#"><u>N1P1216</u></a>	–	<a href="#"><u>N1P1216G</u></a>	Retired	<a href="#"><u>N1P1216PP</u></a>	Retired	12 x 16	14.25 x 10.25 [362 x 260]
<a href="#"><u>N1P1220</u></a>	–	<a href="#"><u>N1P1220G</u></a>	Retired	<a href="#"><u>N1P1220PP</u></a>	Retired	12 x 20	18.25 x 10.25 [464 x 260]

Notes: Dimensions in inches [millimeters].

Letters in table correspond to letters on dimensional drawing.

## Dimensions



Note: Perforated panels have 0.13in [3 mm] diameter holes at 0.25in [6 mm] spacing.