


HydroMode™ Lead Free Brass Adapter Fittings

HydroMode lead free brass fittings are designed for use in potable water and beverage applications. These hose barb adapters work well with PVC hose and stainless steel hose clamps.

Note: Actual product dimensions and appearance may vary



NLBHB-316-18N



HydroMode™ Lead Free Brass Straight Barb Fitting								
Inch Sizes - dimensions in inches [mm]								
Part No.	Price	Description	Parts Per Pkg	Weight	T	L	ØD	C Hex
NLBHB-316-18N		Straight barb, 3/16 inch hose to 1/8 inch male NPT	3	0.1	1/8	1.27 [32.1]	0.20 [5.1]	0.44 [11.1]
NLBHB-14-18N		Straight barb, 1/4 inch hose to 1/8 inch male NPT	3	0.1	1/8	1.43 [36.3]	0.24 [6.1]	0.44 [11.1]
NLBHB-14-14N		Straight barb, 1/4 inch hose to 1/4 inch male NPT	3	0.1	1/4	1.69 [42.9]	0.24 [6.1]	0.56 [14.3]
NLBHB-516-18N		Straight barb, 5/16 inch hose to 1/8 inch male NPT	3	0.1	1/8	1.40 [35.6]	0.29 [7.4]	0.44 [11.1]
NLBHB-516-14N		Straight barb, 5/16 inch hose to 1/4 inch male NPT	3	0.1	1/4	1.43 [36.3]	0.29 [7.4]	0.56 [14.3]
NLBHB-38-14N		Straight barb, 3/8 inch hose to 1/4 inch male NPT	3	0.1	1/4	1.63 [41.5]	0.36 [9.2]	0.56 [14.3]
NLBHB-38-38N		Straight barb, 3/8 inch hose to 3/8 inch male NPT	3	0.2	3/8	1.52 [38.6]	0.36 [9.2]	0.69 [17.5]
NLBHB-38-12N		Straight barb, 3/8 inch hose to 1/2 inch male NPT	3	0.2	1/2	1.61 [40.9]	0.36 [9.2]	0.88 [22.2]
NLBHB-12-14N		Straight barb, 1/2 inch hose to 1/4 inch male NPT	3	0.2	1/4	1.64 [41.8]	0.48 [12.3]	0.56 [14.3]
NLBHB-12-38N		Straight barb, 1/2 inch hose to 3/8 inch male NPT	3	0.2	3/8	1.74 [44.1]	0.48 [12.3]	0.69 [17.5]
NLBHB-12-12N		Straight barb, 1/2 inch hose to 1/2 inch male NPT	3	0.3	1/2	1.80 [45.7]	0.48 [12.3]	0.88 [22.2]
NLBHB-58-12N		Straight barb, 5/8 inch hose to 1/2 inch male NPT	3	0.3	1/2	1.84 [46.7]	0.60 [15.3]	0.88 [22.2]
NLBHB-34-12N		Straight barb, 3/4 inch hose to 1/2 inch male NPT	3	0.3	1/2	1.78 [45.2]	0.73 [18.5]	0.88 [22.2]
NLBHB-34-34N		Straight barb, 3/4 inch hose to 3/4 inch male NPT	3	0.4	3/4	1.90 [48.3]	0.73 [18.5]	1.06 [27.0]