

KNIPEX® Wire Stripping and Dismantling Tools

Electrician's Pliers

Features

- Designed for gripping and bending wire
- Ideal for cutting soft, medium, and hard wire
- Precision cutting edges induction-hardened to 60 HRC
- Vanadium electric steel; oil-hardened, and tempered






1301160



1301614SBA

| Wire Stripping and Dismantling Tools | | | | | | | | |
|--------------------------------------|---|---|---------------------|---------------------|---------------------|--------------------|---------|-------|
| Part Number | Description | Stripping Capacity | Cutting Capacity Ø | | Length | Weight | Pcs/Pkg | Price |
| | | | Med-Hard | Hard | | | | |
| 1301160 | 4 in 1 electrician pliers, plastic-coated handles: for gripping, cutting, stripping, and crimping | 20-18/ 15 / 13 AWG [0.5-0.75 / 1.5 / 2.5 mm ²] | 0.10 in [2.5 mm] | 0.06 in [1.6 mm] | 6.30 in [160 mm] | 3.95 oz [112 g] | 1 | |
| 1301614SBA | 4 in 1 electrician pliers, plastic-coated handles: for gripping, cutting, stripping, and crimping | 14, 12, 10 AWG [2.1 / 3.3 / 5.3 mm ²] | 0.10 in [2.5 mm] | 0.06 in [1.6 mm] | 6.30 in [160 mm] | 3.95 oz [112 g] | 1 | |

Inch dimensions are rounded to the nearest hundredth. HRC refers to Rockwell C Scale.



Wire Stripping Tools

Cable Stripping Tool Features

- Designed to dismantle round PVC, rubber, silicone, PTFE cables
- Self-cocking holding lever
- Replaceable blade
- Plastic housing; impact-resistant

Data Cable Stripping Tool Features

- Designed to strip UTP and STP data cables
- Double shell, folding back stripping tool
- Opening spring and locking lever
- Practical clip for safe transport
- Plastic housing; fiberglass-reinforced

| Wire Stripping and Dismantling Tools | | | | | | | |
|--------------------------------------|--|-----------------------------------|---|---------------------|--------------------|---------|-------|
| Part Number | Description | Stripping Capacity Ø | Stripping Capacity Cross Section | Length | Weight | Pcs/Pkg | Price |
| 1630135SB | Shock-resistant cable stripping tool, plastic body | 0.24 - 1.14 in [6.0 - 29.0 mm] | N/A | 5.31 in [135 mm] | 4.23 oz [120 g] | 1 | |
| 1639135 | Spare blade for 1630135SB | N/A | N/A | N/A | 0.39 oz [11 g] | 1 | |
| 1665125SB | Data cable stripper, Cat 5, Cat 6, Cat 7, Twisted-Pair (UTP/STP) | 0.18 - 0.39 in [4.5 - 10.0 mm] | 24 - 11 AWG [0.2 - 4.0 mm ²] | 4.92 in [125 mm] | 1.76 oz [50 g] | 1 | |

Inch dimensions are rounded to the nearest hundredth.



1630135SB



1665125SB