

Subpanels for Heartland Series Enclosures

Aluminum Subpanels

- Material: 3003-H14 aluminum
- Finish: Mill



Aluminum Subpanels				
Part Number	Price	Subpanel Size HxW	Fits Heartland series Enclosures	Drawing Link
BP66A		4.88 x 4.88 [124 x 124]	AHx664xxx	PDF
BP86A		6.88 x 4.88 [175 x 124]	AHx864xxx	PDF
BP88A		6.88 x 6.88 [175 x 175]	AHx884xxx	PDF
BP108A		8.88 x 6.88 [226 x 175]	AH1083xxx AH1084xxx AHx1086xxx	PDF
BP1010A		8.88 x 8.88 [226 x 226]	AHxx10106xxx	PDF
BP1210A		10.88 x 8.88 [276 x 226]	AH12104xxx AHxx12106xxx	PDF
BP1412A		12.88 x 10.88 [327 x 276]	AH14124xxx AHxx14126xxx	PDF
BP1614A		14.88 x 12.88 [378 x 327]	AH16144xxx AHxx16148xxx	PDF
BP1816A		16.88 x 14.88 [429 x 378]	AH18164xxx AHxx181610xxx	PDF
BP2016A		18.88 x 14.88 [480 x 378]	AH20164xxx AHxx20168xxx	PDF
BP2424A		22.88 x 22.88 [581 x 581]	AH24246xxx AH242410xxx	PDF
Note: Dimensions in inches (millimeters).				



BP66A

Aluminum Swing Panel Kits

- Material: 3003-H14 aluminum
- Finish: Mill
- Includes swing panel, (4) AHSPM brackets and mounting screws

Aluminum Swing Panel Kits				
Part Number	Price	Subpanel Size HxW	Fits Heartland series Enclosures	Drawing Link
AH66SPK		5.63 x 5.63 [143 x 143]	AHx664xxx	PDF
AH86SPK		7.63 x 5.63 [194 x 143]	AHx864xxx	PDF
AH88SPK		7.63 x 7.63 [194 x 194]	AH884xxx	PDF
AH108SPK		9.63 x 7.63 [245 x 194]	AHx1084xxx AHx1086xxx	PDF
AH1010SPK		9.63 x 9.63 [245 x 245]	AHxx10106xxx	PDF
AH1210SPK		11.63 x 9.63 [295 x 245]	AHxx12106xxx	PDF
AH1412SPK		13.63 x 11.63 [346 x 295]	AHxx14126xxx	PDF
AH1614SPK		15.63 x 13.63 [397 x 346]	AHxx16148xxx	PDF
AH1816SPK		17.63 x 15.63 [448 x 397]	AH18164xxx AHxx181610xxx	PDF
AH2016SPK		19.63 x 15.63 [499 x 397]	AHxx20168xxx	PDF
AH2424SPK		23.63 x 23.63 [600 x 600]	AHxx242410xxx	PDF
Note: Dimensions in inches (millimeters). Not compatible with Heartland SL enclosures				



AH66SPK

Subpanels for Heartland Series Enclosures

Aluminum Side Panels

- Material: 3003-H14 aluminum
- Finish: Mill



Aluminum Subpanels				
Part Number	Price	Subpanel Size HxW	Fits Heartland series Enclosures	Drawing Link
SP6		5.00 x 3.00 [127 x 76]	AH664xxx AHF664x	PDF
SP8		7.00 x 3.00 [178 x 76]	AH864xxx AHF864x AH884xxx AHF884x	PDF
SP10		9.00 x 3.50 [229 x 89]	AH1084xxx AHF1084x AH10xx6xxx AHF10xx6x	PDF
SP12		11.00 x 5.00 [279 x 127]	AH12106xxx AHF12106x	PDF
SP14		13.00 x 5.00 [330 x 127]	AH14126xxx AHF14126x	PDF
SP16		15.00 x 7.00 [381 x 178]	AH16148xxx AHF16148x	PDF
SP18		17.00 x 9.00 [432 x 229]	AH181610xxx AHF181610x	PDF
SP20		19.00 x 7.00 [483 x 178]	AH20168xxx AHF20168x	PDF
SP24		23.00 x 9.00 [584 x 229]	AH242410xxx	PDF
Note: Dimensions in inches (millimeters). Corrosion resistant slot nut fastening hardware kit included				

[SP8](#)

ABS Plastic Subpanels

- Material: ABS plastic
- Finish: Mill

ABS plastic Subpanels				
Part Number	Price	Subpanel Size HxW	Fits Heartland series Enclosures	Drawing Link
BP66ABS		4.75 x 4.75 [121 x 121]	AHx664xxx	PDF
BP86ABS		6.75 x 4.75 [171 x 121]	AHx864xxx	PDF
BP108ABS		8.75 x 6.75 [222 x 171]	AH1083xxx AH1084xxx AHx1086xxx	PDF
BP1010ABS		8.75 x 8.75 [222 x 222]	AHxx10106xxx	PDF
BP1210ABS		10.75 x 8.75 [273 x 222]	AH12104xxx AHxx12106xxx	PDF
BP1412ABS		12.75 x 10.75 [324 x 273]	AH14124xxx AHxx14126xxx	PDF
BP1614ABS		14.75 x 12.75 [375 x 324]	AH16144xxx AHxx16148xxx	PDF
BP1816ABS		16.75 x 14.75 [425 x 375]	AH18164xxx AHxx181610xxx	PDF
BP2016ABS		18.75 x 14.75 [476 x 375]	AH20164xxx AHxx20168xxx	PDF
BP2424ABS		22.75 x 22.75 [578 x 578]	AH24246xxx AH242410xxx	PDF
Note: Dimensions in inches (millimeters).				

[BP108ABS](#)