



1/4 inch Drive Metric Ratchet Sets



Zyklop Speed Ratchet and Socket Sets

1/4 inch Drive Metric Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price Each
05003532055	Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 18 pieces, includes ratchet, 75 mm and 150 mm extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, (13) sockets (4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 and 14 mm). Manufacturer part number: 003532. Sturdy metal case included.	1 set	
05003533055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 42 pieces, includes ratchet, 75 mm and 150 mm locking extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, 56 mm wobble extension, 1/4 inch x 1/4 inch x 37 mm long bit adaptor, (13) sockets (4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 and 14 mm), (3) flat/slotted bits (4.5, 5.5 and 8.0 mm), (3) Phillips bits (#1, #2 and #3), (3) Pozidriv bits (#1, #2 and #3), (5) Hex-Plus bits (3, 4, 5, 6 and 8 mm), (8) Torx bits (TX8, TX9, TX10, TX15, TX20, TX25, TX30 and TX40). Manufacturer part number: 003533. Sturdy metal case included.	1 set	
05051045055	Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, SAE, 15 pieces, includes ratchet, 75 mm and 150 mm extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, (10) sockets (3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 and 9/16 inch). Manufacturer part number: 003534. Sturdy metal case included.	1 set	



Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 18 pieces. Includes the pieces listed in the table below.

05003532055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	Sliding T-handle	1/4 x 110
	6-point socket	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
	Extension	1/4 x 150, 1/4 x 75
	Universal joint	1/4 x 35.5

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**

Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 42 pieces. Includes the pieces listed in the table below.

05003533055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	Sliding T-handle	1/4 x 110
	6-point socket	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
	Wobble extension	1/4 x 56
	Universal joint	1/4 x 35.5
	Lockable extension	1/4 x 75, 1/4 x 150
	Bit adaptor	1/4 x 37
	Flat (slotted) bit	0.6 x 4.5, 1.0 x 5.5, 1.2 x 8
	Hex bit	3, 4, 5, 6, 8
	Phillips bit	PH 1, PH 2, PH 3
	Pozidriv bit	PZ 1, PZ 2, PZ 3
	Tamper-proof Torx® bit	TX 8, TX 9, TX 10, TX 15, TX 20, TX 25, TX 30, TX 40

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**

Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, SAE, 15 pieces. Includes the pieces listed in the table below.

05051045055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	6-point socket	5.5, 6, 7, 8, 10, 12, 13
	Lockable extension	1/4 x 150
	Bit adaptor	1/4 x 37
	Flat (slotted) bit - 50mm long	1.0 x 5.5
	Hex bit - 50mm long	3, 4, 5, 6
	Phillips bit	PH 1, PH 2, PH 3
	Pozidriv bit	PZ 1, PZ 2
	Tamper-proof Torx® bit	TX 10, TX 15, TX 20, TX 25, TX 30, TX 40

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**



Wera

Zyklop Speed Ratchet and Socket Sets

1/4 inch Drive Imperial Ratchet Sets



1/4 inch Drive Imperial Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price Each
05003534055	Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, SAE, 15 pieces, includes ratchet, 75 mm and 150 mm extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, (10) sockets (3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 and 9/16 inch). Manufacturer part number: 003534. Sturdy metal case included.	1 set	
05003535055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, SAE, 41 pieces, includes ratchet, 75 mm and 150 mm locking extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, 56 mm wobble extension, 1/4 inch x 1/4 inch x 37 mm long bit adaptor, (10) sockets (3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2 and 9/16 inch), (3) flat/slotted bits (4.5, 5.5 and 8.0 mm), (3) Phillips bits (#1, #2 and #3), (3) Pozidriv bits (#1, #2 and #3), (7) Hex-Plus bits (5/64, 3/32, 1/8, 9/64, 5/32, 3/16 and 7/32 inch), (8) Torx bits (TX8, TX9, TX10, TX15, TX20, TX25, TX30 and TX40). Manufacturer part number: 003535. Sturdy metal case included.	1 set	



Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, SAE, 15 pieces. Includes the pieces listed in the table below.

05003534055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	Sliding T-handle	1/4 x 4
	6-point socket	3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16
	Extension	1/4 x 6, 1/4 x 3
	Universal joint	1/4 x 1.4

Note: All dimensions are in inches.



Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, SAE, 41 pieces. Includes the pieces listed in the table below.

05003535055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	Sliding T-handle	1/4 x 4
	6-point socket	3/16, 7/32, 1/4, 9/32, 5/16, 11/32, 3/8, 7/16, 1/2, 9/16
	Wobble extension	1/4 x 2
	Universal joint	1/4 x 1.4
	Lockable extension	1/4 x 6, 1/4 x 3
	Bit adaptor	1/4 x 1.5
	Flat (slotted) bit	0.6 x 4.5, 1.0 x 5.5, 1.2 x 8.0
	Hex bit	5/64, 3/32, 1/8, 9/64, 5/32, 3/16, 7/32
	Phillips bit	PH 1, PH 2, PH 3
	Pozidriv bit	PZ 1, PZ 2, PZ 3
	Torx® bit	TX 8, TX 9, TX 10, TX 15, TX 20, TX 25, TX 30, TX 40

Note: All dimensions are in inches.



1/4 inch Drive Metric Ratchet Sets



Zyklop Speed Ratchet and Socket Sets

1/4 inch Drive Metric Ratchet Sets			
Part Number	Description	Pcs/Pkg	Price Each
05003532055	Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 18 pieces, includes ratchet, 75 mm and 150 mm extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, (13) sockets (4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 and 14 mm). Manufacturer part number: 003532. Sturdy metal case included.	1 set	
05003533055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 42 pieces, includes ratchet, 75 mm and 150 mm locking extensions with free-turning sleeves, 110 mm sliding T-handle, universal joint, 56 mm wobble extension, 1/4 inch x 1/4 inch x 37 mm long bit adapter, (13) sockets (4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 and 14 mm), (3) flat/slotted bits (4.5, 5.5 and 8.0 mm), (3) Phillips bits (#1, #2 and #3), (3) Pozidriv bits (#1, #2 and #3), (5) Hex-Plus bits (3, 4, 5, 6 and 8 mm), (8) Torx bits (TX8, TX9, TX10, TX15, TX20, TX25, TX30 and TX40). Manufacturer part number: 003533. Sturdy metal case included.	1 set	
05051045055	Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 26 pieces, includes ratchet, 150 mm extension with free-turning sleeve, 1/4 inch x 1/4 inch x 37 mm long bit adapter, (7) 1/4 inch drive sockets (5.5, 6, 7, 8, 10, 12 and 13 mm), 5.5 mm flat/slotted bit, (3) Phillips bits (#1, #2 and #3), (2) Pozidriv bits (#1 and #2), (4) Hex-Plus bits (3, 4, 5 and 6 mm), (6) Torx bits (TX10, TX15, TX20, TX25, TX27 and TX30). Manufacturer part number: 051045. Sturdy metal case included.	1 set	



Wera socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 18 pieces. Includes the pieces listed in the table below.

05003532055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	Sliding T-handle	1/4 x 110
	6-point socket	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
	Extension	1/4 x 150, 1/4 x 75
	Universal joint	1/4 x 35.5

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**

Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 42 pieces. Includes the pieces listed in the table below.

05003533055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	Sliding T-handle	1/4 x 110
	6-point socket	4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13, 14
	Wobble extension	1/4 x 56
	Universal joint	1/4 x 35.5
	Lockable extension	1/4 x 75, 1/4 x 150
	Bit adaptor	1/4 x 37
	Flat (slotted) bit	0.6 x 4.5, 1.0 x 5.5, 1.2 x 8
	Hex bit	3, 4, 5, 6, 8
	Phillips bit	PH 1, PH 2, PH 3
	Posidriv bit	PZ 1, PZ 2, PZ 3
	Torx® bit	TX 8, TX 9, TX 10, TX 15, TX 20, TX 25, TX 30, TX 40

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**

Wera driver bit and socket set with Zyklop Speed ratchet, 1/4 inch drive, metric, 26 pieces. Includes the pieces listed in the table below.

05051045055 Ratchet Set Contents		
	1/4 Zyklop ratchet	
	6-point socket	5.5, 6, 7, 8, 10, 12, 13
	Lockable extension	1/4 x 150
	Bit adaptor	1/4 x 37
	Flat (slotted) bit - 50mm long	1.0 x 5.5
	Hex bit - 50mm long	3, 4, 5, 6
	Phillips bit	PH 1, PH 2, PH 3
	Posidriv bit	PZ 1, PZ 2
	Torx® bit	TX 10, TX 15, TX 20, TX 25, TX 30, TX 40

**Note: Fractional dimensions are in inches.
Whole and decimal dimensions are in millimeters.**

Company
Information

Terminal Blocks

Power
Distribution
BlocksWiring
AccessoriesZIPLink
Connection
SystemMulti-wire
ConnectorsSensor Cables
and ConnectorsM12 Junction
BlocksPanel Interface
Connectors

Wiring Duct

Cable Ties

Wire

Bulk
Multi-conductor
CablesWire
Management
Products

Power Supplies

DC Converters

Transformers
and Filters

Circuit Protection

Tools

Test
Equipment

Enclosures

Enclosure
Climate ControlSafety: Electrical
ComponentsSafety: Protective
WearTerms and
Conditions

Wera Ratchets



Zyklop Speed Ratchet




Small return angle

The fine 72 tooth ratchet mechanism has a low return angle of 5°. This short stroke allows fast and precise work in small spaces.



Swivel ratchet head


The ratchet head pivots freely and locks at 0°, 15° and 90°, making it possible to work in confined spaces with ample hand clearance.



Simple direction change

Rotating the large thumbwheel quickly changes rotation from clockwise to counterclockwise from any position of the ratchet head.

Wera Speed Ratchets			
Part Number	Description	Pcs/ Pkg	Price Each
05003500055	Wera Zyklop Speed ratchet, 1/4 inch drive, with locking swivel head and ergonomic grip handle.	1	
05003550055	Wera Zyklop Speed ratchet, 3/8 inch drive, with locking swivel head and ergonomic grip handle.	1	
05003600055	Wera Zyklop Speed ratchet, 1/2 inch drive, with locking swivel head and ergonomic grip handle.	1	



Unbelievably fast

The gyrating mass design along with the Kraftform handle and free-turning sleeve allow for rapid rotation when used as a screwdriver.